

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [74547-2021](#)
Status: **Active**
Overview: iPass™ Connector System
Description: External iPass™ Mini Multi-Lane SAS-to-4X LaneLink™ SAS Cable Assembly, 26 Circuits, 28 AWG, 1.0m Length, Key 2, 4

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR64395
UL E72548

General

Product Family Cable Assemblies
Series [74547](#)
Comments Table Routing (Out Port), SAS
Connector to Connector Mini SAS-to-SFF-8470
Overview [iPass™ Connector System](#)
Product Name 4X, iPass™, LaneLink™, Mini Multi-Lane, Multi-Lane, SAS
UPC 822350238212

Physical

Cable Length 1.0m
Circuits (Loaded) 26, 4X
Color - Resin Black
Gender Male-Male
Lock to Mating Part Yes
Material - Metal Phosphor Bronze, Stainless Steel
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Packaging Type Bag
Pitch - Mating Interface 0.80mm
Plating min - Mating 1.016µm
Plating min - Termination 3.048µm
Single Ended No
Termination Interface: Style Surface Mount
Wire Insulation Diameter N/A
Wire Size AWG 28
Wire/Cable Type Parallel Pair


Electrical

Current - Maximum per Contact 1A
Shielded Yes
Voltage - Maximum 30V

Material Info

Reference - Drawing Numbers

Sales Drawing SD-74547-200



Series

image - Reference only

EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[74547Series](#)

Mates With

[75586](#) iPass™ Receptacle. [74548](#) EMI Housing Assembly

Use With

[74735](#) X2 Transceiver. [74739](#) XPAK Transceiver. [74548](#) Guide Rail

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74547-2021](#)