

nichicon

6mmL Chip Type, For general Audio Equipment



-

[illegible]

Capacitance
Lot No.

*Voltage Plastic platform 0.3MAX.

$\phi D \pm 0.5$
 $L \pm 0.3$
 $C \pm 0.2$
 $B \pm 0.2$
 E
 $A \pm 0.2$
 $0.5 - 0.8$

⊕ Positive
⊖ Negative

(mm)

ϕD	4	5	6.3
A	1.8	2.1	2.4
B	4.3	5.3	6.6
C	4.3	5.3	6.6
E	1.0	1.3	2.2
L	5.8	5.8	5.8

*Voltage mark for 6.3V is [6V].

1 2 3 4 5 6 7 8 9 10 11 12 13 14

U U K 1 C 1 0 0 M C U 1 G S

Type

Series name

Rated voltage (16V)

Capacitance (10µF)

Rated Capacitance tolerance (±20%)

Configuration

Size code

Taping code

[illegible]

- Rated Ripple(mA rms)at 85°C 120Hz

Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz~
Coefficient	0.70	1.00	1.17	1.36	1.50

- Taping Specifications are given in page 22.

CAT.8100T