

B

1

A

5. 材料 (MATERIAL)
 キャリアテープ: 導電性ポリスチレン (PS)
 CARRIER TAPE: CONDUCTIVE POLYSTYRENE (PS)
 トップテープ: 帯電防止ポリエチレンテレフタレート (PET)、
 ポリエチレン (PE)
 TOP TAPE: ANTISTATIC POLYETHYLENE TEREPHTHALATE (PET),
 POLYETHYLENE (PE)
 リール: 帯電防止ポリスチレン (PS)
 REEL: ELECTROSTATIC DISSIPATIVE POLYSTYRENE (PS)

EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	RELEASED 04/02/17 EC NO. J2004-2484 DRWN: Y. NUKANOBU CHK: T. HIRATA APPR: M. SASAO	DESCRIPTION	MATERIAL 材料	GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	SCALE //	DESIGN UNITS ☒ mm ☐ INCH	THIRD ANGLE PROJECTION	DIMENSIONS: ☐ mm ☐ INCH ☒ mm ONLY	SHT REVISE ON CAD ONLY	REV
						REFER TO NOTES 注記参照	10 UNDER 未満	±0.2	DRAWN BY & DATE Y. NUKANOBU '04/02/17	TITLE: Embstp Pkg FOR 0.5 B-T0-B PLUG Assy (Hgt=3) [ELECTRO CONDUCTIVITY]	SHEET NO. 1 OF 2	SIZE B	
						FINISH 仕上げ	10 OVER 以上 30 UNDER 未満	±0.25	CHECKED BY & DATE T. HIRATA '04/02/17				
						WIRE RANGE 適用電線範囲	30 OVER 以上	±0.3	APPROVED BY & DATE M. SASAO '04/02/17				MOLEX INCORPORATED
				0	REV	INS. RANGE 被覆外径	ANGLE 角度	±3°	CAD FILENAME SD-53748-001.SOI	MATERIAL NO. SEE CHART	DRAWING NO. SD-53748-001		
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.													

DWG. NO.
SD-53748-001

F

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D

C

B

A

F

E

D