

# Surface Mount Glass Passivated Junction Rectifier

## SUPERECTIFIER®



DO-213AA (GL34)

## FEATURES

- Superectifier structure for high reliability condition
- Ideal for automated placement
- Low forward voltage drop
- Low leakage current
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified
- Material categorization: For definitions of compliance please see [www.vishay.com/doc?999912](http://www.vishay.com/doc?999912)



**RoHS**  
COMPLIANT

## TYPICAL APPLICATIONS

For use in general purpose rectification of power supplies, inverters, converters and freewheeling diodes for consumer, automotive and telecommunication.

## MECHANICAL DATA

**Case:** DO-213AA, molded epoxy over glass body  
Molding compound meets UL 94 V-0 flammability rating  
Base P/N-E3 - RoHS-compliant, commercial grade  
Base P/NHE3 - RoHS-compliant, AEC-Q101 qualified

**Terminals:** Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102  
E3 suffix meets JESD 201 class 1A whisker test, HE3 suffix meets JESD 201 class 2 whisker test

**Polarity:** Two bands indicate cathode end - 1<sup>st</sup> band denotes device type and 2<sup>nd</sup> band denotes repetitive peak reverse voltage rating

| PRIMARY CHARACTERISTICS |                                  |
|-------------------------|----------------------------------|
| $I_{F(AV)}$             | 0.5 A                            |
| $V_{RRM}$               | 50 V, 100 V, 200 V, 400 V, 600 V |
| $I_{FSM}$               | 10 A                             |
| $V_F$                   | 1.2 V, 1.3 V                     |
| $I_R$                   | 5.0 $\mu$ A                      |
| $T_J$ max.              | 175 °C                           |
| Package                 | DO-213AA (GL34)                  |
| Diode variations        | Single die                       |

| MAXIMUM RATINGS (T <sub>A</sub> = 25 °C unless otherwise noted)                    |                                   |               |       |        |        |       |      |
|------------------------------------------------------------------------------------|-----------------------------------|---------------|-------|--------|--------|-------|------|
| PARAMETER                                                                          | SYMBOL                            | GL34A         | GL34B | GL34D  | GL34G  | GL34J | UNIT |
| STANDARD RECOVERY DEVICE: 1 <sup>ST</sup> BAND IS WHITE                            |                                   |               |       |        |        |       |      |
| Polarity color bands (2 <sup>nd</sup> band)                                        |                                   | Gray          | Red   | Orange | Yellow | Green |      |
| Max. repetitive peak reverse voltage                                               | V <sub>RRM</sub>                  | 50            | 100   | 200    | 400    | 600   | V    |
| Max. RMS voltage                                                                   | V <sub>RMS</sub>                  | 35            | 70    | 140    | 280    | 420   | V    |
| Max. DC blocking voltage                                                           | V <sub>DC</sub>                   | 50            | 100   | 200    | 400    | 600   | V    |
| Max. average forward rectified current at T <sub>L</sub> = 75 °C                   | I <sub>F(AV)</sub>                | 0.5           |       |        |        |       | A    |
| Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load | I <sub>FSM</sub>                  | 10            |       |        |        |       | A    |
| Max. full load reverse current, full cycle average at T <sub>A</sub> = 55 °C       | I <sub>R(AV)</sub>                | 30            |       |        |        |       | μA   |
| Operating junction and storage temperature range                                   | T <sub>J</sub> , T <sub>STG</sub> | - 65 to + 175 |       |        |        |       | °C   |

**ELECTRICAL CHARACTERISTICS** ( $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)

| PARAMETER                                            | TEST CONDITIONS                                                          |                         | SYMBOL          | GL34A | GL34B | GL34D | GL34G | GL34J | UNIT |
|------------------------------------------------------|--------------------------------------------------------------------------|-------------------------|-----------------|-------|-------|-------|-------|-------|------|
| Max. instantaneous forward voltage                   | 0.5 A                                                                    |                         | V <sub>F</sub>  | 1.2   |       |       |       | 1.3   | V    |
| Max. DC reverse current at rated DC blocking voltage |                                                                          | T <sub>A</sub> = 25 °C  | I <sub>R</sub>  | 5.0   |       |       |       |       | μA   |
|                                                      |                                                                          | T <sub>A</sub> = 125 °C |                 | 50    |       |       |       |       |      |
| Typical reverse recovery time                        | I <sub>F</sub> = 0.5 A, I <sub>R</sub> = 1.0 A, I <sub>rr</sub> = 0.25 A |                         | t <sub>rr</sub> | 1.5   |       |       |       |       | μs   |
| Typical junction capacitance                         | 4.0 V, 1 MHz                                                             |                         | C <sub>J</sub>  | 4.0   |       |       |       |       | pF   |

**THERMAL CHARACTERISTICS** ( $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)

| PARAMETER                  | SYMBOL                | GL34A | GL34B | GL34D | GL34G | GL34J | UNIT |
|----------------------------|-----------------------|-------|-------|-------|-------|-------|------|
| Maximum thermal resistance | $R_{\theta JA}^{(1)}$ | 150   |       |       |       |       | °C/W |
|                            | $R_{\theta JT}^{(2)}$ | 70    |       |       |       |       |      |

**Notes**

- (1) Thermal resistance from junction to ambient, 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pads to each terminal  
 (2) Thermal resistance from junction to terminal, 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pads to each terminal

**ORDERING INFORMATION** (Example)

| PREFERRED P/N              | UNIT WEIGHT (g) | PREFERRED PACKAGE CODE | BASE QUANTITY | DELIVERY MODE                      |
|----------------------------|-----------------|------------------------|---------------|------------------------------------|
| GL34G-E3/98                | 0.036           | 98                     | 2500          | 7" diameter plastic tape and reel  |
| GL34G-E3/83                | 0.036           | 83                     | 9000          | 13" diameter plastic tape and reel |
| GL34GHE3/98 <sup>(1)</sup> | 0.036           | 98                     | 2500          | 7" diameter plastic tape and reel  |
| GL34GHE3/83 <sup>(1)</sup> | 0.036           | 83                     | 9000          | 13" diameter plastic tape and reel |

**Note**

- (1) AEC-Q101 qualified


**RATINGS AND CHARACTERISTICS CURVES** ( $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)

Fig. 1 - Forward Current Derating Curve




Fig. 2 - Max. Non-Repetitive Peak Forward Surge Current




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 5 - Typical Junction Capacitance






Fig. 4 - Typical Reverse Characteristics

### PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

#### DO-213AA (GL34)



#### Mounting Pad Layout





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.