


PRODUCT NUMBER SEE NOTE 3	"DIM L"
10084660-E0100YYLF	1000mm



PIN OUT/WIRING TABLE (SEE NOTE 6)

FROM "P1"	WIRE SIZE	TYPE	TO "P2"	COLOR
POS. 1	10 AWG	POWER		RED
POS. 2	10 AWG	POWER		BLUE
SIG. 1	SHORT WITH SIG. 2			
SIG. 2	SHORT WITH SIG. 1			

mat'l. code				surface		tolerance		projection		product family																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																													
--				ISO 1302		ISO 406 ISO 1101				Cable Assembly																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																													
ltr	ecn no.	dr	date	tolerances unless otherwise specified								title																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																											
A	N08-0210	delhly	09/25/08	ANGULAR		LINEAR				MM		Pwr D-SUB 48V/DC TO CUT C&A																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																											
																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																							
										scale 4																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																													
				dr	delhly	Sep.25,08																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																	



FCIconnect.com


PRODUCT NUMBER SEE NOTE 3	"DIM L"
10084660-E0100YYLF	1000mm

NOTES:

- END "P1" MATES WITH FCI HEADER PART NUMBER: 10070158-00X1XXLF
END "P2" MATES WITH FCI HEADER PART NUMBER: N/A
- UNLESS OTHERWISE SPECIFIED ASSEMBLIES LENGTH TOLERANCE=
< = 1 METER: $\pm 15.0\text{mm}$
> 1 METER TO 10 METER: $\pm 2\%$ OF "DIM L"
> 10 METER: $+0.00\%$ / -4% OF "DIM L"
- PART NUMBER DESCRIPTION:

BASE NUMBER DASH NUMBER

1 0 0 8 4 6 6 0 - E 0 1 0 0 Y Y L F



- UNLESS OTHERWISE SPECIFIED LABEL POSITION SHALL BE APPROXIMATELY 50mm FROM REAR OF CONNECTOR
- UNLESS OTHERWISE SPECIFIED STANDARD LABEL SHALL BE FCI LABEL, LABEL DETAILS AS BELOW

FCI NT	- MANUFACTURE CODE OR NAME
10084660-E0100YYLF	- FCI P/N
REV A	- REVISION
WWYY	- DATE CODE WW/YY FORMAT
MADE IN CHINA	- COUNTRY ORIGIN

FONT SHALL BE CLEARLY VISABLE AND BLACK IN COLOR

- ALL CABLE ASSEMBLIES SHALL BE TESTED 100% FOR CONTINUITY AS DEFINED IN WIRING LIST
- UNLESS OTHERWISE SPECIFIED ALL CABLE ASSEMBLIES SHALL BE 100% HI-POT TESTED BY APPLYING 300V DC FOR MINIMUM FOR 10ms, UNLESS ACTIVE COMPONENTS ARE USED IN THIS ASSEMBLY
- OTHER TESTING PERFORMED AS REQUIRED BY PRODUCT SPECIFICATION: GS-XX-XXX
- THIS DIMENSION IS A FINISHED PRODUCT LENGTH
- LEAD FREE PRODUCTS MUST MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
LEAD FREE SOLDER TAIL PLATING 2.00um(80u") MIN. MATTE TIN OVER 1.27um(50u") MIN. NICKEL UNDERPLATE.
PACKAGING OF LEAD FREE PRODUCTS MEETS LABELING AND PACKAGING SPECIFICATION GS-14-920

- ASSEMBLY SHOWN IS FOR REFERENCE ONLY AND MAY NOT SHOW ALL PART DETAIL. REFERENCE CONNECTORE ASSEMBLY DRAWING FOR COMPLETE DETAILS
- GLOBAL STANDARDS FOR CABLE PACKAGING: GS-14-1093
- TUBING TO BE ADDED TO ALL 24 AWG SIGNAL CABLE, TUBING NOT SHOWN. CABLES SHALL BE TIE WRAPPED
- A "Δ" SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION. THE CURRENT REVISION WILL BE SHOWN IN THE SYMBOL
- CABLE: UL APPROVED, TEMPERATURE RATING 105°C. 600V MIN

mat'l. code				surface	tolerance	projection	product family			
--				ISO 1302	ISO 406 ISO 1101		Cable Assembly			
ltr	ecr no.	dr	date	tolerances unless otherwise specified			title			
A	N08-0210	delhly	09/25/08	ANGULAR	LINEAR	MM	Pwr D-SUB 48V/DC TO CUT C&A			
						scale 4				
				dr	delhly	Sep.25,08				
				engr	delhly	Sep.25,08				
				chr	delhly	Sep.25,08				
				appd	Jackson	Sep.25,08				
sheet index	revision	A	A					dwg no.	sheet 2 of 2	size
	sheet	1	2					10084660-E0100YYLF		A3
								Type	CUSTOMER	Drawing