


# SMD Power Inductor CDRH3D23



## Description

- Ferrite drum core construction.
- Magnetically shielded.
- L × W × H: 3.92 × 3.92 × 2.5 mm Max.
- Product weight: 112mg(Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.

## Environmental Data

- Operating temperature range: -40°C ~ +105°C (including coil's self temperature rise)
- Storage temperature range: -40°C ~ +105°C
- Solder reflow temperature: 260 °C peak.


## Packaging

- Carrier tape and reel packaging
- 7.0" diameter reel
- 500pcs per reel


## Applications

- Ideally used in Mobilephone, PDA, MP3, DSC/DVC, etc as DC-DC converter inductors.

## Dimension - [mm]



## Land pattern and Schematics - [mm]



# SMD Power Inductor

## CDRH3D23



### Electrical Characteristics

| Part Name        | Stamp | Inductance<br>( $\mu$ H)<br>[within] ※1 | D.C.R. (m $\Omega$ )<br>Max. (Typ.)<br>(at 20°C) | Saturation Current<br>(A) ※2 |          | Temperature<br>Rise Current<br>(A) ※3 |
|------------------|-------|-----------------------------------------|--------------------------------------------------|------------------------------|----------|---------------------------------------|
|                  |       |                                         |                                                  | at 20°C                      | at 105°C |                                       |
| CDRH3D23NP-R47NC | A     | $0.47 \pm 30\%$                         | 23.5(18.8)                                       | 3.10                         | 2.40     | 3.30                                  |
| CDRH3D23NP-1R0PC | A     | $1.0 \pm 25\%$                          | 25.0(20)                                         | 2.80                         | 2.00     | 3.10                                  |
| CDRH3D23NP-1R5PC | B     | $1.5 \pm 25\%$                          | 29.0(24)                                         | 2.20                         | 1.65     | 2.90                                  |
| CDRH3D23NP-2R2PC | C     | $2.2 \pm 25\%$                          | 38.3(31)                                         | 1.80                         | 1.30     | 2.50                                  |
| CDRH3D23NP-3R3PC | D     | $3.3 \pm 25\%$                          | 56.3(45)                                         | 1.45                         | 1.10     | 2.20                                  |
| CDRH3D23NP-4R7PC | E     | $4.7 \pm 25\%$                          | 68.8(55)                                         | 1.30                         | 0.95     | 1.90                                  |
| CDRH3D23NP-5R6PC | F     | $5.6 \pm 25\%$                          | 75.0(60)                                         | 1.10                         | 0.80     | 1.80                                  |
| CDRH3D23NP-6R8PC | G     | $6.8 \pm 25\%$                          | 87.8(72)                                         | 1.00                         | 0.75     | 1.70                                  |
| CDRH3D23NP-8R2PC | H     | $8.2 \pm 25\%$                          | 94.8(77)                                         | 0.95                         | 0.70     | 1.60                                  |
| CDRH3D23NP-100MC | I     | $10.0 \pm 20\%$                         | 117(95)                                          | 0.85                         | 0.60     | 1.40                                  |
| CDRH3D23NP-150MC | J     | $15.0 \pm 20\%$                         | 191(154)                                         | 0.70                         | 0.50     | 0.85                                  |
| CDRH3D23NP-220MC | K     | $22.0 \pm 20\%$                         | 270(219)                                         | 0.55                         | 0.40     | 0.75                                  |
| CDRH3D23NP-330MC | L     | $33.0 \pm 20\%$                         | 381(307)                                         | 0.50                         | 0.35     | 0.60                                  |
| CDRH3D23NP-470MC | M     | $47.0 \pm 20\%$                         | 546(441)                                         | 0.35                         | 0.25     | 0.55                                  |

※1. Inductance measuring condition: at 100kHz.

※2. Saturation current: The value of D.C. current when the inductance decreases to 65% of it's nominal value.


※3. Temperature rise current: The value of D.C. current when the temperature rise is  $\Delta t = 40^\circ\text{C}$  ( $T_a = 20^\circ\text{C}$ ).

# SMD Power Inductor CDRH3D23



## Saturation Current & Temperature Rise Graph

— L (20°C) — L (100°C) —  $\Delta T$





# SMD Power Inductor CDRH3D23




## Saturation Current & Temperature Rise Graph

— L (20°C) — L (100°C) —  $\Delta T$




## Solder Reflow Condition

**Heat Endurance**



**Temperature Chart**



Please refer to the sales offices on our website - <http://www.sumida.com>

### Hong Kong

Tel.+852-2880-6781  
FAX.+852-2565-9600  
[sales@hk.sumida.com](mailto:sales@hk.sumida.com)

### Saitama(Japan)

Tel.+81-48-691-7300  
FAX.+81-48-691-7340  
[sales@jp.sumida.com](mailto:sales@jp.sumida.com)

### Chicago

Tel.+1-847-545-6700  
FAX. +1-847-545-6720  
[sales@us.sumida.com](mailto:sales@us.sumida.com)

### Shanghai

Tel.+86-21-5836-3299  
FAX.+86-21-5836-3266  
[shanghai.sales@cn.sumida.com](mailto:shanghai.sales@cn.sumida.com)

### Seoul

Tel.+82-2-6237-0777  
FAX.+82-2-6237-0778  
[sales@kr.sumida.com](mailto:sales@kr.sumida.com)

### Obernzell

Tel.+49-8591-937-0  
FAX. +49-8591-937-103  
[contact@eu.sumida.com](mailto:contact@eu.sumida.com)

### Shenzhen

Tel.+86-755-8291-0228  
FAX.+86-755-8291-0338  
[shenzhen.sales@cn.sumida.com](mailto:shenzhen.sales@cn.sumida.com)

### Singapore

Tel.+65-6296-3388  
FAX.+65-6841-4426  
[sales@sg.sumida.com](mailto:sales@sg.sumida.com)

### Neumarkt

Tel.+49-9181-4509-110  
FAX. +49-9181-4509-310  
[infocomp@eu.sumida.com](mailto:infocomp@eu.sumida.com)

### Taipei

Tel.+886-2-8751-2737  
FAX.+886-2-8751-2738  
[sales@tw.sumida.com](mailto:sales@tw.sumida.com)

### San Jose

Tel.+1-408-321-9660  
FAX.+1-408-321-9308  
[sales@us.sumida.com](mailto:sales@us.sumida.com)