

UNR4121/4122/4123/4124/412X/412Y

(UN4121/4122/4123/4124/412X/412Y)

Silicon PNP epitaxial planer transistor

For digital circuits

Features


- Costs can be reduced through downsizing of the equipment and reduction of the number of parts.
- New S type package, allowing supply with the radial taping.

Resistance by Part Number


	(R ₁)	(R ₂)
• UNR4121	2.2kΩ	2.2kΩ
• UNR4122	4.7kΩ	4.7kΩ
• UNR4123	10kΩ	10kΩ
• UNR4124	2.2kΩ	10kΩ
• UNR412X	0.27kΩ	5.0kΩ
• UNR412Y	3.1kΩ	4.6kΩ

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Ratings	Unit
Collector to base voltage	V _{CBO}	-50	V
Collector to emitter voltage	V _{CEO}	-50	V
Collector current	I _C	-500	mA
Total power dissipation	P _T	300	mW
Junction temperature	T _j	150	°C
Storage temperature	T _{stg}	-55 to +150	°C



Internal Connection




Note.) The Part numbers in the Parenthesis show conventional part number.







■ Electrical Characteristics (Ta=25°C)

Parameter		Symbol	Conditions	min	typ	max	Unit	
Collector cutoff current		I _{CBO}	V _{CB} = -50V, I _E = 0			-1	μA	
		UNR412X I _{CBO}	V _{CB} = -50V, I _E = 0			- 0.1		
Collector cutoff current		I _{CEO}	V _{CE} = -50V, I _B = 0			-1	μA	
		UNR412X I _{CEO}	V _{CE} = -50V, I _B = 0			- 0.5		
Emitter cutoff current	UNR4121	I _{EBO}	V _{EB} = -6V, I _C = 0			-5	mA	
	UNR4122/412X/412Y					-2		
	UNR4123/4124					-1		
Collector to base voltage		V _{CBO}	I _C = -10μA, I _E = 0	-50			V	
Collector to emitter voltage		V _{CEO}	I _C = -2mA, I _B = 0	-50			V	
Forward current transfer ratio	UNR4121	h _{FE}	V _{CE} = -10V, I _C = -100mA	40				
	UNR4122/412Y			50				
	UNR4123/4124			60				
	UNR412X			20				
Collector to emitter saturation voltage		V _{CE(sat)}	I _C = -100mA, I _B = -5mA			- 0.25	V	
		UNR412X V _{CE(sat)}	I _C = -10mA, I _B = - 0.3mA			- 0.25		
		UNR412Y V _{CE(sat)}	I _C = -50mA, I _B = -5mA			- 0.15		
Output voltage high level		V _{OH}	V _{CC} = -5V, V _B = - 0.5V, R _L = 500Ω	-4.9			V	
Output voltage low level		V _{OL}	V _{CC} = -5V, V _B = -3.5V, R _L = 500Ω			- 0.2	V	
Transition frequency		f _T	V _{CB} = -10V, I _E = 50mA, f = 200MHz		80		MHz	
Input resistance	UNR4121/4124	R _I		(-30%)	2.2	(+30%)	kΩ	
	UNR4122				4.7			
	UNR4123				10			
	UNR412X				0.27			
	UNR412Y				3.1			
Resistance ratio		R _I /R ₂		0.8	1.0	1.2		
					0.17	0.22		0.27
					0.043	0.054		0.065
						0.67		




Common characteristics chart






Characteristics charts of UNR4121









Characteristics charts of UNR4122







Characteristics charts of UNR4123





Characteristics charts of UNR4124








Characteristics charts of UNR412X





Characteristics charts of UNR412Y



Request for your special attention and precautions in using the technical information and semiconductors described in this material

- (1) An export permit needs to be obtained from the competent authorities of the Japanese Government if any of the products or technologies described in this material and controlled under the "Foreign Exchange and Foreign Trade Law" is to be exported or taken out of Japan.
- (2) The technical information described in this material is limited to showing representative characteristics and applied circuit examples of the products. It does not constitute the warranting of industrial property, the granting of relative rights, or the granting of any license.
- (3) The products described in this material are intended to be used for standard applications or general electronic equipment (such as office equipment, communications equipment, measuring instruments and household appliances).
Consult our sales staff in advance for information on the following applications:
 - Special applications (such as for airplanes, aerospace, automobiles, traffic control equipment, combustion equipment, life support systems and safety devices) in which exceptional quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or harm the human body.
 - Any applications other than the standard applications intended.
- (4) The products and product specifications described in this material are subject to change without notice for reasons of modification and/or improvement. At the final stage of your design, purchasing, or use of the products, therefore, ask for the most up-to-date Product Standards in advance to make sure that the latest specifications satisfy your requirements.
- (5) When designing your equipment, comply with the guaranteed values, in particular those of maximum rating, the range of operating power supply voltage and heat radiation characteristics. Otherwise, we will not be liable for any defect which may arise later in your equipment.
Even when the products are used within the guaranteed values, redundant design is recommended, so that such equipment may not violate relevant laws or regulations because of the function of our products.
- (6) When using products for which dry packing is required, observe the conditions (including shelf life and after-unpacking standby time) agreed upon when specification sheets are individually exchanged.
- (7) No part of this material may be reprinted or reproduced by any means without written permission from our company.

Please read the following notes before using the datasheets

- A. These materials are intended as a reference to assist customers with the selection of Panasonic semiconductor products best suited to their applications.
Due to modification or other reasons, any information contained in this material, such as available product types, technical data, and so on, is subject to change without notice.
Customers are advised to contact our semiconductor sales office and obtain the latest information before starting precise technical research and/or purchasing activities.
- B. Panasonic is endeavoring to continually improve the quality and reliability of these materials but there is always the possibility that further rectifications will be required in the future. Therefore, Panasonic will not assume any liability for any damages arising from any errors etc. that may appear in this material.
- C. These materials are solely intended for a customer's individual use.
Therefore, without the prior written approval of Panasonic, any other use such as reproducing, selling, or distributing this material to a third party, via the Internet or in any other way, is prohibited.