

PANDUIT PART NO. **	PANEL THICKNESS	A	B	C	D	E REF.	F * REF	G * REF
GE_36F-C	TO 0.036 (0.91)	0.025 (0.64)	0.045 (1.14)	0.087 (2.21)	0.030 (0.76)	0.106 (2.69)	.060	0.150 (3.81)
GE_62F-C	0.036 - 0.062 (0.91)-(1.57)	0.035 (0.89)	0.070 (1.78)	0.130 (3.30)	0.030 (0.76)	0.131 (3.33)	.105	0.150 (3.81)
GE_99F-C	0.062 - 0.099 (1.57)-(2.51)	0.054 (1.37)	0.108 (2.74)	0.155 (3.94)	0.030 (0.76)	0.169 (4.29)	.125	0.150 (3.81)
GE_144F-C	0.099 - 0.144 (2.51)-(3.66)	0.090 (2.29)	0.152 (3.86)	0.182 (4.66)	0.030 (0.76)	0.213 (5.41)	.160	0.150 (3.81)
GE_189F-C	0.144 - 0.189 (3.66)-(4.80)	0.12 (3.21)	0.206 (5.23)	0.255 (6.48)	0.046 (1.17)	0.297 (7.55)	—	—

The diagram illustrates the geometry of a tapered roller bearing. The dimensions are defined as follows:

- A**: Addendum, the radial distance from the addendum circle to the pitch circle.
- B**: Pitch diameter, the diameter of the pitch circle.
- C**: Outside diameter, the total outer diameter of the bearing.
- D**: Root diameter, the diameter of the fillet at the base of the bearing.
- E**: Bore diameter, the inner diameter of the bearing.
- F**: Fillet radius, the radius of the fillet at the base of the bearing.

SOLID WALL

SLOTTED WALL

G

- 3) SEE CURRENT PRICE SHEET FOR PART NO. SUFFIX DESIGNATION FOR PACKAGE SIZE.
- 4) COLOR: a) NATURAL
b) -0 AFTER PART NO. DENOTES WEATHER RESISTANT BLACK
- 5) SLOTTED WALL STYLE IS RECOMMENDED FOR INSIDE EDGE OF PANEL CUT OUTS.
SOLID WALL STYLE IS RECOMMENDED FOR STRAIGHT, OUTSIDE EDGES.

G00239FU_DC_03A.PRT

PANDUIT

CORP. TINLEY PARK, ILLINOIS

CONTINUOUS ROLL GROMMET EDGING

[illegible]