



MBRS2535CT THRU MBRS2560CT

30.0 AMPS. Schottky Barrier Rectifiers



Voltage Range
35 to 60 Volts
Current
30.0 Amperes


Features

- ✧ For surface mounted application
- ✧ Plastic material used carries Underwriters Laboratory Classifications 94V-0
- ✧ Metal silicon junction, majority carrier conduction
- ✧ Low power loss, high efficiency
- ✧ High current capability, low forward voltage drop
- ✧ High surge capability
- ✧ For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications
- ✧ Guardring for overvoltage protection
- ✧ High temperature soldering guaranteed:
260°C/10 seconds at terminals

Mechanical Data

- ✧ Cases: JEDEC D²PAK molded plastic
- ✧ Terminals: Leads solderable per MIL-STD-750, Method 2026
- ✧ Polarity: As marked
- ✧ Mounting position: Any
- ✧ Mounting torque: 5 in. - lbs. max
- ✧ Weight: 0.06 ounce, 1.70 grams

D²PAK



PIN 1 PIN 3 CASE P/N 4
Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	MBRS 2535CT	MBRS 2545CT	MBRS 2550CT	MBRS 2560CT	Units
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	35	45	50	60	V
Maximum RMS Voltage	V _{RMS}	24	31	35	42	V
Maximum DC Blocking Voltage	V _{DC}	35	45	50	60	V
Maximum Average Forward Rectified Current at T _C =130°C	I _(AV)	30				A
Peak Repetitive Forward Current (Rated V _R , Square Wave, 20KHz) at T _C =130°C	I _{FRM}	30.0				A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I _{FSM}	150				A
Peak Repetitive Reverse Surge Current (Note 1)	I _{RRM}	1.0		0.5		A
Maximum Instantaneous Forward Voltage at (Note 2) I _F =15A, T _C =25°C I _F =15A, T _C =125°C I _F =30A, T _C =25°C I _F =30A, T _C =125°C	V _F	0.82 0.73 — —	0.75 0.65 — —		V	
Maximum Instantaneous Reverse Current @ T _C =25°C at Rated DC Blocking Voltage Per Leg @ T _C =125°C (Note 2)	I _R	0.2 40.0	1.0 50.0		mA mA	
Voltage Rate of Change, (Rated V _R)	dV/dt	1,000				V/μS
Maximum Thermal Resistance Per Leg (Note 3)	R θ JC	1.0				°C/W
Operating Junction Temperature Range	T _J	-65 to +150				°C
Storage Temperature Range	T _{STG}	-65 to +175				°C

Notes: 1. 2.0us Pulse Width, $f=1.0$ KHz

2. Pulse Test: 300us Pulse Width, 1% Duty Cycle

3. Thermal Resistance from Junction to Case Per Leg

RATINGS AND CHARACTERISTIC CURVES (MBRS2535CT THRU MBRS2560CT)

FIG.1- FORWARD CURRENT DERATING CURVE




FIG.2- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT PER LEG




FIG.3- TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS PER LEG




FIG.4- TYPICAL REVERSE CHARACTERISTICS PER LEG




FIG.5- TYPICAL JUNCTION CAPACITANCE PER LEG




FIG.6- TYPICAL TRANSIENT THERMAL IMPEDANCE PER LEG

