


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/6/10	D.GRIFFIN

DESCRIPTION	MATERIAL	PLATING
BODY 1	BRASS	NICKEL
BODY 2	BRASS	NICKEL
DIELECTRIC	TEFLON	-
CENTER PIN 1	BRASS	GOLD
CENTER PIN 2	BRASS	GOLD
RETAINING RING	BRASS	NICKEL
GASKET	RUBBER	-
PRESS FIT GROUND RING	BRASS	NICKEL
SHELL	BRASS	NICKEL
STAMP WASHER	BRASS	NICKEL



NOTES:

ELECTRICAL:

IMPEDANCE: 50 OHMS
DIELECTRIC WITHSTAND VOLTAGE: 2500 VOLTS PEAK
FREQUENCY RANGE: DC ~ 11 GHz
INSERTION LOSS: .15 dB MAX.
VOLTAGE RATING: 1500 V PEAK

MISCELLANEOUS:

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC PS-0031.

ALL DIMENSIONS ARE FOR REFERENCE ONLY

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005 PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D. CASTRO	4/6/10		
	CHECKED BY K. BURGNER	4/6/10	CATEGORY COAXIAL	
	APPROVED BY K. BURGNER	4/6/10	PRODUCT DESCRIPTION ADP,N-Male to N-Female R/Angle	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321	DWG. NO. AXA-NMNF90
COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: AXA-NMNF90.SLDDRW	REV. A
		SHEET 1 OF 1		