

DATA SHEET

74ALVCH16823

18-bit bus-interface D-type flip-flop
with reset and enable (3-State)

Product specification

1998 Jul 29

IC24 Data Handbook

18-bit D-type flip-flop (3-State)

74ALVCH16823

FEATURES

- Wide supply voltage range of 1.2V to 3.6V
- Complies with JEDEC standard no. 8-1A.
- CMOS low power consumption
- Direct interface with TTL levels
- Current drive ± 24 mA at 3.0 V
- Multibyte™flow-through standard pin-out architecture
- Low inductance multiple V_{CC} and GND pins to minimize noise and ground bounce
- All data inputs have bus hold
- Output drive capability 50Ω transmission lines @ 85°C

DESCRIPTION

The 74ALVCH16823 is a 18-bit edge-triggered flip-flop featuring separate D-type inputs for each flip-flop and 3-state outputs for bus oriented applications. Incorporates bushold data inputs which eliminate the need for external pull-up resistors to hold unused inputs. The 74ALVCH16823 consists of two sections of nine edge-triggered flip-flops. A clock (CP) input, an output-enable (\overline{OE}) input, a Master reset (\overline{MR}) input and a clock-enable (\overline{CE}) input are provided for each total 9-bit section.

With the clock-enable (\overline{CE}) input LOW, the D-type flip-flops will store the state of their individual D-inputs that meet the set-up and hold time requirements on the LOW-to-HIGH CP transition. Taking \overline{CE} HIGH disables the clock buffer, thus latching the outputs. Taking the Master reset (\overline{MR}) input LOW causes all the Q outputs to go LOW independently of the clock.

When \overline{OE} is LOW, the contents of the flip-flops are available at the outputs. When the \overline{OE} is HIGH, the outputs go to the high impedance OFF-state. Operation of the \overline{OE} input does not affect the state of flip-flops.

Active bus hold circuitry is provided to hold unused or floating data inputs at a valid logic level.

QUICK REFERENCE DATA

$GND = 0\text{V}$; $T_{amb} = 25^\circ\text{C}$; $t_r = t_f \leq 2.5\text{ns}$

SYMBOL	PARAMETER	CONDITIONS	TYPICAL	UNIT
t_{PHL}/t_{PLH}	Propagation delay CP to Q_n	$V_{CC} = 2.5\text{V}$, $CL = 30\text{pF}$ $V_{CC} = 3.3\text{V}$, $CL = 50\text{pF}$	2.1 2.1	ns
F_{max}	Maximum clock frequency	$V_{CC} = 2.5\text{V}$, $CL = 30\text{pF}$ $V_{CC} = 3.3\text{V}$, $CL = 50\text{pF}$	300 350	MHz
C_I	Input capacitance		5.0	pF
C_{PD}	Power dissipation capacitance per latch	$V_I = \text{GND to } V_{CC}^1$	Outputs enabled	16
			Outputs disabled	10

NOTES:

1. C_{PD} is used to determine the dynamic power dissipation (P_D in μW):

$$P_D = C_{PD} \times V_{CC}^2 \times f_i + \sum (C_L \times V_{CC}^2 \times f_o)$$
 where:
 f_i = input frequency in MHz; C_L = output load capacity in pF;
 f_o = output frequency in MHz; V_{CC} = supply voltage in V;
 $\sum (C_L \times V_{CC}^2 \times f_o)$ = sum of outputs.

ORDERING INFORMATION

PACKAGES	TEMPERATURE RANGE	OUTSIDE NORTH AMERICA	NORTH AMERICA	DWG NUMBER
56-Pin Plastic SSOP Type II	-40°C to +85°C	74ALVCH16823 DL	ACH16823 DL	SOT371-1
56-Pin Plastic TSSOP Type II	-40°C to +85°C	74ALVCH16823 DGG	ACH16823 DGG	SOT364-1


18-bit D-type flip-flop (3-State)

74ALVCH16823


PIN DESCRIPTION

PIN NUMBER	SYMBOL	FUNCTION
2, 27	1 \overline{OE} , 2 \overline{OE}	Output enable input (active-Low)
54, 52, 51, 49, 48, 47, 45, 44, 43 42, 41, 40, 38, 37, 36, 34, 33, 31	1D0-1D8 2D0-2D8	Data inputs
3, 5, 6, 8, 9, 10, 12, 13, 14 15, 16, 17, 19, 20, 21, 23, 24, 26	1Q0-1Q8 2Q0-2Q8	Data outputs
56, 29	1CP, 2CP	Clock pulse input (active rising edge)
55, 30	1 \overline{CE} , 2 \overline{CE}	Clock enable input (active-Low)
1, 28	1MR, 2MR	Master reset input (active-Low)
4, 11, 18, 25, 32, 39, 46, 53	GND	Ground (0V)
7, 22, 35, 50	V _{CC}	Positive supply voltage

PIN CONFIGURATION




LOGIC SYMBOL




18-bit D-type flip-flop (3-State)

74ALVCH16823


LOGIC SYMBOL (IEEE/IEC)



BUS HOLD CIRCUIT



LOGIC DIAGRAM



18-bit D-type flip-flop (3-State)

74ALVCH16823

FUNCTION TABLE

INPUTS					OUTPUT	OPERATING MODES
nOE	nMR	nCE	nCP	nDx	nQx	
L	L	X	X	X	L	Clear
L	H	L	↑	h	H	Load and read data
L	H	L	↑	I	L	
L	H	L	L	X	Q ₀	Hold
L	H	H	X	X	Q ₀	
H	X	X	X	X	Z	Disable outputs

H = HIGH voltage level

h = HIGH voltage level one set-up time prior to the Low-to-High clock transition

L = LOW voltage level

I = LOW voltage level one set-up time prior to the Low-to-High clock transition

X = Don't care

Z = HIGH impedance "off" state

↑ = LOW to High clock transition

RECOMMENDED OPERATING CONDITIONS

SYMBOL	PARAMETER	CONDITIONS	LIMITS		UNIT
			MIN	MAX	
V _{CC}	DC supply voltage 2.5V range (for max. speed performance @ 30 pF output load)		2.3	2.7	V
	DC supply voltage 3.3V range (for max. speed performance @ 50 pF output load)		3.0	3.6	
V _{CC}	DC supply voltage (for low-voltage applications)		1.2	3.6	V
V _I	DC Input voltage range	for data input pins	0	V _{CC}	V
		for control pins	0	5.5	V
V _O	DC output voltage range		0	V _{CC}	V
T _{amb}	Operating free-air temperature range		-40	+85	°C
t _r , t _f	Input rise and fall times	V _{CC} = 2.3 to 3.0V V _{CC} = 3.0 to 3.6V	0 0	20 10	ns/V

ABSOLUTE MAXIMUM RATINGS

In accordance with the Absolute Maximum Rating System (IEC 134). Voltages are referenced to GND (ground = 0V).

SYMBOL	PARAMETER	CONDITIONS	RATING	UNIT
V _{CC}	DC supply voltage		-0.5 to +4.6	V
I _{IK}	DC input diode current	V _I < 0	-50	mA
V _I	DC input voltage	For control pins ¹	-0.5 to +5.5	V
		For data inputs ¹	-0.5 to V _{CC} +0.5	
I _{OK}	DC output diode current	V _O > V _{CC} or V _O < 0	±50	mA
V _O	DC output voltage	Note 1	-0.5 to V _{CC} +0.5	V
I _O	DC output source or sink current	V _O = 0 to V _{CC}	±50	mA
I _{GND} , I _{CC}	DC V _{CC} or GND current		±100	mA
T _{stg}	Storage temperature range		-65 to +150	°C
P _{TOT}	Power dissipation per package -plastic medium-shrink (SSOP) -plastic thin-medium-shrink (TSSOP)	For temperature range: -40 to +125 °C above +55°C derate linearly with 11.3 mW/K above +55°C derate linearly with 8 mW/K	850 600	mW

NOTE:

1. The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

18-bit D-type flip-flop (3-State)

74ALVCH16823

DC ELECTRICAL CHARACTERISTICS

Over recommended operating conditions. Voltage are referenced to GND (ground = 0 V).

SYMBOL	PARAMETER	TEST CONDITIONS	LIMITS			UNIT	
			Temp = -40°C to +85°C				
			MIN	TYP ¹	MAX		
V _{IH}	HIGH level Input voltage	V _{CC} = 1.2V	V _{CC}			V	
		V _{CC} = 1.8V	0.7*V _{CC}	0.9			
		V _{CC} = 2.3 to 2.7V	1.7	1.2			
		V _{CC} = 2.7 to 3.6V	2.0	1.5			
V _{IL}	LOW level Input voltage	V _{CC} = 1.2V		–	GND	V	
		V _{CC} = 1.8V		0.9	0.2*V _{CC}		
		V _{CC} = 2.3 to 2.7V		1.2	0.7		
		V _{CC} = 2.7 to 3.6V		1.5	0.8		
V _{OH}	HIGH level output voltage	V _{CC} = 1.8 to 3.6V; V _I = V _{IH} or V _{IL} ; I _O = -100µA	V _{CC} -0.2	V _{CC}	–	V	
		V _{CC} = 1.8V; V _I = V _{IH} or V _{IL} ; I _O = -6mA	V _{CC} -0.4	V _{CC} -0.10	–		
		V _{CC} = 2.3V; V _I = V _{IH} or V _{IL} ; I _O = -6mA	V _{CC} -0.3	V _{CC} -0.08	–		
		V _{CC} = 2.3V; V _I = V _{IH} or V _{IL} ; I _O = -12mA	V _{CC} -0.5	V _{CC} -0.17	–		
		V _{CC} = 2.3V; V _I = V _{IH} or V _{IL} ; I _O = -18mA	V _{CC} -0.6	V _{CC} -0.26	–		
		V _{CC} = 2.7V; V _I = V _{IH} or V _{IL} ; I _O = -12mA	V _{CC} -0.5	V _{CC} -0.14	–		
		V _{CC} = 3.0V; V _I = V _{IH} or V _{IL} ; I _O = -24mA	V _{CC} -1.0	V _{CC} -0.28	–		
V _{OL}	LOW level output voltage	V _{CC} = 1.8 to 3.6V; V _I = V _{IH} or V _{IL} ; I _O = 100µA		GND	0.20	V	
		V _{CC} = 1.8V; V _I = V _{IH} or V _{IL} ; I _O = 6mA		0.09	0.30		
		V _{CC} = 2.3V; V _I = V _{IH} or V _{IL} ; I _O = 6mA		0.07	0.20		
		V _{CC} = 2.3V; V _I = V _{IH} or V _{IL} ; I _O = 12mA		0.15	0.40		
		V _{CC} = 2.3V; V _I = V _{IH} or V _{IL} ; I _O = 18mA		0.23	0.60		
		V _{CC} = 2.7V; V _I = V _{IH} or V _{IL} ; I _O = 12mA		0.14	0.40		
		V _{CC} = 3.0V; V _I = V _{IH} or V _{IL} ; I _O = 24mA		0.27	0.55		
I _I	Input leakage current per control pin	V _{CC} = 1.8 to 3.6V; V _I = 5.5V or GND		0.1	5	µA	
	Input leakage current per data pin	V _{CC} = 1.8 to 3.6V; V _I = V _{CC} or GND		0.1	5		
I _{IHZ} /I _{ILZ}	Input current for common I/O pins	V _{CC} = 1.8 to 2.7V; V _I = V _{CC} or GND		0.1	10	µA	
		V _{CC} = 3.6V; V _I = V _{CC} or GND		0.1	15		
I _{OZ}	3-State output OFF-state current	V _{CC} = 1.8 to 2.7V; V _I = V _{IH} or V _{IL} ; V _O = V _{CC} or GND		0.1	5	µA	
		V _{CC} = 2.7 to 3.6V; V _I = V _{IH} or V _{IL} ; V _O = V _{CC} or GND		0.1	10		
ΔI _{CC}	Additional quiescent supply current given per data I/O pin	V _{CC} = 2.7V to 3.6V; V _I = V _{CC} - 0.6V; I _O = 0		150	750	µA	
I _{BHL}	Bus hold LOW sustaining current	V _{CC} = 2.3V; V _I = 0.7V ²	45	–		µA	
		V _{CC} = 3.0V; V _I = 0.8V ²	75	150			
I _{BHH}	Bus hold HIGH sustaining current	V _{CC} = 2.3V; V _I = 1.7V ²	-45			µA	
		V _{CC} = 3.0V; V _I = 2.0V ²	-75	-175			
I _{BHLO}	Bus hold LOW overdrive current	V _{CC} = 2.7V ²	300			µA	
		V _{CC} = 3.6V ²	450				
I _{BHHO}	Bus hold HIGH overdrive current	V _{CC} = 2.7V ²	-300			µA	
		V _{CC} = 3.6V ²	-450				

NOTES:

1. All typical values are at T_{amb} = 25°C.
2. Valid for data inputs of bus hold parts.

18-bit D-type flip-flop (3-State)

74ALVCH16823

AC CHARACTERISTICS FOR $V_{CC} = 2.3V$ TO $2.7V$ RANGE AND $V_{CC} < 2.3V$ GND = 0V; $t_r = t_f \leq 2.0\text{ns}$; $C_L = 30\text{pF}$

SYMBOL	PARAMETER	WAVEFORM	LIMITS						UNIT	
			$V_{CC} = 2.3$ to $2.7V$			$V_{CC} = 1.8V$				
			MIN	TYP ^{1, 2}	MAX	MIN	TYP1	MAX		
t_{PLH}/t_{PHL}	Propagation delay nCP to nQ _n	1, 5	1.0	2.8	4.9	1.5	4.5	7.5	10.6	ns
t_{PLH}/t_{PHL}	Propagation delay nMR to nQ _n	2, 5	1.0	2.9	5.0	1.5	4.6	7.4	9.9	ns
t_{PZH}/t_{PZL}	3-State output enable time nOE _n to nQ _n	4, 5	1.0	2.8	5.3	1.5	4.4	7.7	10.4	ns
t_{PHZ}/t_{PLZ}	3-State output disable time nOE _n to nQ _n	4, 5	1.0	2.2	4.1	1.5	3.3	5.5	6.7	ns
t_W	nCP pulse width	1, 5	3.0	1.6		4.0	2.0			ns
	nMR pulse width, LOW	3, 5	3.0	0.4		4.0	0.8			
t_{SU}	Set up time nD _n to nCP	3, 5	1.2	0.2		1.5	0.2			ns
	Set up time nCE to nCP		1.8	-0.2		2.0	-0.2			
t_h	Hold time nD _n to nCP	3, 5	0.8	-0.1		0.6	-0.2			ns
	Hold time nCE to nCP		0.3	0.2		0.3	0.2			
t_{rec}	Recovery time nMR to nCP	2, 5	1.0	0.3		0.8	0.2			ns
F_{max}	Maximum clock pulse frequency	1, 5	150	300		125	250			MHz

NOTE:

1. All typical values are measured at $T_{amb} = 25^\circ\text{C}$.2. Typical value is measured at $V_{CC} = 2.5V$.AC CHARACTERISTICS FOR $V_{CC} = 3.0V$ TO $3.6V$ RANGE AND $V_{CC} = 2.7V$ GND = 0V; $t_r = t_f \leq 2.5\text{ns}$; $C_L = 50\text{pF}$

SYMBOL	PARAMETER	WAVEFORM	LIMITS						UNIT	
			$V_{CC} = 3.0 \pm 0.3V$			$V_{CC} = 2.7V$				
			MIN	TYP ^{1, 2}	MAX	MIN	TYP1	MAX		
t_{PLH}/t_{PHL}	Propagation delay nCP to nQ _n	1, 5	1.0	2.5	3.7	1.0	2.7	4.3	ns	
t_{PLH}/t_{PHL}	Propagation delay nMR to nQ _n	2, 5	1.0	2.6	4.0	1.0	3.1	4.6	ns	
t_{PZH}/t_{PZL}	3-State output enable time nOE _n to nQ _n	4, 5	1.0	2.5	4.3	1.0	3.1	5.2	ns	
t_{PHZ}/t_{PLZ}	3-State output disable time nOE _n to nQ _n	4, 5	1.0	2.8	3.9	1.0	3.1	4.3	ns	
t_W	nCP pulse width HIGH or LOW	1, 5	2.5	1.4		3.0	1.6		ns	
	nMR pulse width HIGH or LOW	3, 5	2.5	0.3		3.0	0.6			
t_{SU}	Set up time nD _n to nCP	3, 5	1.2	0.2		1.5	0.4		ns	
	Set up time nCE to nCP		1.5	-0.1		1.9	-0.1			
t_h	Hold time nD _n to nCP	3, 5	0.8	0.0		0.6	-0.2		ns	
	Hold time nCE to nCP		0.5	0.1		0.4	0.1			
t_{rec}	Recovery time nMR to nCP	2, 5	1.0	0.2		0.8	0.1		ns	
F_{max}	Maximum clock pulse frequency	1, 5	200	350		150	300		MHz	

NOTES:

1. All typical values are measured at $T_{amb} = 25^\circ\text{C}$.2. Typical value is measured at $V_{CC} = 3.3V$.

18-bit D-type flip-flop (3-State)

74ALVCH16823

AC WAVEFORMS FOR $V_{CC} = 2.3V$ TO $2.7V$ AND $V_{CC} < 2.3V$ RANGE

$V_M = 0.5 V_{CC}$

$V_X = V_{OL} + 0.15V$

$V_Y = V_{OH} - 0.15V$

 V_{OL} and V_{OH} are the typical output voltage drop that occur with the output load.

$V_I = V_{CC}$

AC WAVEFORMS FOR $V_{CC} = 3.0V$ TO $3.6V$ AND $V_{CC} = 2.7V$ RANGE


$V_M = 1.5 V$

$V_X = V_{OL} + 0.3V$


$V_Y = V_{OH} - 0.3V$

 V_{OL} and V_{OH} are the typical output voltage drop that occur with the output load.



$V_I = 2.7V$



Waveform 1. Clock (nCP) to Output (nQn) Propagation Delays, Clock Pulse Width, and Maximum Clock Pulse Frequency




Waveform 2. Master Reset (MR) Pulse Width, MR to Output propagation Delay and MR to Clock Recovery Time

Waveform 3. Data Setup and Hold Times for the D_n or \overline{CE} input to the CP input

Waveform 4. 3-State Enable and Disable Times

TEST CIRCUIT



Test Circuit for 3-State Outputs

SWITCH POSITION

TEST	SWITCH
t_{PLH}/t_{PHL}	Open
t_{PLZ}/t_{PZL}	$2 * V_{CC}$
t_{PHZ}/t_{PZH}	GND

V_{CC}	V_{IN}
$< 2.7V$	V_{CC}
$2.7 - 3.6V$	$2.7V$

DEFINITIONS

 R_L = Load resistor C_L = Load capacitance includes jig and probe capacitance R_T = Termination resistance should be equal to Z_{OUT} of pulse generators.


Waveform 5. Load circuitry for switching times

18-bit bus-interface D-type flip-flop with reset and enable (3-State)

74ALVCH16823

SSOP56: plastic shrink small outline package; 56 leads; body width 7.5 mm

SOT371-1



DIMENSIONS (mm are the original dimensions)

UNIT	A max.	A ₁	A ₂	A ₃	b _p	c	D ⁽¹⁾	E ⁽¹⁾	e	H _E	L	L _p	Q	v	w	y	Z ⁽¹⁾	θ
mm	2.8 0.2	0.4 0.2	2.35 2.20	0.25	0.3 0.2	0.22 0.13	18.55 18.30	7.6 7.4	0.635	10.4 10.1	1.4	1.0 0.6	1.2 1.0	0.25	0.18	0.1	0.85 0.40	8° 0°

Note

1. Plastic or metal protrusions of 0.25 mm maximum per side are not included.


OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	EIAJ			
SOT371-1		MO-118AB				93-11-02 95-02-04

18-bit bus-interface D-type flip-flop with reset and enable (3-State)

74ALVCH16823

TSSOP56: plastic thin shrink small outline package; 56 leads; body width 6.1mm

SOT364-1



DIMENSIONS (mm are the original dimensions).

UNIT	A max.	A ₁	A ₂	A ₃	b _p	c	D ⁽¹⁾	E ⁽²⁾	e	H _E	L	L _p	Q	v	w	y	z	θ
mm	1.2 0.05	0.15 0.85	1.05	0.25	0.28 0.17	0.2 0.1	14.1 13.9	6.2 6.0	0.5	8.3 7.9	1.0	0.8 0.4	0.50 0.35	0.25	0.08	0.1	0.5 0.1	8° 0°

Notes

1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.
2. Plastic interlead protrusions of 0.25 mm maximum per side are not included.

OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	EIAJ			
SOT364-1		MO-153EE				-93-02-03 95-02-10

18-bit bus-interface D-type flip-flop
with reset and enable (3-State)

74ALVCH16823

NOTES

18-bit bus-interface D-type flip-flop with reset and enable (3-State)

74ALVCH16823

Data sheet status

Data sheet status	Product status	Definition [1]
Objective specification	Development	This data sheet contains the design target or goal specifications for product development. Specification may change in any manner without notice.
Preliminary specification	Qualification	This data sheet contains preliminary data, and supplementary data will be published at a later date. Philips Semiconductors reserves the right to make changes at any time without notice in order to improve design and supply the best possible product.
Product specification	Production	This data sheet contains final specifications. Philips Semiconductors reserves the right to make changes at any time without notice in order to improve design and supply the best possible product.

[1] Please consult the most recently issued datasheet before initiating or completing a design.

Definitions

Short-form specification — The data in a short-form specification is extracted from a full data sheet with the same type number and title. For detailed information see the relevant data sheet or data handbook.

Limiting values definition — Limiting values given are in accordance with the Absolute Maximum Rating System (IEC 134). Stress above one or more of the limiting values may cause permanent damage to the device. These are stress ratings only and operation of the device at these or at any other conditions above those given in the Characteristics sections of the specification is not implied. Exposure to limiting values for extended periods may affect device reliability.

Application information — Applications that are described herein for any of these products are for illustrative purposes only. Philips Semiconductors make no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Disclaimers

Life support — These products are not designed for use in life support appliances, devices or systems where malfunction of these products can reasonably be expected to result in personal injury. Philips Semiconductors customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Philips Semiconductors for any damages resulting from such application.

Right to make changes — Philips Semiconductors reserves the right to make changes, without notice, in the products, including circuits, standard cells, and/or software, described or contained herein in order to improve design and/or performance. Philips Semiconductors assumes no responsibility or liability for the use of any of these products, conveys no license or title under any patent, copyright, or mask work right to these products, and makes no representations or warranties that these products are free from patent, copyright, or mask work right infringement, unless otherwise specified.

Philips Semiconductors
811 East Arques Avenue
P.O. Box 3409
Sunnyvale, California 94088-3409
Telephone 800-234-7381

© Copyright Philips Electronics North America Corporation 1998
All rights reserved. Printed in U.S.A.

print code

Document order number:

Date of release: 05-96

9397-750-04554

Let's make things better.

Philips
Semiconductors



PHILIPS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NXP](#):

[74ALVCH16823DG](#) [74ALVCH16823DG-T](#) [74ALVCH16823DL](#)