


LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				F	REV PER 063A-0236-99	250CT99	JR/TM



AMP
WIRE RANGE

2 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]

- NOTE:
- 1 STAMP AMP 2* LOCATE APPROX AS SHOWN
 - 2. TONGUE MATERIAL THK 1.45±0.08[.057±.003]
 - 3. WIRE INSULATION DIA 14.22[.560] MAX
- 9.91±0.13 [.390±.005] DIA
(FOR 3/8 STUD)

OBSOLETE	50	LOOSE PC, BOX 8-53953-2	
	50	LOOSE PC	53953-1
	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 150°c		DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20[.008] 3 PLC DEC ± - ANGLES ± -		DR 10-6-93 S.S. GOULDEN		AMP AMP Incorporated Harrisburg, PA 17105-3608		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600 V MAX		CHK 10-6-93 R. HERSEY					
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 26.65-42.41mm² [52,600-83,700] STRANDED		MATERIAL COPPER PER ASTM B-152 PVF², COLOR:NATURAL		APPD 10-6-93 B. BARE		NAME TERMINAL, RING TONGUE, PVF², PLASTI-GRIP, WIRE SIZE:2 AWG	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		FINISH TIN/LEAD (93-7) PLATE PER ASTM B545		APPD 10-6-93 M. ELLIS			
						PRODUCT SPEC NOT AVAILABLE		APPLICATION SPEC NOT AVAILABLE			
						WEIGHT -		SCALE NTS			
								SIZE B		CAGE CODE 00779	
										DRAWING NO C-53953	
										SHEET 1 OF 1	