

REVISION CI


DO NOT SCALE
THIS DRAWING

FIG 1

-LC: LOCKING CLIP OPTION
CLIPS N/A WITH -A OPTION.DIFFERENT AS SHOWN.
OTHERWISE SAME AS FIG 1.

$$\text{FOR EVEN: "A"} = \frac{(\text{NO. OF POS.} \times .100 [2.54]) - .300 [7.62]}{2} + .050 [1.27]$$

$$\text{FOR ODD: "A"} = \frac{(\text{NO. OF POS.} \times .100 [2.54]) - .300 [7.62]}{2}$$




TABLE 3

POS.	"E"
ODD	.150 [3.81]
EVEN	.100 [2.54]

FIG 3

-P: PICK & PLACE PAD
PLACE PPP-08 ON ϕ AS SHOWN

TABLE 2	
No OF POS	S/S BOW
02 - 10	.0030 [.080]
11 - 20	.0050 [.127]
21 - 30	.0070 [.178]
31 - 36	.0080 [.203]

PLATING SPECIFICATION

- T: MATTE TIN CONTACT AND TAIL
- S: 30 μ " SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- L: 10 μ " SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- F: 3 μ " FLASH SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- H: 30 μ " HEAVY GOLD IN CONTACT AREA, 3 μ " FLASH GOLD ON TAIL
- TL: TIN/LEAD (90/10+/-5) CONTACT AND TAIL
- STL: 30 μ " SELECTIVE GOLD, ON CONTACT, TIN/LEAD (90/10+/-5) TAIL
- SM: 30 μ " SELECTIVE GOLD, IN CONTACT AREA, MATTE TIN ON TAIL
- LM: 10 μ " LIGHT SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- FM: 3 μ " FLASH SELECTIVE GOLD, IN CONTACT AREA, MATTE TIN ON TAIL
- TM: MATTE TIN CONTACT AND TAIL
- SS: 30 μ " STRIPED SELECTIVE GOLD IN CONTACT, MATTE TIN ON TAIL (SEE NOTE 14)

ROW OPTION

- DH: DOUBLE HORIZONTAL (USE TSM-50-DHU)
- MT: MIXED TECHNOLOGY (SEE FIG. 4 & TABLE 1) (NOT AVAILABLE WITH -LC, -SL, -TR OR -A OPTIONS)

NOTES:

1. ϕ REPRESENTS A CRITICAL DIMENSION.
2. DELETED
3. DELETED
4. DELETED
5. .005 [0.13] MAX CUT FLASH.
6. .002 [0.51] MAX BURR. MUST BE AWAY FROM SMT BOARD SIDE.
7. DELETED
8. CUT TO POSITION BODIES TO BE MULTI-CUT OR ROTO-CUT ONLY. NEVER AIR CUT.
9. TUBE POSITIONS 5-36, BULK PACKAGE POSITIONS 2-4.
10. 3 LBS. MIN PUSHOUT FORCE.
11. -04 LEAD STYLE DOES NOT MATE WITH SSM-DH.
12. ORIENTATION OF PART IN TAPE AND REEL TO BE CONTROLLED BY POCKET DESIGN.
13. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.
14. -SS OPTION ONLY AVAILABLE IN LEAD STYLE -01 AND CAN ONLY MATE WITH SSW, SSO, SSM, ESW, ESQ AND BCS.

DIMENSIONS ARE IN INCHES		TOLERANCES ARE:		TITLE:		DWG NO:	
ONE PLACE DECIMALS $\pm .1$ [3]	THREE PLACE DECIMALS $\pm .005$ [.13]	ANGLES $\pm 2^\circ$		TERMINAL SRTIP DOUBLE SURFACE MOUNT		TSM-1XX-XX-XXX-XX-XX-XXX-XX	
TWO PLACE DECIMALS $\pm .01$ [.3]	FOUR PLACE DECIMALS $\pm .0020$ [.051]					SHEET 1 OF 3	

TSM-1XX-XX-XXX-XX-XX-XXX-XX

NO. OF POSITIONS
-02 THRU -36
LEAD STYLE
(SEE TABLE 1)

OPTION #3

- P: PICK & PLACE PAD, SEE FIG 3 (USE PPP-08) (AVAILABLE ON POS -05 THRU -36) (AVAILABLE ON POS -02 THRU -04 WITH -TR OPTION ONLY) (NOT AVAILABLE WITH -K OPTION)
- TR: TAPE & REEL (29 POS MAX) (AVAILABLE FOR -DH ONLY)
- K: POLYIMIDE FILM (SEE FIG 5, SHT 2) (NOT AVAILABLE WITH -P OPTION) (USE K-DOT-197-344-.005) (AVAILABLE ON POS -04 THRU -36) (AVAILABLE ON POS -02 THRU -03 WITH -TR OPTION ONLY)

OPTION #2

POLARIZED POSITION: SPECIFY OMITTED PIN

OPTION #1

- LC: LOCKING CLIP (USE LC-06-TM - SEE FIG. 1) (SEE NOTE 13) (03-36 POS USE 2 PER STRIP, 02 POS USE 1 PER STRIP) (USE TSM-XX-DHU) (NOT AVAILABLE WITH -A OR -SL OPTIONS) (USE TSM-XX-DHU)
- A: ALIGNMENT PIN (SEE FIG 2, SHT 3) (STAKED: 4 POS MIN) (MOLDED: 2 POS MIN) (NOT AVAILABLE WITH -LC OR -SL OPTIONS) (LEAVE BLANK FOR NO HOLD DOWN OPTION)
- SL: SOLDER LOCK (SEE FIG 6, SHT 2) (2 POSITION MINIMUM) (NOT AVAILABLE WITH -LC OR -A OPTIONS)

TABLE 1

ROW OPTION	LEAD STYLE	BOTTOM ROW PIN #1	TOP ROW PIN #2	"C"
-DH	-01	T-156-09-X-2	T-156-20-X-2	.230 [5.84]
-DH	-02	T-156-09-X-2	T-156-20-X-2	.320 [8.13]
-DH	-03	T-156-09-X-2	T-156-20-X-2	.420 [10.67]
-DH	-04 (SEE NOTE 11)	T-156-09-X-2	T-156-20-X-2	.120 [3.05]
-MT	-01	T-156-08-X-2	T-156-20-X-2	.230 [5.84]
-MT	-02	T-156-15-X-2	T-156-20-X-2	.320 [8.13]
-MT	-03	T-156-09-X-2	T-156-20-X-2	.420 [10.67]

MISC\MKTG

TSM-1XX-XX-XXX-XX-XX-XXX-XX-MKT1

MATERIAL:
INSULATOR:
LCP, UL 94 VO
COLOR: BLACK
TERMINALS:
PHOSPHOR BRONZE

samtec
520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 844-6733 P.O. BOX 1147
CODE 55322

MADE BY:
BRATCHER 7-27-95TSM-1XX-XX-XXX-XX-XX-XXX-XX
SHEET 1 OF 3

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION THAT IS THE PROPERTY OF SAMTEC. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED IN THE ORDER. IT IS NOT TO BE REPRODUCED, COPIED, OR DISTRIBUTED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF SAMTEC INC.