



## HT High-Temp Silicone Conformal Coating

2106

Techspray offers a variety of coating formulas to match field and engineering requirements. Specifications generally depend on the type of protection needed: e.g. thermal, moisture, and static resistance.

Coatings contain Opti/Scan to allow quality control inspection of coverage and evenness of the coating on a PCB. A coated board can be passed under a standard, low-cost UV (short-wave black) light, and the coated areas glow. The brighter the glow, the thicker the coating.



### Superior thermal and moisture resistance

High Temperature Silicone Coating is designed to prevent thermal breakdown at high temperatures. Silicone Conformal Coating is the most universal coating, offering protection for a wide variety of environments.

- Designed for high temperature environments
- Fast-drying silicone 1-step process
- Non-ozone depleting
- Max operating temperature to 662°F (350°C)
- Dielectric strength 560 volts/mil
- Moisture resistant
- Vibration resistant flexible
- UV indicator for bla

Specifications:

- MIL-I-46058C Type SR
- IPC-CC-830B

### Product Packaging

**2106-12S**  
Fine-L-Kote HT Conformal  
Coating  
12 oz  
12 units/case



**2106-G**  
Fine-L-Kote HT Conformal  
Coating  
1 gal  
1 units/case



**Techspray**  
P.O. Box 949, Amarillo, TX 79105  
800-858-4043 • [www.techspray.com](http://www.techspray.com)



## Technical Information

### Chemical & Physical Properties

Appearance	Clear, colorless liquid
Odor	Aromatic odor
Flash Point	40°F
VOC (EPA)	724 g/l
Boiling Point	110°C (230°F)

### Chemical Composition

CHEMICAL NAME	CAS #
Xylenes (o-,m-,p- isomers)	1330-20-7
Benzene- methyl, (Toluene)	108-88-3
Polysiloxane mixture	811-97-2
1,1,1,2-Tetrafluoroethane (aerosol only)	

### Performance & Application Data

Cure type	Thermal / air
Tack-free time (min)	45
Accelerated cure time/temp	1 Step: 15 Min.@ 49°C
Ambient cure time	24 hrs
Viscosity (bulk)	10-30 cps
Operating temperature range	-40° - 350° C
Dielectric strength	560 V/Mil
Insulation resistance (ohms)	1.33 x 10 <sup>16</sup>

## Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.



---

## Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email [tsales@techspray.com](mailto:tsales@techspray.com) or visit our web site at: [www.techspray.com](http://www.techspray.com).

### North America

Techspray  
P.O. Box 949  
Amarillo, TX 79105  
800-858-4043  
Email: [tsales@techspray.com](mailto:tsales@techspray.com)

### Europe

ITW Contamination Control  
Saffierlaan 5  
2132 VZ Hoofddorp  
The Netherlands  
+31 88 1307 400  
Email: [info@itw-cc.com](mailto:info@itw-cc.com)

### Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2013 Techspray, A Division of ITW