

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Specification Sheets
 - PDF-Keyed LC Opt ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'FLCSSCRLV'

Your search criteria matched only one product, shown below

FLCSSCRLV



- Exceed TIA/EIA-568-B.3 requirements
- Insertion loss: 0.3dB average (multimode and singlemode)
- Return loss: >26dB (10Gig™ multimode), >20dB (multimode), >50dB (singlemode)
- Include color-specific keys with positive and negative keying features to visually and mechanically distinguish connections to prevent unauthorized mating with unlike keyed or non-keyed adapters
- Part of a complete Keyed LC System that includes Opti-Core® Patch Cords and Pigtailed, OptiCam® Pre-Polished Cam Connectors, Opticom® Fiber Adapter Panels (FAPs) and Mini-Com® Adapter Modules
- Translucent housing assembly is laser marked to identify fiber stub fiber type (9µm, 62.5, 50 or 50X)
- Spring-loaded "Senior" rear pivot latch LC connector
- Quick installation; provide field termination in less than half the time of field polish connectors
- Patented re-termination capability provides yield rates approaching 100%
- Factory pre-polished fiber endface eliminates time-consuming field polishing to reduce installation costs, labor, scrap, and the number of tools required
- Cam activated fiber and buffer clamp mechanisms provide superior fiber and buffer retention – less sensitivity to fiber tensile loading
- No separate clamps, tools, or steps are required to secure both the fiber and the buffer
- OptiCam® Termination Tool simplifies tooling and termination, and virtually eliminates operator error by providing visual indication of proper termination after the cam step has been completed
- Cable retention boot assemblies consistently provide higher than industry standard cable retention
- Non-optical disconnect maintains data transmission under tensile loads for jacketed cable
- Fiber cable size: accept 900µm tight-buffered fiber with included boot(s); accepts 1.6mm – 2.0mm and 3.0mm jacketed cable with available OptiCam® Cable Retention Boot Assemblies (ten per package)
- For 250µm coated fiber termination, use 250 micron fiber build-up tube kit or fan-out kits
- Ferrule type: 1.25mm zirconia ceramic (highest durability for repeated matings)
- Use OptiCam® Termination Kit (FCAMKIT)

Additional keyed colors include the following: G– Violet, H– Aqua, J– Rose, K– Slate, L– Brown, P– White, Q– Charcoal, R– Lavender, S– Peach, T– Steel Blue, V– Maroon and W– Mint.

| | |
|--------------------------------|--|
| ▪ Part Number | FLCSSCRLV |
| ▪ RoHS Compliancy Status | RoHS directive is not applicable |
| ▪ Note | Intended for use in fixed installations which are outside the scope of RoHS |
| ▪ Part Description | LC (keyed R – lavender) OptiCam® Singlemode Simplex Fiber Optic Connector for 900µm tight-buffered fiber installation. |
| ▪ Product Type | Keyed LC Duplex Connectors |
| ▪ Fiber Compatibility | 9/125µm |
| ▪ Fiber Cable Size | 900µm |
| ▪ Fiber Cable Type | Tight-buffered |
| ▪ Fiber Type | Singlemode |
| ▪ Termination Style | Pre-Polished Cam |
| ▪ Boot Color | Black |
| ▪ Ferrule Type | Zirconia Ceramic |
| ▪ Key Type and Color | Keyed R – Lavender |
| ▪ Pricing Description | Keyed LC OPTICAM 9/125Um OS1/OS2 Simplex Keyed R |
| ▪ Min. Order UOM | PC |
| ▪ Min. Order Qty. | 1 |
| ▪ BOM Qty. (# of Pkgs.) | 0 |
| ▪ Add to Favorite Product List | <input type="checkbox"/> |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.