

DATASHEET

C1210X7R250-475MNP

GENERAL PURPOSE CERAMIC CAPACITORS (C SERIES)
1210, X7R, 25V, 4.7uF, $\pm 20\%$, 100% matte Tin(Sn) over Nickel



VENKEL LTD.



SIZE SPECIFICATIONS units: inches

Length:	0.126
Width:	0.980
T(max):	0.075
Min E/B:	.020 $\pm$.01
Size(EIA):	1210

COMPONENT SPECIFICATIONS

Category:	Ceramic Capacitors
Series:	General Purpose (C Series)
Size:	1210
Dielectric:	X7R
Voltage:	25V
Capacitance:	4.7uF
Tolerance:	$\pm 20\%$
Termination:	100% matte Tin(Sn) over Nickel
Packaging:	Paper Tape (7" Reel)
Quantity per Reel:	2,000

DIELECTRIC SPECIFICATIONS

Temperature Coefficient:	0 $\pm 15\% \Delta^\circ\text{C}$ MAX
Temperature Voltage Coefficient	X7R not applicable
Ageing:	2.5% per decade hour, typical
Withstanding Voltage:	>2.5 times VDCW
Operating Temp:	-55°C to +85°C
Dissipation Factor:	See C Series Datasheet

COMPLIANCE STATUS

RoHS Status	6 of 6 Compliant
REACH Status	Compliant
Halogen Status	Halogen Free
Conflict Mineral Status	Conflict Mineral Free

REEL DIMENSIONS units: mm

Tape	B min	C	A(7")	A(13")	D Min	N Min	G	T max
8mm	0.30	13 $\pm$.05	178 $\pm$ 2.0	330 $\pm$ 2.0	20.20	50.00	10 $\pm$ 1.5	14.90

TAPING SPECIFICATIONS units: mm

A	B	W	F	E	Po
2.9 $\pm$ 0.2	3.6 $\pm$ 0.2	8.0 $\pm$ 0.2	3.5 $\pm$ 0.1	1.75 $\pm$ 0.1	4.0 $\pm$ 0.1
Pz	D	T	P	To	T(E)
2.0 $\pm$ 0.05 - 0.0	1.5 $\pm$ 0.1		4.0 $\pm$ 0.1	2.5 MAX	0.6 MAX