

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20





© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	4	INCREASE MATERIAL THICKNESS	11OCT2016	VL	SS
	A	DRAWING RELEASED	24APR2017	VL	SS
	A1	REVISED PER ECO-17-007644	26MAY2017	VL	SS
	A2	REVISED PER ECO-17-013857	20SEP2017	SS	HL




SCALE 4:1

NOTES:

- 1 MATERIAL: 0.15mm CRS. 1,25 - 3.00µm MATTE TIN FINISH.
- 2 MATERIAL: 0.15mm AL. 1.20 - 2.00µm MATTE TIN FINISH OVER NICKEL FLASH.
- 3 STAMPING BURR OUTSIDE OF PART, MAX 0.05mm.
- 4 PARTS TO BE FREE OF OIL AND CONTAMINENTS.
- 5 PART IS RoHS COMPLIANT PER TE CONNECTIVITY STANDARD TEC-138-702.
- 6 REFER TO 3D MODEL FOR UNSPECIFIED DIMENSIONS.
- 7 PACKAGING: BULK

7	2	2118715-4
7	1	2118715-2
PACKAGING	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. LAC 06APR2016	 TE Connectivity		
		CHK S. SU 24APR2017			
		APVD V. LAC 24APR2017	NAME STANDARD SHIELD COVER		
		PRODUCT SPEC 108-19493			
		APPLICATION SPEC 114-115014	SIZE A3 CAGE CODE - DRAWING NO C-2118715 RESTRICTED TO -		
		WEIGHT -			
CUSTOMER DRAWING		SCALE 6:1		SHEET 1 OF 1	REV A2

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±0.20
	1 PLC ±0.15
	2 PLC ±0.10
	3 PLC ±
	4 PLC ±
	ANGLES ±2
MATERIAL SEE TABLE	FINISH SEE TABLE
-	-