

FULLY SEALABLE HEIDI-XP lenses for CREE XP-E LEDs




- Specially designed for Cree XLAMP XP-E series of LEDs.
- Lens material optical grade PMMA with high UV and temperature resistance (105°C/220°F)
- High optical efficiency, up to 90%
- No lens holder. Fastening to heat sink with a PU foam adhesive tape of automotive grade
- Please check fastening details from this link:
(http://www.ledil.com/datasheets/DataSheet_TAPE.pdf)
- Lens foot can be potted with resin without losses in optical efficiency (**fully sealed construction** of luminaire possible)
- Diameter 21.6 mm

LENS TYPES

NAME	ORDERING CODE	FWHM Angle
HEIDI diffuser	CA11264_Heidi-D-XP	±4°
HEIDI medium	CA11265_Heidi-M-XP	±14°
HEIDI oval	CA11266_Heidi-O-XP	±25° x ±5°
HEIDI oval turned 90°	CA11267_Heidi-O-90-XP	±25° x ±5°
HEIDI wide	CA11268_Heidi-W-XP	Coming soon

MEASUREMENTS

Relative Intensity of CA11264_Heidi-D-XP





© Ledil Oy – Subject to change without prior notice

Ledil Oy
Tehdaskatu 13
FIN-24100 SALO, Finland

www.ledil.com
email: ledil@ledil.com
FAX: +358-2-733 8001


2010-10-04

Relative Intensity of CA11265_Heidi-M-XP



© Ledil Oy – Subject to change without prior notice

Relative Intensity of CA11266_Heidi-O-XP




© Ledil Oy – Subject to change without prior notice

Ledil Oy
Tehdaskatu 13
FIN-24100 SALO, Finland

www.ledil.com
email: ledil@ledil.com
FAX: +358-2-733 8001

2010-10-04

DRAWINGS



© Ledil Oy – Subject to change without prior notice