


PART NUMBER	REV	FIRST USED
1385469-1	B	122500-1
1385469-2	B	565435-5
1385469-3	B	354500-1



TERMINAL NAME: 45 AMP POWER PRODUCT (10-14 AWG)					
AMP TERM PN		CRIMP DATA BLOCK			
1445962	-	PAD LTR	CRIMP HEIGHT		WIRE SIZE
		A	.116 ±.003 [2.95 ±0.08mm]		10
		B	.105 ±.003 [2.67 ±0.08mm]		12
		C	.096 ±.003 [2.44 ±0.08mm]		14
		D	NOT		USED
		CRIMP	SIZE	TYPE	RANGE
		WIRE	.155 [3.94mm]	F	14-10
		INSUL	-	-	-
WIRE STRIP LENGTH	TERM APPL SPEC	FEED	APPL INSTRUCTION	SET UP GAGE	LAYOUT
.266-.297	NONE	.547	408-8040	458637-1	L2705

2	2	2	-	C	6-354778-9	PIN, WIRE DISC (.2840)C	129
2	2	2	-	C	4-354778-9	PIN, WIRE DISC (.2740)B	128
2	2	2	-	C	3-354778-1	PIN, WIRE DISC (.2650)A	126
1	1	1	-	A	986950-1	WASHER, FLAT PRECISION	125
1	1	1	-	A	217238-1	GENERAL INSTRUCTION PACKAGE	124
1	1	1	-	-	4088040	SF APPL INST 408-8040	123
							122
							121
							120
							119
3	3	3	-	A	21024-5	WASHER, LOCK (#10)ADJ BLOCK	118
							117
							116
2	2	2	-	A	21024-2	WASHER, LOCK (#4)FRONT STP GUIDE	114
							113
2	-	2	-	A	21055-6	WASHER, FLAT (#8) STRIPPER	112
4	4	4	-	A	21024-4	WASHER, LOCK (#8) STRIPPER	111
							110
-	1	-	-	A	2-21002-6	SCR, BHC (10-32x.38) LUBE ASSY	109
							108
							107
							106
							105
1	1	-	-	A	992031-1	PIN, CLEVIS	104
1	1	1	-	A	21009-2	SCR, SKT SET (1/4-20x.25 LW) RAM	103
2	2	2	-	A	21017-2	SCR, DRIVE (#2x.19) ID PLATE	102
							101
1	1	1	-	B	461264-1	PLATE, IDENTIFICATION	100
2	2	2	-	A	3-21002-0	SCR, BHC (10-32x.88) DRAG	99
1	1	1	-	A	22733-8	SCR, BHC (8-32x.38 LW) ANVIL	98
4	4	4	-	A	2-21002-9	SCR, BHC (10-32x.75) CAP	97
3	3	3	-	A	2-22733-8	SCR, BHC (1/4-20x.62) HSG	96
1	1	1	-	A	2-21002-7	SCR, BHC (10-32x.50) 56 ADJ BLK	95
2	2	2	-	A	2-21002-2	SCR, BHC (8-32x.50) TERM H DWN	94
							93
							92
							91
							90
1	1	-	-	A	7-21000-9	SCR, SHC (4-40x.19) STRIPPER	89
1	1	-	-	A	3-21000-0	SCR, SHC (8-32x.88) SHEAR	88
							87
1	1	1	-	A	2-22603-1	SCR, HEX HD (8-32x.38) FEED FINGER	86
2	2	2	-	A	1-21000-5	SCR, SHC (4-40x.50) FR ST GUIDE	85
1	1	1	-	A	2-21000-8	SCR, SHC (8-32x.62) STRIPPER	84
2	2	2	-	A	2-21000-6	SCR, SHC (8-32x.38) HOLD DOWN	83
2	2	2	-	A	2-21002-0	SCR, BHC (8-32x.25) GUIDE	82
1	1	1	-	A	3-21000-4	SCR, SHC (10-32x.38) 56 ADJ BL	81
1	1	1	-	A	1633055-1	GUIDE, STOCK	80
-	1	-	-	B	462992-7	GUARD ASSY	79
REF	-	-	-	B	679532-1	INSERT, GUARD	78
-	1	-	-	C	1-465184-0	LUBRICATOR ASSY	77
							76
-	1	-	-	A	22317-3	ELBOW, COPPER TUBE	75
							74
1	1	1	-	B	21024-8	WASHER, LOCK (3/8) AIR FEED	73
1	1	1	-	B	3-21001-5	SCR, SHC (3/8-16x1.00) AIR FEED	72
1	1	1	-	B	459610-1	MOUNT, FEED BRACKET	71
-3	-2	-1	U/M	DWG SIZE	PART NO	DESCRIPTION	ITEM NO

QTY RECD PER ASSY		PARTS LIST			
FENCE SET-UP DIM REF .210 29					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1385469-3](#)