

CERAMIC SMD ULTRA MINIATURE QUARTZ CRYSTAL

ABM3C

Pb in glass

(Exempt per RoHS 2002/95/EC Annex (5))

RoHS
Compliant

ABM3C

5.0 x 3.2 x 1.3mm

FEATURES:

- Low in height; suitable for thin equipment.
- Glass sealed package assures high reliability and high temperature operation
- Tight tolerance and stability available.
- Suitable for RoHS reflow profile

APPLICATIONS:

- Automotive applications
- High density applications.
- Modems, communication and test equipment.
- PCMCIA, Wireless applications

STANDARD SPECIFICATIONS:

Parameters	Minimum	Typical	Maximum	Units	Notes
Frequency Range	10.000	-----	50.000	MHz	Fundamental
Operation Mode	Fundamental				
Operating Temperature	-10	-----	+70	°C	See options
Storage Temperature	-40	-----	+90	°C	
Frequency Tolerance @+25°C	-50	-----	+50	ppm	See options
Frequency Stability over the Operating Temperature (ref. to +25°C)	-50	-----	+50	ppm	See options
Equivalent series resistance (R1)	See table 1 below				
Shunt capacitance (C0)	-----	-----	7	pF	
Load capacitance (CL)	-----	18	-----	pF	Standard (See options if other than STD)
Drive Level	-----	10	100	μW	
Aging	-5	-----	+5	ppm	@25°C±3°C First year
Insulation Resistance	500	-----	-----	MΩ	@ 100Vdc ± 15V

Table 1 – Standard ESR

Frequency (MHz)	ESR(Ω) max.
10.000 – 15.999	60
16.000 – 50.000	50

OPTIONS & PART IDENTIFICATION:

(Left blank if standard)

ABM3C - MHz - - - -

Frequency in MHz
Please specify the frequency in MHz.
e.g. 14.31818MHz

Load Capacitance (pF)
Please specify CL in pF or S for series

Custom ESR if other than standard
R□
□: Specify a value in Ω (e.g.: R40)

Operating Temp.
E: 0°C ~ +70°C
B: -20°C ~ +70°C
C: -30°C ~ +70°C
N: -30°C ~ +85°C
D: -40°C ~ +85°C
J(***): -40°C ~ +105°C
K(****): -40°C ~ +125°C

Freq. Tolerance
2: ± 20 ppm
3: ± 25 ppm
4: ± 30 ppm

Packaging
Blank: Bulk
T: Tape & Reel

Freq. Stability
Y*: ± 30 ppm
H*: ± 35 ppm
A**: ± 80 ppm
Q**: ± 100 ppm
V: ± 120 ppm

* Standard temp. or option E only

** Standard temp. or option E, B, C, N, D only

*** Stability option Q and V only

**** Stability option V only

ABRACON IS
ISO9001:2008
CERTIFIED



ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale **Revised: 02.26.11**

30332 Esperanza, Rancho Santa Margarita, California 92688

tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

ABM3C

5.0 x 3.2 x 1.3mm

(Exempt per RoHS 2002/95/EC Annex (5))

RoHS
Compliant



The drawing includes the following views and dimensions:

- Top View:** Shows a rectangular connector with a central pin area. Dimensions include a total width of $0.20 \pm .006$ (5.0 ± 0.15), a central pin width of 0.10 (2.6), and a pin pitch of 0.012 C(0.3). The overall height is $0.126 \pm .006$ (3.2 ± 0.15).
- Side View:** Shows the profile of the connector with a maximum height of 0.051 Max. (1.3).
- Detail View:** A close-up of the pin area showing four pins labeled 1, 2, 3, and 4. The distance between pins 1 and 2 is 0.055 (1.4).
- TOP VIEW:** A schematic diagram of the connector showing the internal circuitry and the locations of the four pins (1, 2, 3, 4) relative to the ground (GND) connections.

Dimensions: inches (mm)

1000pcs/reel

FEEDING (PULL) DIRECTION



Dimensions: mm

Figure 1 is a graph showing a typical reflow profile. The Y-axis represents Temperature in degrees Celsius (°C), with marked values at 25°C, 150°C, 180°C, 230°C, and 260°C. The X-axis represents Time in seconds (s). The profile consists of three main phases: Pre-Heat, Reflow, and Cool. The Pre-Heat phase starts at 25°C and rises to 150°C, with a duration of 60~120s. The Reflow phase starts at 150°C and rises to 260°C, with a duration of 30~40s. The Cool phase starts at 260°C and decreases back to 25°C, with a duration of 60~90s. A note indicates '10s max. 1 time at +260°C±5°C'.

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO9001:2008
CERTIFIED



ABRACON CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale **Revised: 02.26.11**

30332 Esperanza, Rancho Santa Margarita, California 92688

tel 949-546-8000 | fax 949-546-8001 | www.abracon.com