





REVISIONS					
SYM.	DESCRIPTION			DATE	APPROVED
A	REVISED	PER	DCN 09808	05/27/92	T. L.
B	REVISED	PER	DCN 11011	03/07/94	T. L.
C	REVISED	PER	DCN 11818	05/23/95	T. L.
D	REVISED	PER	DCN 11968	08/28/95	T. L.
E	REVISED	PER	DCN 12326	03/08/96	T. L.
F	REVISED	PER	DCN 12358	05/24/96	T. L.
G	REVISED	PER	DCN 21536	10/21/03	T. L.
H	REVISED	PER	DCN 21634	11/13/03	T. L.
J	REVISED	PER	DCN 23288	12/29/04	T. L.
K	REVISED	PER	DCN 27043	02/06/07	T. L.




GROUND LUG
LOCATION
STRAIGHT 14-24



SHELL SIZE, TABLE I.

Technical drawing of a mechanical part, likely a valve or plug, showing a cross-section. The part has a central threaded section with a cross-hatched pattern. Dimensions include a maximum length of .690 and a 90-degree angle. The drawing is labeled "SYM A - 90°" and "F".

GROUND LUG
LOCATION
08-24



GROUND LUG
LOCATION
08-24



1. ASSEMBLY IDENTIFIED WITH MANUFACTURERS NAME AND P/N,
SPACE PERMITTING.
2. GLENAIR 600 SERIES BACKSHELL ASSEMBLY TOOLS ARE RECOMMENDED
FOR ASSEMBLY AND INSTALLATION.

4. MATERIAL/FINISH:
COUPLING NUT, QWIK-TY® BODIES - AL ALLOY/SEE TABLE III
HARDWARE - CRES/PASSIVATE


UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONS ± 1/16 DECIMALS .XX ±.03 .XXX ±.015 ANGLES ± 2°		DRAWN S. SMITH 6/19/86		GLENAIR, INC. 1211 AIR WAY - GLENDALE - CALIFORNIA 91201				CAD 1986	
		CHECK R. KEIM 6/19/86							
		ENGR P. OAKES 6/19/86		QWIK-TY [®] , FOR CONNECTORS PER TABLE I					
		 APPROVED							
RELEASE DATE 6/19/86									
DO NOT SCALE THIS DRAWING		ORIGINAL RELEASE DATE		CODE IDENT. NO. 06324		SIZE C	450-005		REV K
B/F 87-8116	P/C 45	NON REPARABLE COMMERCIAL ITEM		SCALE N/A		WEIGHT N/A		SHEET 1 OF 2	

TABLE I										
SHELL SIZE					A THREAD	C DIA MAX	E MAX	F CABLE ENTRY	G MAX	H MAX
A	F	H	L	S						
	08 		08	08	7/16-28 UNEF	.65	.990	.260	1.066	.89
		09 			M12 X 1.0 - 6H	.77	.990	.260	1.066	.89
08					1/2-20 UNF	.65	.990	.260	1.066	.89
03	10 		10	10	9/16-24 UNEF	.77	.990	.365	1.066	.95
		11 			M15 X 1.0 - 6H	.82	.990	.365	1.066	.95
10					5/8-24 UNEF	.77	.990	.365	1.066	.95
	12 		12	12	11/16-24 UNEF	.89	1.050	.501	1.066	1.01
		13 			M18 X 1.0 - 6H	.94	1.050	.501	1.066	1.01
12 					3/4-20 UNEF	.94	1.050	.501	1.066	1.01
	14 		14	14	13/16-20 UNEF	1.02	1.230	.575	1.285	1.33
		15 			M22 X 1.0 - 6H	1.07	1.230	.575	1.285	1.33
14 					7/8-20 UNEF	1.02	1.230	.575	1.285	1.33
	16 		16	16	15/16-20 UNEF	1.15	1.230	.700	1.285	1.39
		17 			M25 X 1.0 - 6H	1.21	1.230	.700	1.285	1.39
16 					1-20 UNEF	1.21	1.230	.700	1.285	1.39
18 	18 		18	18	1 1/16-18 UNEF	1.23	1.290	.779	1.285	1.46
		19 			M28 X 1.0 - 6H	1.36	1.290	.779	1.285	1.46
20 	20 		20	20	1 3/16-18 UNEF	1.36	1.420	.904	1.285	1.51
		21 			M31 X 1.0 - 6H	1.48	1.420	.904	1.285	1.51
22	22 		22	22	1 5/16-18 UNEF	1.48	1.540	1.029	1.285	1.59
		23 			M34 X 1.0 - 6H	1.60	1.540	1.029	1.285	1.59
24	24 		24	24	1 7/16-18 UNEF	1.73	1.660	1.144	1.285	1.64
		25 			M37 X 1.0 - 6H	1.70	1.660	1.144	1.285	1.64

NOTE: CONNECTOR DESIGNATIONS DEPICTED WITH

*

 ARE FOR
REFERENCE ONLY AND ARE NOT TO BE USED IN PART NUMBER DEVELOPMENTS

TABLE II		
CONNECTOR DESIGNATOR REFERENCE TABLE		
CONNECTOR DESIGNATOR	CONNECTOR SPECIFICATION	SERIES
A	MIL-C-5015	MS34*0
	MIL-C-26482	2
	MIL-C-81703	3
	MIL-C-83723	I & III
	40M39569	
	CECC 75201.001	
	DEF 5326-3	
	EN2997	
	EN3646	
	ESC10	
	ESC11	
	LN 29504	
	NFC 93422	HE302
	PAN 6432-1	
	PAN 6432-2	
	PATT 602	
F	MIL-C-38999	I & II
	40M38277	
	NFC 93422	HE309
	NFC 93422	HE308
	PAN 6433-1	
	PATT 614	
	PATT 616	
H	MIL-C-38999	III & IV
L	EN 3372	
	JN 1003	
	LN 29729	
	NFC 93422	HE306
	PAN 6433-2	
	PATT 615	
	VG 96912	
S	PATT 105	
	PATT 603	
	PATT 608	

REVISIONS			
SYM.	DESCRIPTION	DATE	APPROVED
	SEE SHEET 1		

TABLE III	
SYM	FINISH DESCRIPTION
B	CADMIUM PLATE, OLIVE DRAB
C*	ANODIZE, BLACK
G*	HARD COAT, ANODIC
J	GOLD IRIDITE OVER CADMIUM PLATE OVER NICKEL
LF	CADMIUM PLATE, BRIGHT OVER ELECTROLESS NICKEL
M	ELECTROLESS NICKEL
N	CADMIUM PLATE, OLIVE DRAB OVER NICKEL
NC	ZINC COBALT, DARK OLIVE DRAB
NF	CAD/O. D. OVER ELECTROLESS NICKEL (500 HOUR SALT SPRAY)
T	CADMIUM PLATE, BRIGHT DIP OVER NICKEL
U**	CADMIUM PLATE, BLACK
UC	ZINC COBALT, BLACK
X	CADMIUM PLATE, BLACK OVER ELECTROLESS NICKEL
Z1**	PASSIVATE
ZN	ZINC NICKEL, OLIVE DRAB

*NON-CONDUCTIVE FINISH - NOT
SUITABLE FOR RFI/EMI SHIELDING
APPLICATIONS

**APPLICABLE TO CORROSION
RESISTING STEEL BACKSHELLS
AND ACCESSORIES
CONSULT FACTORY FOR OTHER
AVAILABLE FINISHES

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONS ± 1/16 .XX ±.03 DECIMALS .XXX ±.015 ANGLES ± 2°	DRAWN		S. SMITH		6/19/86		GLENAIR, INC. CAD 1986[®] 1211 AIR WAY - GLENDALE - CALIFORNIA 91201						
	CHECK		R. KEIM		6/19/86								
	ENGR		P. OAKES		6/19/86		QWIK-TY [®] , FOR CONNECTORS PER TABLE I						
	APPROVED												
	RELEASE DATE 6/19/86												
DO NOT SCALE THIS DRAWING		ORIGINAL RELEASE DATE				CODE IDENT. NO.		SIZE	450-005		REV. K		
B/F 87-8116		P/C 45		NON REPAIRABLE COMMERCIAL ITEM				SCALE N/A		WEIGHT N/A		SHEET 2 OF 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[450FA005N12](#) [450FS005N24](#) [450AA005NF12](#) [450AA005NF14](#) [450AS005NF18](#) [450FS005N10](#) [450FS005N14](#)
[450FS005N16](#) [450FS005N20](#) [450FS005N22](#) [450HS005NF13](#) [450HS005NF15](#) [450HS005NF17](#) [450HS005NF21](#)
[450HS005NF23](#) [450HS005NF25](#) [450AA005B08](#) [450AA005B10](#) [450AA005C08](#) [450AA005M08](#) [450AA005M10](#)
[450AA005M12](#) [450AA005M14](#) [450AA005M16](#) [450AA005M22](#) [450AA005N10](#) [450AA005N12](#) [450AA005N16](#)
[450AA005N18](#) [450AA005NF10](#) [450AA005NF16](#) [450AA005NF18](#) [450AA005NF20](#) [450AA005NF24](#) [450AB005N10](#)
[450AS005B10](#) [450AS005B14](#) [450AS005B28](#) [450AS005C08](#) [450AS005M08](#) [450AS005M10](#) [450AS005M12](#)
[450AS005M14](#) [450AS005M16](#) [450AS005M20](#) [450AS005M22](#) [450AS005M24](#) [450AS005N10](#) [450AS005N12](#)
[450AS005N14](#) [450AS005N18](#) [450AS005N20](#) [450AS005N28](#) [450AS005NF10](#) [450AS005NF12](#) [450AS005NF14](#)
[450AS005NF16](#) [450AS005NF22](#) [450DS005B08](#) [450FA005B08](#) [450FA005B12](#) [450FA005M08](#) [450FA005M10](#)
[450FA005M22](#) [450FA005N08](#) [450FA005N10](#) [450FA005N14](#) [450FA005N16](#) [450FA005N18](#) [450FA005N20](#)
[450FA005N22](#) [450FA005N24](#) [450FA005NF12](#) [450FA005NF14](#) [450FA005NF16](#) [450FA005NF20](#) [450FA005NF22](#)
[450FA005NF24](#) [450FB005N12](#) [450FB005N14](#) [450FB005N16](#) [450FB005N18](#) [450FB005N20](#) [450FB005N22](#)
[450FB005N24](#) [450FS005B08](#) [450FS005B10](#) [450FS005B22](#) [450FS005C14](#) [450FS005M08](#) [450FS005M10](#)
[450FS005M12](#) [450FS005M14](#) [450FS005M16](#) [450FS005M18](#) [450FS005M20](#) [450FS005M22](#) [450FS005M24](#)
[450FS005N08](#) [450FS005N12](#)