


This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.



SPECIFICATIONS:

- | | |
|---|----|
| 1) SOLDER CUP CONTACT: TO ACCOMMODATE 22-30 AWG
SOLID AND 24-30 STRANDED CONNECTOR WIRES. | 12 |
| 2) DIELECTRIC: DIALLY-PHTHALATE PER MIL-M-14F TYPE MDG UL-94V0 | 13 |
| 3) CONTACT MATERIAL: COPPER ALLOY | 14 |
| 4) CONTACT: 20 MICRO-INCHES MIN. GOLD MATING AREA: 3-5 MICRO-INCHES GOLD
TERMINAL AREA: 50 MICRO-INCHES MIN. NICKEL UNDERPLATING ALL OVER. | |
| 5) SHELL MATERIAL: ZINC PLATED STEEL WITH CLEAR CHROMATE COATING | |
| 6) CURRENT CAPACITY: 5 AMPS/CONTACT | |
| 7) VOLTAGE RATING: 700 VOLTS D.C. AT SEA LEVEL
200 VOLTS D.C. AT 70,000 FEET | |
| 8) INSULATION RESISTANCE: >5000 M OHM | |
| 9) DIELECTRIC WITHSTANDING VOLTAGE: 1200 VAC (RMS) AT SEA LEVEL | |
| 10) CONNECTOR MATING FORCE: REFER TO TABLE 1. | |

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
A	HK	PRELIMINARY RELEASE	11/20/02	Y.M.LEE
B	HK	ADD CHOP OF ROHS	7/18/06	IP


TABLE 1

CONNECTOR SIZES	AVERAGE MATING FORCE (POUNDS)
14	5
24	8
36	12
50	15
64	19



- 11) CONTACT RETENTION FORCE: 2 LBS MAX.
- 12) DURABILITY: 250 CYCLES MIN.
- 13) VIBRATION: NO INTERRUPTIONS < 1u SEC.
- 14) OPERATING TEMPERATURE: -55°C TO +105°C (-67°F TO +221°F)

CUSTOMER INFORMATION DRAWING

ITEM NO		NOMENCLATURE OR DESCRIPTION				QTY REQ'D			
PARTS LIST									
UNLESS OTHERWISE SPECIFIED TOLERANCES U.S. METRIC .X +/- .015 .XX +/- .010 .XXX +/- .005 FRACTIONS +/- ANGLES +/- 1° FOR MATERIALS AND FINISHES SEE NOTES REMOVE SHARP EDGES DIMENSIONS U.S. INCHES (METRIC) (MM)		APPROVAL		DATE		Amphenol			
		DRAWN XS.GUO		7/18/06					
		CHECKED							
		CHECKED							
		DRAWING FILE:				TITLE		14 SIZE RECEPTACLE ASSY, RACK & PANEL MINIATURE RIBBON	
\DRAWING\57\C5720140.DWG									
		ANGLE OF PROJECTION		SIZE		DRAWING NO.		REV.	
				A3		C57-20140		B	
				SCALE		NONE		SHEET 1 OF 1	