

40x40x6 mm



SUNON

4.5~5.9 CFM



Green Motor Series (Magnetic Levitation System Motor)

Model	P/N	Bearing ● VAPO ○ BALL ⊗ 2BALL	Rating Voltage (VDC)	Power Current (AMP)	Power Consumption (WATTS)	Speed (RPM)	Air Flow (CFM)	Static Pressure (Inch-H ₂ O)	Noise (dBA)	Weight (g)
GM0504PEV1-8		●	5	0.09	0.45	7000	5.9	0.1	32	7.5
GM0504PEV2-8		●	5	0.06	0.3	6000	5.5	0.08	26	7.5
GM0504PEV3-8		●	5	0.04	0.2	5000	4.5	0.06	22.5	7.5
GM0504PEB1-8		○	5	0.09	0.45	7000	5.9	0.1	32	7.5
GM0504PEB2-8		○	5	0.06	0.3	6000	5.5	0.08	28	7.5
GM0504PEB3-8		○	5	0.04	0.2	5000	4.5	0.06	23	7.5



*Specifications subject to change without notice.

40x40x8 mm

SUNON


5.4 CFM



KDE Series (Magnetic Levitation System Motor)

Model	P/N	Bearing ● VAPO ○ BALL ⊗ 2BALL	Rating Voltage (VDC)	Power Current (AMP)	Power Consumption (WATTS)	Speed (RPM)	Air Flow (CFM)	Static Pressure (Inch-H ₂ O)	Noise (dBA)	Weight (g)
KDE0504PDV2-8	MS	●	5	0.13	0.7	6600	5.4	0.12	32.5	11.8
KDE1204PDV2-8	MS	●	12	0.13	0.7	6600	5.4	0.12	32.5	11.8

*Remarks : GM series are available with lower power consumption, higher torque and higher T^o range (ïÜ70℃J).



*Specifications subject to change without notice.

40x40x10 mm

SUNON




4.9~8.6 CFM



KDE Series (Magnetic Levitation System Motor)

Model	P/N	Bearing ● VAPO ○ BALL ⊙ 2BALL	Rating Voltage (VDC)	Power Current (AMP)	Power Consumption (WATTS)	Speed (RPM)	Air Flow (CFM)	Static Pressure (Inch-H ₂ O)	Noise (dBA)	Weight (g)
KDE1204PFVX	MS	●	12	0.10	1.2	8800	8.6	0.23	36	16
KDE1204PFV1	MS	●	12	0.08	1.0	7400	7.3	0.18	30	16
KDE1204PFV2	MS	●	12	0.05	0.6	5500	4.9	0.12	25	16
KDE1204PFBX	MS	○	12	0.10	1.2	8800	8.6	0.23	37	16
KDE1204PFB1	MS	○	12	0.08	1.0	7400	7.3	0.18	31	16
KDE1204PFB2	MS	○	12	0.05	0.6	5500	4.9	0.12	26	16

*Remarks : GM series are available with lower power consumption, higher torque and higher T^o range (ïÜ70℃J).



*Specifications subject to change without notice.

40x40x20 mm

SUNON


6.3~10.8 CFM



KDE Series (Magnetic Levitation System Motor)

Model	P/N	Bearing ● VAPO ○ BALL ⊙ 2BALL	Rating Voltage (VDC)	Power Current (AMP)	Power Consumption (WATTS)	Speed (RPM)	Air Flow (CFM)	Static Pressure (Inch-H ₂ O)	Noise (dBA)	Weight (g)
KDE1204PKVX	MS	●	12	0.13	1.6	8200	10.8	0.27	27.5	30
KDE1204PKV1	MS	●	12	0.10	1.2	7200	8.9	0.21	25.5	30
KDE1204PKV2	MS	●	12	0.07	0.8	6200	7.7	0.16	21	30
KDE1204PKV3	MS	●	12	0.05	0.6	5200	6.3	0.11	18	30
KDE1204PKBX	MS	○	12	0.13	1.6	8200	10.8	0.27	29	30
KDE1204PKB1	MS	○	12	0.10	1.2	7200	8.9	0.21	26	30
KDE1204PKB2	MS	○	12	0.07	0.8	6200	7.7	0.16	21.5	30
KDE1204PKB3	MS	○	12	0.05	0.6	5200	6.3	0.11	18.5	30

*Remarks : GM series are available with lower power consumption, higher torque and higher T[°] range (jÜ70CJ).



*Specifications subject to change without notice.