

DESCRIPTION

An adjustable Multi-lamp Recessed fixture for trimless installation suitable for downlighting and accent applications. Utilizes FIVE (5) PAR38 120V lamps.

For new construction applications. Insulation must be kept 3" from all sides and at least 1" above the housing.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

A... Housing

Housing, junction box & trimless meshplate assembly are all steel construction. Perforated meshplate allows for trimless installation in drywall/plaster ceilings by allowing the ceiling's mudding compound to be applied right up to the edge of the fixture opening. Includes a beveled "knife-edge" lips to ensure a clean edge. Can accommodate 0.50" to 1.25" ceiling thickness. Optional Chicago Plenum configuration available.

B... System Protection:

Thermal protection provided to guard against overheating and misuse of insulation over and around fixture. Vent holes in housing provide cooler operation.

C... Junction Box

Junction Box is UL listed for through

branch wiring, 6 #12 90° C supply conductors or 60° C for end of run. The fixture is also UL listed as 'access above ceiling not required'.

D... Electrical

Electrical accessible through ceiling opening. J-Box located on the side wall of the housing behind removable access doors. Electrical components on individually removable "trays" for easy maintenance.

E... Lamps

Five (5) PAR38 120V lamps mounted in adjustable double gimbal. Lamp holders are individually removable and may be regressed 1" for additional cut-off. Lamp can accept optical accessories. 45° x 45° locking lamp adjustment. Beveled-edge lamp ring is secured with threadless,

bayonet action. Optional retractable arm is available for lamp pulldown and extreme aiming. Includes Med. base sockets.

F... Mounting

Butterfly Brackets accept 1/2" EMT, C Channel, Tbar fasteners, and bar hangers. Four tabs on housing for securing to structure. Perforated flaps along housing sides for securing trimless insert to fixture and drywall.

G... Labels


cULus listed for non-type IC applications, suitable for use in damp locations.

Ceiling Cut-Out: 7.49" x 34.24"

COMBOLIGHT® Next Generation Recessed Multi-Lamp Fixture

Five (5) Light
PAR38 120V

New Construction
Housing
Trimless



For use with PAR38 120V lamps 100W max.

ORDERING INFORMATION



C5			N	120	N			N
Configuration C5 = COMBOLIGHT Recessed Five (5) Light		Lamp Type / Wattage Label 100P38 = 100 Watt max. PAR38 120V		Primary Voltage 1 = 120V		Lamp Mechanism G = Double Gimbal R = Retractable Double Gimbal		Trim Insert Finish N = Trimless
	Housing N = New Construction C = Chicago Plenum		Power Supply N = None - Line Voltage Lamp		Trim Insert N = Trimless		Housing Interior/Electrical Door/Sleeve Finish W = White B = Black S = Industrial Silver	