








P R O D U C T D A T A S H E E T

1.0VA PCB MOUNTED ENCAPSULATED TRANSFORMER



-  Independantly Approved to **EN60950**
-  Inherently Short Circuit Proof
-  CE Marked
-  Single 230V primarys
-  Comprehensive choice of secondary voltages
-  UL94- V0 Vacuum Encapsulated Construction
-  Suitable for flow soldering

| | | | |
|--------------------|--------------------|----|-----------|
| Weight | 0.065 | Kg | Approvals |
| Typical Regulation | 25 | % | EN |
| Frequency | 50/60 | Hz | |
| Max Ambient | 40 | °C | |
| Bobbin Material | UL94-V0 “B” 130 °C | | |

| Part No | Primary | Secondary | Secondary Fuse |
|---------|---------|-----------|---|
| D3508 | 230 | 6+6 | Not Required. All Parts Inherently Short-Circuit Proof. |
| D3509 | 230 | 9+9 | |
| D3510 | 230 | 12+12 | |
| D3511 | 230 | 15+15 | |

Please see sheet 2 for dimensions, pin outs and connection information.

DAGNALL ELECTRONICS LIMITED

Shuttleworth Road, Elms Industrial Estate, Bedford. MK41 0EP UK

TEL +44(0)1234 330077 FAX +44(0)1234 330088

E-mail sales@dagnall-electronics.com


Issue 1. 25/10/02

2 of 2


PRODUCT DATASHEET

1.0VA PCB MOUNTED ENCAPSULATED TRANSFORMER

Outline Drawing



Pin Grid



PCB Pins 0.635mm Sq

Pin length 5.0mm

Hole size 1.0mm

5mm pin grid

Connection Diagrams for D3508

