










20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																															
CKT SIZE	① HOUSING	② TPA	③ POWER TERMINAL	④ SIGNAL TERMINAL	⑤ SIGNAL HOUSING (3 OF EA REQ'D)	DIMENSION 'A'	DIMENSION 'B'	DIMENSION 'C'	DIMENSION 'D'	DIMENSION 'E'																																																																																																																																																																																																								
	MATERIAL: PBT, FILLED	MATERIAL: PBT, FILLED	MATERIAL: COPPER ALLOY FINISH: TIN OVER NICKEL W/SELECT GOLD	MATERIAL: PHOS BRONZE FINISH: TIN OVER NICKEL W/SELECT GOLD	MATERIAL: NYLON, UNFILLED																																																																																																																																																																																																													
2P-12S	172512-3212	46708-3212	173693-****	70058-****	46709-0004	63.81	55.01	26.48	12.37	43.74																																																																																																																																																																																																								
2P-18S	172512-3218	46708-3218	173693-****	70058-****	46709-0006	68.89	60.09	31.80	17.44	48.82																																																																																																																																																																																																								
2P-24S	172512-3224	46708-3224	173693-****	70058-****	46709-0008	73.97	65.17	36.85	22.53	53.90																																																																																																																																																																																																								
4P-12S	172512-3412	46708-3412	173693-****	70058-****	46709-0004	78.81	70.01	41.48	12.37	58.74																																																																																																																																																																																																								
4P-18S	172512-3418	46708-3418	173693-****	70058-****	46709-0006	83.89	75.09	46.80	17.44	63.82																																																																																																																																																																																																								
4P-24S	172512-3424	46708-3424	173693-****	70058-****	46709-0008	88.97	80.17	51.85	22.53	68.90																																																																																																																																																																																																								
6P-12S	172512-3612	46708-3612	173693-****	70058-****	46709-0004	93.81	85.01	55.73	12.37	73.74																																																																																																																																																																																																								
6P-18S	172512-3618	46708-3618	173693-****	70058-****	46709-0006	98.89	90.09	61.85	17.44	78.82																																																																																																																																																																																																								
6P-24S	172512-3624	46708-3624	173693-****	70058-****	46709-0008	103.97	95.17	66.93	22.53	83.90																																																																																																																																																																																																								
																																																																																																																																																																																																																		
												NOTES: - SEE CHART FOR MATERIAL DETAILS - PART MATES TO MOLEX PLUG SERIES 172458. - ASSEMBLY SHOWN FOR REFERENCE ONLY. EACH ITEM HAS TO BE ORDERED SEPARATELY. - PANEL MOUNTING HARDWARE: (2) M3 X 0.5 X 4.00 LG PRECISION SHOULDER SCREWS AND (2) M3 X 0.5 HEX NUTS TO BE PURCHASED SEPARATELY BY CUSTOMER. - SEE SD-173693-001 FOR POWER TERMINAL DETAILS. - SEE SD-70058-*** FOR SIGNAL TERMINAL DETAILS.												<table><tr><td rowspan="2">CHG TRMNL P/N EC NO: UCP2016-4071 DRAWN: JSCHAFER CHKD: APPR: BPISZCZOR</td><td rowspan="10">2016/04/18 2016/10/03</td><td rowspan="10">DESCRIPTION</td><td rowspan="10">QUALITY SYMBOLS</td><td colspan="2" rowspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2" rowspan="2">DIMENSION STYLE MM ONLY</td><td rowspan="2">SCALE 1.5:1</td><td rowspan="10">DESIGN UNITS METRIC</td><td rowspan="2">THIRD ANGLE PROJECTION</td><td rowspan="2">DRAWN BY JSCHAFER</td><td rowspan="10">DATE 2014/01/24</td><td rowspan="10">TITLE TEN60 RECEPT ASSY POWER/SIGNAL MIXED PANEL-TO-BOARD</td><td rowspan="10">APPROVED BY BPISZCZOR</td><td rowspan="10">DATE 2016/10/03</td><td rowspan="10">MATERIAL NO. SEE CHART</td><td rowspan="10">DOCUMENT NO. SD-172512-001</td><td rowspan="10">SHEET NO. 1 OF 1</td></tr><tr></tr><tr><td colspan="4"></td><td colspan="2">4 PLACES ± --- ± ---</td><td colspan="2">mm</td><td colspan="2">INCH</td><td rowspan="8">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td><td colspan="8"></td></tr><tr><td colspan="4"></td><td colspan="2">3 PLACES ± --- ± ---</td><td colspan="2">mm</td><td colspan="3">INCH</td><td colspan="8"></td></tr><tr><td colspan="4"></td><td colspan="2">2 PLACES ± 0.13 ± ---</td><td colspan="2">mm</td><td colspan="3">INCH</td><td colspan="8"></td></tr><tr><td colspan="4"></td><td colspan="2">1 PLACE ± 0.25 ± ---</td><td colspan="2">mm</td><td colspan="3">INCH</td><td colspan="8"></td></tr><tr><td colspan="4"></td><td colspan="2">0 PLACE ± --- ± ---</td><td colspan="2">mm</td><td colspan="3">INCH</td><td colspan="8"></td></tr><tr><td colspan="4"></td><td colspan="2">ANGULAR ± 1/2°</td><td colspan="2"></td><td colspan="3"></td><td colspan="8"></td></tr><tr><td colspan="4"></td><td colspan="2">DRAFT WHERE APPLICABLE</td><td colspan="2"></td><td colspan="3"></td><td colspan="8"></td></tr><tr><td colspan="4"></td><td colspan="2">MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2"></td><td colspan="3"></td><td colspan="8"></td></tr></table>																CHG TRMNL P/N EC NO: UCP2016-4071 DRAWN: JSCHAFER CHKD: APPR: BPISZCZOR	2016/04/18 2016/10/03	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1.5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	DRAWN BY JSCHAFER	DATE 2014/01/24	TITLE TEN60 RECEPT ASSY POWER/SIGNAL MIXED PANEL-TO-BOARD	APPROVED BY BPISZCZOR	DATE 2016/10/03	MATERIAL NO. SEE CHART	DOCUMENT NO. SD-172512-001	SHEET NO. 1 OF 1					4 PLACES ± --- ± ---		mm		INCH		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													3 PLACES ± --- ± ---		mm		INCH															2 PLACES ± 0.13 ± ---		mm		INCH															1 PLACE ± 0.25 ± ---		mm		INCH															0 PLACE ± --- ± ---		mm		INCH															ANGULAR ± 1/2°																			DRAFT WHERE APPLICABLE																			MUST REMAIN WITHIN DIMENSIONS														
CHG TRMNL P/N EC NO: UCP2016-4071 DRAWN: JSCHAFER CHKD: APPR: BPISZCZOR	2016/04/18 2016/10/03	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1.5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	DRAWN BY JSCHAFER	DATE 2014/01/24	TITLE TEN60 RECEPT ASSY POWER/SIGNAL MIXED PANEL-TO-BOARD	APPROVED BY BPISZCZOR	DATE 2016/10/03	MATERIAL NO. SEE CHART	DOCUMENT NO. SD-172512-001	SHEET NO. 1 OF 1																																																																																																																																																																																																
				4 PLACES ± --- ± ---		mm		INCH		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																																																																																																								
				3 PLACES ± --- ± ---		mm		INCH																																																																																																																																																																																																										
				2 PLACES ± 0.13 ± ---		mm		INCH																																																																																																																																																																																																										
				1 PLACE ± 0.25 ± ---		mm		INCH																																																																																																																																																																																																										
				0 PLACE ± --- ± ---		mm		INCH																																																																																																																																																																																																										
				ANGULAR ± 1/2°																																																																																																																																																																																																														
				DRAFT WHERE APPLICABLE																																																																																																																																																																																																														
				MUST REMAIN WITHIN DIMENSIONS																																																																																																																																																																																																														