

SERIES 84LS

Sealed, Low Profile



FEATURES

- Waterproof Silicone Rubber
- Easily Customized Legends
- Audible, Tactile Contacts
- Low Contact Resistance
- Optional RFI/EMI Shielding
- 3,000,000 Operations per Button




DESCRIPTION



The Series 84LS is the low profile version of Grayhill's popular Series 84S sealed keypads. These keypads are legendary by epoxy ink printing the rubber key tops. Custom legends and colors are available at a nominal cost. The Series 84LS is offered with a choice of matrix or single pole/common bus circuitries and EMI shielding.

DIMENSIONS In inches (and millimeters)



3x4 Keyboard





1x4 Keyboard




Matrix Output




Single Pole/Common Bus



Single Pole/Common Bus



DIMENSIONS In inches (and millimeters)



Keyboards and Keypads

CODE AND TRUTH TABLES

The chart indicates the relationship of the terminal pins to each key switch. The dot indicates a closed switch. Terminals are identified on the keyboard.

4 Button Keypads

BUTTON LOCATION	CODES			
	PINS			
1	•			•
2		•		
3			•	
4				•
	A	B	C	D
	TERMINAL LOCATION			

12 Button Keypads

BUTTON LOCATION	CODES											
	Matrix						Single Pole/Common Bus					
1	•						•					
2		•										•
3			•									•
4				•								•
5					•							•
6						•						•
7							•					•
8								•				•
9									•			•
10										•		•
11											•	•
12												•
	C	B	A	G	F	E	D	E	C	B	F	D
	TERMINAL LOCATION											

16 Button Keypads

BUTTON LOCATION	CODES															
	Matrix								Single Pole/Common Bus							
1	•								•							
2		•														•
3			•													•
4				•												•
5					•											•
6						•										•
7							•									•
8								•								•
9									•							•
10										•						•
11											•					•
12												•				•
13													•			•
14														•		•
15															•	•
16																•
	A	B	C	D	E	F	G	H	D	B	A	C	H	F	E	G
	TERMINAL LOCATION															

SPECIFICATIONS

Rating Criteria

Rating at 24 Vdc: ≤ 10 milliamps resistive
Contact Bounce: 4 milliseconds maximum at make; 10 milliseconds, at break
Contact Resistance: MOS, TTL, and DTL compatible. (10 ohms maximum)
Operating Temperature: -55°C to 85°C

Life Expectancy: 3 million operations/button
Insulation Resistance: 1,000 megohms

Operating Features


Pre-Travel: .030 inches minimum
Operating Force: 20 ± 4 ounces
Humidity: 0 to 98% (no condensation)
Minimum Push Out Force Per Pin: 5 pounds

Materials and Finishes

Terminal Pins: Copper alloy CDA 725
PC Board: FR-4 glass cloth epoxy
Dome Retainer/Rear Seal Sheet: Polyester
Mounting Studs: Phosphor bronze
Optional Hex Nut: Stainless steel, passivated
Optional EMI Shield: Aluminum foil
Keypad: Silicone rubber

Shielding Effectiveness

Results shown are typical for a standard Grayhill Series 84LS Keyboard. A conductive gasket will generally increase the shielding, depending on the size and shape of the gasket and its material. Data derived for E-Field Radiation.



Frequency MHz	Rating in dB
0.1	66.2
10	94.8
100	89.0
400	70.6
800	42.5
2,000	39.5
6,000	32.6
10,000	45.2
18,000	42.2

Test Method:

Measurements were made with the keyboard mounted to a brass plate, which in turn was mounted to a shielded enclosure containing the receiving equipment. A signal generator

provided the frequency source that was radiated from the transmitting antenna to the enclosed receiving antenna. The spacing between antennas was maintained constant throughout the frequency range. The effectiveness rating is determined by establishing a reference reading without obstruction between the two antennas and determining the difference between that reading and the test setup reading.


Note:

When measured in actual equipment, shielding effectiveness is determined by many factors. This method accurately represents the shielding effectiveness of the Grayhill Series 84LS under ideal test conditions.


STANDARD LEGENDS

Available through Grayhill Distributors


To order one of the configurations below, use the dash number shown here; select the keypad size and code, and order the part number with the appropriate legend dash number.




-112



-014



-113



-016

301

302

CUSTOM LEGENDS

Any reasonable legend can be printed in the key area. Fax a sketch of your requirements to Grayhill. Printing and symbols will be coordinated in keeping with concepts of good design. Or, if required, the details of your

submitted artwork will be matched as closely as possible. Allow 3 to 4 weeks for custom legend delivery. A nominal charge, depending on the total quantity of keypads ordered and the complexity of the legend, will be assessed.

HEADER CONNECTORS

Compatible with:

Samtec, Inc. Header Series BCS, BSW, CES, ESW, ESQ, SLW, SSW, SSQ, IDSS and IDSD or equivalent.

ORDERING INFORMATION

84LS-AC2-113-N

Grayhill Series Number

Shielded or Non-Shielded Option

Size Option

Circuitry Option

Mounting Nut Option

Standard Legend Choices

S = Shielded

SN = Non-Shielded

A = 3x4 B = 4x4 C = 1x4

B2 = Matrix in-line pins C2 = Single pole/common bus, in-line pins

N = Provided with hex nuts for mounting

Blank = Nuts not provided

3x4 Size, choose -112 or -113

4x4 Size, choose -014 or -016

1x4 Size, choose -301 or -302

Available from your local Grayhill Distributor.

For prices and discounts, contact a local Sales Office, an authorized local distributor or Grayhill.