



Features:

- ✓ Allows cables with F style connector to attach quickly and reliably to BNC connectors.
- ✓ Adapter is precision machined (not die-cast) from brass.
- ✓ Adapter utilizes gold plated center contacts for superior signal transfer.

Materials:

Connector Body	Nickel plated brass
Pin Contact	Gold plated brass
Socket Contact	Gold plated phosphor bronze
Insulator (BNC side)	Delrin
Insulator (F side)	Polybutylene Terephthalate
Rubber Gasket	Silicone Rubber

Ratings:

Impedance:	75 Ohms
Frequency:	0 to 500 MHz
VSWR:	1.5 max
Contact Resistance:	3 Milliohms max.
Voltage	* 500 V
Insulation Resistance:	5,000 Megohms min.
Insertions:	500
Temperature:	-40 to +65 C

* *Hands free testing* in controlled voltage environment: For CE compliance: not intended for hand held use at voltages above 33 Vrms / 70 Vdc.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360 Technical Assistance: 800-241-2060
For "Where to Buy" information, visit the Pomona web site at www.pomonaelectronics.com