


# Micro-displacement Sensor Z4D-B01

## ■ Dimensions

**Note:** All units are in millimeters unless otherwise indicated.



Recommended Mating Connectors:  
Tyco Electronics AMP  
175778-4 (crimp connector)  
173977-4 (press-fit connector)

## ■ Features

- Easier control enabled by built-in processor circuit.
- Resolution:  $\pm 10 \mu\text{m}$ .
- Operating area:  $6.5 \pm 1 \text{ mm}$ .
- Adapts well to changes in reflection factor using division processing.

| Pin no. | Remarks  |
|---------|----------|
| 1       | PLS      |
| 2       | $V_{CC}$ |
| 3       | OUT      |
| 4       | GND      |

Unless otherwise specified, the tolerances are as shown below.

| Dimensions               | Tolerance   |
|--------------------------|-------------|
| 3 mm max.                | $\pm 0.3$   |
| $3 < \text{mm} \leq 6$   | $\pm 0.375$ |
| $6 < \text{mm} \leq 10$  | $\pm 0.45$  |
| $10 < \text{mm} \leq 18$ | $\pm 0.55$  |
| $18 < \text{mm} \leq 30$ | $\pm 0.65$  |
| $30 < \text{mm} \leq 50$ | $\pm 0.8$   |

## ■ Absolute Maximum Ratings ( $T_a = 25^\circ\text{C}$ )

| Item                                    | Symbol    | Value     | Unit             | Remarks                  |
|-----------------------------------------|-----------|-----------|------------------|--------------------------|
| Supply voltage                          | $V_{CC}$  | 7         | VDC              | ---                      |
| LED pulse light emission control signal | PLS       | 7         | VDC              | LED                      |
| LED light emission pulse                | $t_{FP}$  | 100       | ms               | ---                      |
| Operating temperature                   | $T_{opr}$ | -10 to 65 | $^\circ\text{C}$ | No icing or condensation |
| Storage temperature                     | $T_{stg}$ | -25 to 80 | $^\circ\text{C}$ | ---                      |

## ■ Electrical and Optical Characteristics ( $T_a = -10^\circ\text{C}$ to $65^\circ\text{C}$ )

| Item                                    | Symbol   | Rated value                     | Remarks                      |
|-----------------------------------------|----------|---------------------------------|------------------------------|
| Supply voltage                          | $V_{CC}$ | 5 VDC $\pm 10\%$                | Ripple (p-p): 10 mV p-p max. |
| Output voltage                          | OUT      | 0.2 VDC to ( $V_{CC} - 0.3$ ) V | (see note 1)                 |
| Response time                           | $t_r$    | 100 $\mu\text{s}$ max.          | (see note 2)                 |
| LED pulse light emission control signal | PLS      | 3.5 VDC to $V_{CC}$             | (see note 3)                 |

- Note:**
1. Load impedance (between OUT-GND) is set at more than 10 k $\Omega$ .
  2. The time for output voltage to rise from 10% to 90% of the full output range.
  3. Apply the voltage ranging from 3.5 V to  $V_{CC}$  on the LED pulse light emission control signal terminal. In this case, a maximum of 2 mA (TYP 1 mA) current is sunk.

## ■ Characteristics (Ta = -10°C to 65°C)

Object: N8.5 Munsell paper with a reflection factor of 70%.

| Item                               | Value                     |
|------------------------------------|---------------------------|
| Operating area (see note 1)        | 6.5 ±1 mm                 |
| Sensitivity variation (see note 2) | -1.4 mV/μm ±10% max.      |
| Resolution (see note 3)            | ±10 μm max. (Ta = 25°C)   |
| Linearity (see note 4)             | 2% F.S. (full scale) max. |

**Note:** 1. Distance from the mounting reference plane.

2. "Sensitivity" is defined as "inclination of divided output line" and the variation value between individual products of fluctuating divided output voltage per unit length.


$$\text{Sensitivity} = \frac{V_2 - V_0}{2000} \quad (\text{mV/mm})$$

Where V0: Output voltage when d = 5.5 mm

V2: Output voltage when d = 7.5 mm

d: Distance from reference mounting plane to an object.

3. Value of electrical noise range of divided output signal converted to distance under the following conditions.



(1) Ripple noise of power supply: 10 mV p-p max.

(2) Sampling time of the sample and hold circuit: 50 μsec

(3) Distance to object: Distance from the reference mounting plane is 6.5 mm ±1 mm.

\*\* When the testing conditions are deviated from the above conditions, resolution changes. For details, please consult OMRON sales representative.


4. The peak-to-peak value of the output error from the ideal line.

Calculation, based on a linearity of 2% F.S., is as follows:


(1) The conversion value based on the full scale distance: 2 mm × 0.02 = 0.04 mm (40 μm)

(2) The conversion value based on the output voltage: 1.4 mV/μm × 40 μm = 56 mV


(When the product sensitivity variation is 1.4 mV/μm.)



## ■ Circuit Diagram



■ Engineering Data



■ Typical Application

Paper thickness detection for printers

