

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0039000067

Status:

Active

Overview:

Mini-Fit Jr.™ Power Connectors

Description:

Mini-Fit® Male Crimp Terminal, Tin (Sn) over Phosphor Bronze, 22-28 AWG, Reel

Documents:

Drawing (PDF)

Product Specification PS-5556-002 (PDF)

Packaging Specification PK-5558-001 (PDF)

Test Summary TS-5556-002 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Crimp Quality Equipment

Overview

Product Name

UPC

Crimp Terminals

5558

Power

Yes

Mini-Fit Jr.™ Power Connectors

Mini-Fit®

800754394024

Physical

Durability (mating cycles max)

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Plating min - Mating

Plating min - Termination

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

30

Male

Phosphor Bronze

Tin

Tin

0.120/g

Reel

0.889µm

0.914µm

Crimp or Compression

0.90-1.80mm

22, 24, 26, 28

N/A

Electrical

Current - Maximum per Contact

Voltage - Maximum

9.0A

600V

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Old Part Number

5558-PBT2

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

Test Summary

PK-5558-001

PS-5556-002

SD-5558****

TS-5556-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Contains SVHC(2015

June 15): No

Halogen-Free

Status

Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the Contact Us section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

5558 Series

Mates With

5556 Mini-Fit® Crimp Terminal

Use With

5559 Mini-Fit Jr.™ Plug Housing, 30068

Mini-Fit® TPA Plug Housing, 42475 Mini-

Fit® BMI Plug Housing

Application Tooling | FAQ

Tooling specifications and manuals are

found by selecting the products below.

Crimp Height Specifications are then

contained in the Application Tooling

Specification document.

Global

Description

Product #

FineAdjust™

0639020200

Applicator for

Insulation OD

1.10-1.30mm - 22-28	
AWG	
FineAdjust™	<u>0639002700</u>
Applicator for	
Insulation OD	
1.30-1.50mm, 22-28	
AWG Wire	
Extraction Tool	<u>0011030044</u>
Hand Crimp Tool for	<u>0638191000</u>
Crimp Terminals	
FineAdjust™	<u>0639023800</u>
Applicator for	
Insulation OD	
0.95-1.08mm - 22-28	
AWG	
T2 Terminator™	<u>0639102700</u>
for insulation OD	
1.30-1.50mm - 22-28	
AWG	
T2 Terminator™	<u>0639120200</u>
for insulation OD	
1.10-1.30mm - 22-28	
AWG	
T2 Terminator™	<u>0639123800</u>
for insulation OD	
0.95-1.08mm - 22-28	
AWG	
Japan	
Description	Product #
Applicator for M211A	<u>0570383000</u>
Bench Press, 22-28	
AWG Wire	

This document was generated on 09/09/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION