






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	M1	REVISED PER ECO-11-005027	14MAR11	RK	HMR
	N	REVISED PER ECR-16-017870	20APR2017	BDA	MZ



OBSOLETE	M3 X 0.5	NO	208489-4
OBSOLETE	.120	YES	208489-2
	.120	NO	208489-1
	H	PERIPHERAL SEAL	PART NUMBER

NOTES:

- 208489-1 MATES WITH AMP PLUG 208488-1 OR -3. 208489-2 MATES WITH 208488-1 ONLY.
- THIS RECEPTACLE ACCEPTS SIXTEEN (16) MULTIMATE PIN CONTACTS. MAXIMUM WIRE INSULATION DIAMETER = .105.
- AMP PART NUMBER AND DATE CODE LOCATED ON EDGE OF FLANGE.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.LEE BG 6-28-91	TE Connectivity		
DIMENSIONS: INCHES		CHK W.G.LENKER 4-15-92			
		APVD K.BEAVER 4-15-92	NAME RECEPTACLE ASSEMBLY, STD SEX, SERIES 1, 22-16, CMC		
		PRODUCT SPEC 108-10040			
MATERIAL SEE CALLOUT		FINISH SEE CALLOUT	SIZE A2	CAGE CODE 00779	DRAWING NO C=208489
			WEIGHT -	RESTRICTED TO -	
			CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1
				REV N	