



T-25-13



1801 HURD DRIVE
IRVING, TEXAS 75038-4385
PHONE 214/580-1515
FAX 214/550-1309



LOGIC TRIACS 0.8-8 AMPS

General Description

Teccor's line of logic triacs includes devices with current capabilities through 8 Amperes. Voltage ranges are available from 200 to 600 Volts. This line features devices with guaranteed gate control in the second and fourth quadrant as well as control in the commonly used first and third quadrants. Four quadrant control devices form a group termed "logic triacs". They lend themselves to be controlled by digital circuitry where positive pulses must control AC current in both directions through the device.

The logic triac is a bidirectional AC switch and is gate controlled for either polarity of main terminal voltage. Its primary purpose is for AC switching and phase control applications such as motor speed controls, temperature modulation controls, and lighting controls.

A wide range of package variations are available. The plastic TO-92 and THERMOTAB® configurations feature Teccor's electrically isolated construction where the case or tab is internally isolated. Tape and reel capability for the TO-92 and SOT-89 is available.

Non-isolated plastic TO-202 packages are also available.

All Teccor triacs have glass passivated junctions. This glassing process prevents migration of contaminants and insures long term device reliability with parameter stability.

Variations of devices covered in this data sheet are available for custom design applications. Please consult factory for further information.

Features

- Electrically isolated packages
- Glass passivated junctions insure long device reliability and parameter stability
- Voltage capability—up to 600 Volts
- Surge capability—up to 80 Amps

TECCOR ELECTRONICS INC 24E D ■ 8872819 0001290 3 ■

LOGIC TRIACS 0.8-8 AMPS

T-25-13

IT RMS		Part Number				VDRM	IGT				IDRM		VTM		VGT	
RMS On-State Current Conduction Angle of 360° (11)	Amps	Isolated		Non-Isolated			Repetitive Peak Blocking Voltage (1)	DC Gate Trigger Current in Specific Operating Quadrants VD = 12 VDC RL = 60 Ω (3) (6)				Peak Off-State Current Gate Open VDRM = Max Rated Value (1)	Peak On-State Voltage at Max Rated RMS Current TC = 25°C (1) (4)	DC Gate Trigger Voltage VD = 12VDC RL = 60 Ω (2) (5)		
						Volts	mA				mA	Volts	Volts			
MAX		FOR DIMENSIONAL OUTLINE & PACKAGE VARIATIONS SEE PAGE 81				MIN	QI MAX	QII MAX	QIII MAX	QIV MAX	TC=25°C MAX	TC=100°C MAX	MAX	TC=100°C MIN	TC=25°C MAX	
0.8 Amp				L200U5		200	5	5	5	5	.01	0.1	1.6	0.2	2.0	
				L400U5		400	5	5	5	5	.01	0.1	1.6	0.2	2.0	
				L600U5		600	5	5	5	5	.01	0.1	1.6	0.2	2.0	
				L200U7		200	10	10	10	10	.01	0.1	1.6	0.2	2.0	
				L400U7		400	10	10	10	10	.01	0.1	1.6	0.2	2.0	
				L600U7		600	10	10	10	10	.01	0.1	1.6	0.2	2.0	
				L200U9		200	25	25	25	25	.01	0.1	1.6	0.2	2.0	
				L400U9		400	25	25	25	25	.01	0.1	1.6	0.2	2.0	
1.0 Amp				L600U9		600	25	25	25	25	.01	0.1	1.6	0.2	2.0	
	L201E3					200	3	3	3	3	.01	0.1	1.6	0.2	2.0	
	L401E3					400	3	3	3	3	.01	0.1	1.6	0.2	2.0	
	L601E3					600	3	3	3	3	.01	0.1	1.6	0.2	2.0	
	L201E5					200	5	5	5	5	.01	0.1	1.6	0.2	2.0	
	L401E5					400	5	5	5	5	.01	0.1	1.6	0.2	2.0	
	L601E5					600	5	5	5	5	.01	0.1	1.6	0.2	2.0	
	L201E7					200	5	5	5	5	.01	0.1	1.6	0.2	2.0	
	L401E7					400	10	10	10	10	.01	0.1	1.6	0.2	2.0	
	L601E7					600	10	10	10	10	.01	0.1	1.6	0.2	2.0	
	L201E9					200	10	10	10	10	.01	0.1	1.6	0.2	2.0	
	L401E9					400	25	25	25	25	.01	0.1	1.6	0.2	2.0	
4.0 Amps						600	25	25	25	25	.01	0.1	1.6	0.2	2.0	
		L2004L3		L2004F31		200	3	3	3	3	.01	0.2	1.6	0.2	2.0	
		L4004L3		L4004F31		400	3	3	3	3	.01	0.2	1.6	0.2	2.0	
		L6004L3		L6004F31		600	3	3	3	3	.01	0.2	1.6	0.2	2.0	
		L2004L5		L2004F51		200	5	5	5	5	.01	0.2	1.6	0.2	2.0	
		L4004L5		L4004F51		400	5	5	5	5	.01	0.2	1.6	0.2	2.0	
		L6004L5		L6004F51		600	5	5	5	5	.01	0.2	1.6	0.2	2.0	
		L2004L7		L2004F71		200	10	10	10	10	.01	0.2	1.6	0.2	2.0	
		L4004L7		L4004F71		400	10	10	10	10	.01	0.2	1.6	0.2	2.0	
		L6004L7		L6004F71		600	10	10	10	10	.01	0.2	1.6	0.2	2.0	
		L2004L9		L2004F91		200	25	25	25	25	.01	0.2	1.6	0.2	2.0	
		L4004L9		L4004F91		400	25	25	25	25	.01	0.2	1.6	0.2	2.0	
6.0 Amps				L6004F91		600	25	25	25	25	.01	0.2	1.6	0.2	2.0	
	L2006L6					200	5	5	5	5	.02	0.5	1.6	0.2	2.0	
	L4006L6					400	5	5	5	25	.02	0.5	1.6	0.2	2.0	
	L6006L6					600	5	5	5	25	.02	0.5	1.6	0.2	2.0	
	L2006L7					200	10	10	10	10	.02	0.5	1.6	0.2	2.0	
	L4006L7					400	10	10	10	10	.02	0.5	1.6	0.2	2.0	
	L6006L7					600	10	10	10	10	.02	0.5	1.6	0.2	2.0	
	L2006L9					200	25	25	25	25	.02	0.5	1.6	0.2	2.0	
8.0 Amps	L4006L9					400	25	25	25	25	.02	0.5	1.6	0.2	2.0	
	L6006L9					600	25	25	25	25	.02	0.5	1.6	0.2	2.0	
	L2008L6					200	5	5	5	25	.02	0.5	1.6	0.2	2.0	
	L4008L6					400	5	5	5	25	.02	0.5	1.6	0.2	2.0	
	L6008L6					600	5	5	5	25	.02	0.5	1.6	0.2	2.0	
	L2008L7					200	10	10	10	10	.02	0.5	1.6	0.2	2.0	
	L4008L7					400	10	10	10	10	.02	0.5	1.6	0.2	2.0	
	L6008L7					600	10	10	10	10	.02	0.5	1.6	0.2	2.0	
	L2008L9					200	25	25	25	25	.02	0.5	1.6	0.2	2.0	
	L4008L9					400	25	25	25	25	.02	0.5	1.6	0.2	2.0	
	L6008L9					600	25	25	25	25	.02	0.5	1.6	0.2	2.0	
						600	25	25	25	25	.02	0.5	1.6	0.2	2.0	

GENERAL NOTES

• All measurements are made with 50 Ω load

GENERAL NOTES

- All measurements are made with 60 Hz resistive load and at an ambient temperature of +25°C unless otherwise specified.
- Operating temperature range (T_J) is -65°C to +110°C for TO-92 and SOT-89 devices; -40°C to +110°C for all other devices.

- Storage temperature range (T_S) is -65°C to +150°C for TO-92 and SOT-89 devices; -40°C to +150°C for TO-202 devices; and -40°C to +125°C for TO-220 devices.
- Lead solder temperature is a maximum of 230°C for 10 seconds maximum at a minimum of 1/16" from case.
- The case temperature (T_C) is measured as shown on dimensional outline drawings. See "package dimensions" section of this catalog on page 81.

Electrical Specifications

I _H	I _{GTM}	P _{GM}	P _{G(AV)}	I _{TSM}		dv/dt(c)	dv/dt	I _{gt}	I _t	di/dt
Holding Current Gate Open Initial On-State Current = 200mA DC (1) (7)	Peak Gate Trigger Current (12)	Peak Gate Power Dissipation I _{GT} ≤ I _{GTM} (12)	Average Gate Power Dissipation	Peak One Cycle Surge (8) (10)		Critical Rate of Rise of Commutation Voltage at Rated V _{DRM} and I _T (RMS) Commutating di/dt = .54 Rated I _T (RMS)/msec. Gate Unenergized (1) (10)	Critical Rate of Rise of Off-State Voltage at Rated V _{DRM} Gate Open (1)	Gate Controlled Turn-On Time I _{GT} = 100mA 0.1 μs Rise Time	RMS Surge (Non-Repetitive) On-State Current For period of 8.3 msec for Fusing	Maximum Rate of Change of On-State Current I _{GT} = 50 mA With 0.1 μs Rise Time
mA	Amps	Watts	Watts	Amps		Volts/μs	Volts/μs T _C = 100°C	μs	Amps ² sec.	Amps/μs
MAX				60Hz	50Hz	MIN	MIN	MAX		
10	1.0	10	0.2	10	8.3	1	10	2.5	0.41	20
10	1.0	10	0.2	10	8.3	1	10	2.5	0.41	20
10	1.0	10	0.2	10	8.3	1	5	2.5	0.41	20
15	1.0	10	0.2	10	8.3	1	20	2.5	0.41	20
15	1.0	10	0.2	10	8.3	1	20	2.5	0.41	20
15	1.0	10	0.2	10	8.3	1	10	2.5	0.41	20
25	1.0	10	0.2	10	8.3	1	25	3.0	0.41	20
25	1.0	10	0.2	10	8.3	1	25	3.0	0.41	20
25	1.0	10	0.2	10	8.3	1	15	3.0	0.41	20
5	1.0	10	0.2	20	16.7	1	10	2.5	1.6	20
5	1.0	10	0.2	20	16.7	1	10	2.5	1.6	20
5	1.0	10	0.2	20	16.7	1	5	2.5	1.6	20
10	1.0	10	0.2	20	16.7	1	10	2.5	1.6	20
10	1.0	10	0.2	20	16.7	1	10	2.5	1.6	20
10	1.0	10	0.2	20	16.7	1	5	2.5	1.6	20
15	1.0	10	0.2	20	16.7	1	20	2.5	1.6	20
15	1.0	10	0.2	20	16.7	1	20	2.5	1.6	20
15	1.0	10	0.2	20	16.7	1	10	2.5	1.6	20
25	1.0	10	0.2	20	16.7	1	25	3.0	1.6	20
25	1.0	10	0.2	20	16.7	1	25	3.0	1.6	20
25	1.0	10	0.2	20	16.7	1	15	3.0	1.6	20
5	1.2	15	0.3	40	33	1	10	2.5	6.6	50
5	1.2	15	0.3	40	33	1	10	2.5	6.6	50
5	1.2	15	0.3	40	33	1	5	2.5	6.6	50
10	1.2	15	0.3	40	33	1	10	2.5	6.6	50
10	1.2	15	0.3	40	33	1	10	2.5	6.6	50
10	1.2	15	0.3	40	33	1	5	2.5	6.6	50
15	1.2	15	0.3	40	33	1	20	2.5	6.6	50
15	1.2	15	0.3	40	33	1	20	2.5	6.6	50
15	1.2	15	0.3	40	33	1	10	2.5	6.6	50
25	1.2	15	0.3	40	33	1	25	3.0	6.6	50
25	1.2	15	0.3	40	33	1	25	3.0	6.6	50
25	1.2	15	0.3	40	33	1	15	3.0	6.6	50
15	1.6	18	0.4	60	50	2	30	2.5	15.0	70
15	1.6	18	0.4	60	50	2	25	2.5	15.0	70
15	1.6	18	0.4	60	50	2	10	2.5	15.0	70
15	1.6	18	0.4	60	50	2	30	2.5	15.0	70
15	1.6	18	0.4	60	50	2	25	2.5	15.0	70
15	1.6	18	0.4	60	50	2	15	2.5	15.0	70
30	1.6	18	0.4	60	50	2	40	3.0	15.0	70
30	1.6	18	0.4	60	50	2	30	3.0	15.0	70
30	1.6	18	0.4	60	50	2	20	3.0	15.0	70
15	1.6	18	0.4	80	65	2	30	2.5	26.5	70
15	1.6	18	0.4	80	65	2	25	2.5	26.5	70
15	1.6	18	0.4	80	65	2	10	2.5	26.5	70
15	1.6	18	0.4	80	65	2	30	2.5	26.5	70
15	1.6	18	0.4	80	65	2	25	2.5	26.5	70
15	1.6	18	0.4	80	65	2	15	2.5	26.5	70
30	1.6	18	0.4	80	65	2	40	3.0	26.5	70
30	1.6	18	0.4	80	65	2	30	3.0	26.5	70
30	1.6	18	0.4	80	65	2	20	3.0	26.5	70

NOTES TO ELECTRICAL SPECIFICATIONS

- For either polarity of MT2 with reference to MT1 terminal
- For either polarity of gate voltage V_{GT} with reference to MT1 terminal.
- See definition of quadrants and gate characteristics.
- See Figure 3 for I_T vs V_T
- See Figure 5 for V_{GT} vs T_C
- See Figure 6 for I_{GT} vs T_C

- See Figure 4 for I_H vs T_C
- See Figure 8 for surge rating with specific durations
- See Figure 7 for I_{gt} vs I_{GT}
- See Figures 2A & 2B for maximum allowable case temperature @ maximum rated current
- See Figure 1, 2A & 2B for T_A or T_C vs I_T (RMS)
- Pulse width ≤ 3μsec

LOGIC TRIACS 0.8-8 AMPS


GATE CHARACTERISTICS

Teccor triacs may be gated with in-phase signals (using standard AC line) in which quadrants I & III are used, or by applying unipolar pulses (gate always positive or negative) where if a negative pulse is applied quadrants II and III are used, and quadrants I & IV are used when a positive pulse is applied.

ELECTRICAL ISOLATION

Most Teccor isolated triac packages will withstand a minimum high potential test of 2500 VAC RMS from leads to case over the device's operating temperature range. See isolation table for standard and optional isolation ratings.

DEFINITION OF QUADRANTS



THERMAL RESISTANCE (STEADY STATE) JUNCTION TO CASE & JUNCTION TO AMBIENT

$R_{\theta JC} / R_{\theta JA} \text{ } ^\circ\text{C/W (TYP)}$

TYPE	 PLASTIC TO-92	 SOT-89	 TO-202AB TYPE 1	 TO-220AB THERMOTAB	 TO-202AB TYPE 2
0.8 Amp		30			
1.0 Amp	50/105				
4.0 Amp			3.5/45	3.6/50	6.0/70
6.0 Amp				3.3	
8.0 Amp				2.8	

ELECTRICAL ISOLATION FROM LEADS TO CASE

U.L. RECOGNIZED FILE #E71639

TYPE VAC (RMS)	TO-92	TO-220AB THERMOTAB
1600	Standard	—
2500	No	Standard
4000	No	Optional*

*For 4000V Isolation Use V Suffix

TECCOR ELECTRONICS INC 24E D ■ 8872819 0001293 9 ■ T-25-13

LOGIC TRIACS 0.8-8 AMPS

FIGURE 1 — Maximum Allowable Ambient Temperature vs On-State Current




FIGURE 2A — Maximum Allowable Case Temperature vs On-State Current




FIGURE 2B — Maximum Allowable Case Temperature vs On-State Current




FIGURE 3 — On-State Current vs On-State Voltage (Typical)




FIGURE 4 — Normalized DC Holding Current vs Case Temperature




FIGURE 5 — Normalized DC Gate Trigger Voltage for All Quadrants vs Case Temperature




FIGURE 6 — Normalized DC Gate Trigger Current for All Quadrants vs Case Temperature




FIGURE 7—Turn-On Time vs Gate Trigger Current (Typical)




FIGURE 8—Peak Surge Current vs Surge Current Duration




FIGURE 9A — Power Dissipation (Typ.) vs RMS On-State Current




FIGURE 9B — Power Dissipation (Typ.) vs RMS On-State Current

