

SURFACE MOUNT RECTIFIERS

VOLTAGE RANGE: 50 --- 600 V
CURRENT: 3.0 A


FEATURES

- ◇ Low cost
- ◇ Low leakage
- ◇ Low forward voltage drop
- ◇ High current capability
- ◇ Easily cleaned with alcohol, Isopropanol and similar solvents
- ◇ The plastic material carries U/L recognition 94V-0

MECHANICAL DATA

- ◇ Case: JEDEC DO-214AA, molded plastic
- ◇ Terminals: Solderable per MIL-STD-202, Method 208
- ◇ Polarity: Color band denotes cathode
- ◇ Weight: 0.003 ounces, 0.093 grams
- ◇ Mounting position: Any

DO - 214AA(SMB)



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate by 20%.

		ER3AB	ER3BB	ER3CB	ER3DB	ER3EB	ER3GB	ER3JB	UNITS
Maximum recurrent peak reverse voltage	V_{RRM}	50	100	150	200	300	400	600	V
Maximum RMS voltage	V_{RMS}	35	70	105	140	210	280	420	V
Maximum DC blocking voltage	V_{DC}	50	100	150	200	300	400	600	V
Maximum average forward rectified current @ $T_A = 75^\circ\text{C}$	$I_{F(AV)}$	3.0							A
Peak forward surge current 8.3ms single half-sine-wave superimposed on rated load @ $T_J = 125^\circ\text{C}$	I_{FSM}	100							A
Maximum instantaneous forward voltage @ 3.0A	V_F	0.95				1.25	1.7		V
Maximum reverse current @ $T_A = 25^\circ\text{C}$ at rated DC blocking voltage @ $T_A = 125^\circ\text{C}$	I_R	5.0 300							μA
Maximum reverse recovery time (Note 1)	t_{rr}	35							ns
Typical junction capacitance (Note 2)	C_J	95							pF
Typical thermal resistance (Note 3)	$R_{\theta JA}$	40							$^\circ\text{C/W}$
Operating junction temperature range	T_J	- 55 ----- + 150							$^\circ\text{C}$
Storage temperature range	T_{STG}	- 55 ----- + 150							$^\circ\text{C}$


NOTE: 1. Measured with $I_F = 0.5\text{A}$, $I_R = 1\text{A}$, $t_{rr} = 0.25\text{A}$.

2. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.


3. Thermal resistance junction to ambient.

www.galaxycn.com

FIG.1 -- TEST CIRCUIT DIAGRAM AND REVERSE RECOVERY TIME CHARACTERISTIC



NOTES: 1. RISE TIME = 7ns MAX. INPUT IMPEDANCE = $1M\Omega$. 22pF.
2. RISE TIME = 10ns MAX. SOURCE IMPEDANCE = 50 Ω .



SET TIME BASE FOR 10 ns/cm

FIG.2 -- TYPICAL FORWARD CHARACTERISTIC




FIG.3 -- FORWARD DERATING CURVE




FIG.4 -- TYPICAL JUNCTION CAPACITANCE




FIG.5 -- PEAK FORWARD SURGE CURRENT




FIG.6 -- TYPICAL REVERSE CHARACTERISTICS

