







POLARIZATION MARKING


1

2

2 APPLICATION FIGURE



3 RECOMMENDED PATTERN



PART No.	CODE No.	NUMBER OF CONTACTS	A	B	C
DF13- 2P-1.25DSA(20)	CL536-0101-9-20	2	1.25	3.15	4.15
DF13- 3P-1.25DSA(20)	CL536-0102-1-20	3	2.5	4.4	5.4
DF13- 4P-1.25DSA(20)	CL536-0103-4-20	4	3.75	5.65	6.65
DF13- 5P-1.25DSA(20)	CL536-0104-7-20	5	5	6.9	7.9
DF13- 6P-1.25DSA(20)	CL536-0105-0-20	6	6.25	8.15	9.15
DF13- 7P-1.25DSA(20)	CL536-0106-2-20	7	7.5	9.4	10.4
DF13- 8P-1.25DSA(20)	CL536-0107-5-20	8	8.75	10.65	11.65
DF13- 9P-1.25DSA(20)	CL536-0108-8-20	9	10	11.9	12.9
DF13-10P-1.25DSA(20)	CL536-0109-0-20	10	11.25	13.15	14.15
DF13-11P-1.25DSA(20)	CL536-0110-0-20	11	12.5	14.4	15.4
DF13-12P-1.25DSA(20)	CL536-0111-2-20	12	13.75	15.65	16.65
DF13-13P-1.25DSA(20)	CL536-0112-5-20	13	15	16.9	17.9
DF13-14P-1.25DSA(20)	CL536-0113-8-20	14	16.25	18.15	19.15
DF13-15P-1.25DSA(20)	CL536-0114-0-20	15	17.5	19.4	20.4

- 1 WHEN THIS CONNECTOR HAS TWO OR THREE CONTACTS, THE LOCK OF CONNECTOR SHALL BE SET AT THE CENTER OF HOUSING. IN CASE THAT THE NUMBER OF CONTACTS IS MORE THAN FOUR, THE TWO LOCKS SHALL BE SET IN ACCORDANCE WITH THE DRAWINGS.
- 2 WHEN THIS CONNECTOR MATES WITH DF13-S-1.25C, THE MATING LENGTH IS 5.3mm.
- 3 RECOMMENDED DIP POST DIA. : $\phi 0.6 \pm 0.03$

2	BRASS	SURFACE: TIN PLATED $1\mu\text{m min.}$	4	STYRENIC-BASED ELASTOMERS	STOPPER, GREEN
1	POLYAMIDE	BEIGE(NATURAL), UL94V-0	3	PS	ELECTROSTATIC PROTECTION, CLEAR
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD)					
DRAWN		DESIGNED	CHECKED	APPROVED	RELEASED
T. Kumagawa		T. Kumagawa	H. Tanaka	J. Ono	
05.11.16		05.11.16	05.11.16	05.11.16	
DRAWING NO.		PART NO.			
EDC3-083673-05		DF13--P-1.25DSA(20)			
SCALE		CODE NO.			
5 : 1		CL536--			
UNITS					
mm					
HRS		HIROSE ELECTRIC CO., LTD			
5		6		7	
8		9		10	

