


227899
THIS DRAWING IS A CONTROLLED DOCUMENT

Restricted to: General Release

USED ON




Left Side

Connector(s): MT-RJ SECURE (No Pins)

Mode: MM

Housing Color: Blue

Geom. Spec: 115-1215



VIEW C-C
NOT TO SCALE

Fiber Path

Fiber A - ——— - B
Fiber B - ——— - A

Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Label 2 will not be present on any cable assembly less than 5 meters long.
- 3 Includes dust caps (not shown on print).
- 4 IL tested at 1300nm.

Right Side

Connector(s): SC-Duplex

Mode: MM

Housing Color: Beige

Geom. Spec: N/A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	B	Rev Per EC#	06-021324	9/13/2006	-	MK			
P	LTR	REVISION	RECORD	DATE	DN	APVD			

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Customer Print

DRN		Cable Assy Configurator		MATERIAL		HEAT TREAT	
CHK		Michael Kepko		-		-	
APVD		Michael Kepko					
NAME							
FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex							
SCALE		SIZE		DRAWING NO.		SHEET	
NTS		A2		C- 6278897		1 of 3	
						REV B	

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

Restricted to: General Release

USED ON

Part #	L (meters)	L (feet)	MT-RJ SECURE (No Pins), Blue		SC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-6278897-1	0.950 - 1.050	3.11 - 3.44	0.5	20	0.5	-
0-6278897-2	1.950 - 2.050	6.39 - 6.72	0.5	20	0.5	-
0-6278897-3	2.950 - 3.050	9.67 - 10.00	0.5	20	0.5	-
0-6278897-4	3.920 - 4.080	12.86 - 13.38	0.51	20	0.51	-
0-6278897-5	4.920 - 5.080	16.14 - 16.66	0.51	20	0.51	-
0-6278897-6	5.920 - 6.080	19.42 - 19.94	0.51	20	0.51	-
0-6278897-7	6.920 - 7.080	22.70 - 23.22	0.51	20	0.51	-
0-6278897-8	7.920 - 8.080	25.98 - 26.50	0.51	20	0.51	-
0-6278897-9	8.850 - 9.150	29.03 - 30.01	0.51	20	0.51	-
1-6278897-0	9.850 - 10.150	32.31 - 33.30	0.52	20	0.52	-
1-6278897-1	10.850 - 11.150	35.59 - 36.58	0.52	20	0.52	-
1-6278897-2	11.850 - 12.150	38.87 - 39.86	0.52	20	0.52	-
1-6278897-3	12.850 - 13.150	42.15 - 43.14	0.52	20	0.52	-
1-6278897-4	13.850 - 14.150	45.43 - 46.42	0.52	20	0.52	-
1-6278897-5	14.850 - 15.150	48.72 - 49.70	0.52	20	0.52	-
1-6278897-6	15.840 - 16.160	51.96 - 53.01	0.52	20	0.52	-
1-6278897-7	16.830 - 17.170	55.21 - 56.33	0.53	20	0.53	-
1-6278897-8	17.820 - 18.180	58.46 - 59.64	0.53	20	0.53	-
1-6278897-9	18.810 - 19.190	61.71 - 62.95	0.53	20	0.53	-
2-6278897-0	19.800 - 20.200	64.96 - 66.27	0.53	20	0.53	-
2-6278897-1	20.790 - 21.210	68.20 - 69.58	0.53	20	0.53	-
2-6278897-2	21.780 - 22.220	71.45 - 72.90	0.53	20	0.53	-
2-6278897-3	22.770 - 23.230	74.70 - 76.21	0.53	20	0.53	-
2-6278897-4	23.760 - 24.240	77.95 - 79.52	0.54	20	0.54	-
2-6278897-5	24.750 - 25.250	81.20 - 82.84	0.54	20	0.54	-
2-6278897-6	25.740 - 26.260	84.44 - 86.15	0.54	20	0.54	-
2-6278897-7	26.730 - 27.270	87.69 - 89.46	0.54	20	0.54	-
2-6278897-8	27.720 - 28.280	90.94 - 92.78	0.54	20	0.54	-
2-6278897-9	28.710 - 29.290	94.19 - 96.09	0.54	20	0.54	-
3-6278897-0	29.700 - 30.300	97.44 - 99.40	0.55	20	0.55	-
3-6278897-1	30.690 - 31.310	100.68 - 102.72	0.55	20	0.55	-
3-6278897-2	31.680 - 32.320	103.93 - 106.03	0.55	20	0.55	-
3-6278897-3	32.670 - 33.330	107.18 - 109.35	0.55	20	0.55	-
3-6278897-4	33.660 - 34.340	110.43 - 112.66	0.55	20	0.55	-
3-6278897-5	34.650 - 35.350	113.68 - 115.97	0.55	20	0.55	-
3-6278897-6	35.640 - 36.360	116.92 - 119.29	0.55	20	0.55	-
3-6278897-7	36.630 - 37.370	120.17 - 122.60	0.56	20	0.56	-
3-6278897-8	37.620 - 38.380	123.42 - 125.91	0.56	20	0.56	-
3-6278897-9	38.610 - 39.390	126.67 - 129.23	0.56	20	0.56	-
4-6278897-0	39.600 - 40.400	129.92 - 132.54	0.56	20	0.56	-
5-6278897-0	49.500 - 50.500	162.40 - 165.68	0.58	20	0.58	-

Qty	U of M	Description	Item No.
1	piece	DUST COVER, MT-RJ	1
1	piece	SPRING, MT-RJ, 3.8 DESIGN	2
1	piece	PIN KEEPER, 3.8MM	3
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	4
1	piece	CRIMP EYELET, MT-RJ	5
1	piece	MT-RJ Keyed Connector Housing - Blue	6
2	piece	LC, SC, FC Straight Boot, Beige	7
1	piece	MT-RJ FERRULE, THERMOPLAST,MM	8
2	piece	SC Simplex Housing, Beige	9
2	piece	2.5mm ferrule cover	10
AR	meter	2 fiber, 62.5/125, 1.8 mm, Twinzip, Orange, OFNR (Riser)	11
1	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	12
2	piece	SC Duplex Clip	13
2	piece	Eyelet/Shrink tube assembly - White	14
2	piece	CONN SUBASSY, MM, SC 1.6MM	15
2	piece	Trace Label	16

B	Rev Per EC#	06-021324	9/13/2006	-	MK
P	LTR	REVISION RECORD	DATE	DIN	APVD

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Customer Print

SCALE
NTS

SIZE
A2

DRAWING NO
C- 6278897

SHEET
2 of 3

REV
B

DIN
Cable Assy Configurator

OK
Michael Kepko

APVD
Michael Kepko

NAME
FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex

MATERIAL
-

HEAT TREAT
-

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

8 7 6 5 4 3 2 1

Label 1

Per specification 107-1645-1



Trace # - Bar Code

XXXXXXXXXXXXXXXXXX

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code

XXXXXXXXXXXXXXXXXX

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	B	Rev Per EC#	06-021324	9/13/2006	-	MK	
P	LTR	REVISION RECORD		DATE	DIN	APVD	

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
meters			
Ø	1 P.L.C.	±	-
□	2 P.L.C.	±	-
□	3 P.L.C.	±	-
□	4 P.L.C.	±	-

Customer Print

DIN		Cable Assy Configurator		MATERIAL	HEAT TREAT	
OK		Michael Kepko		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD		Michael Kepko				
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex						
SCALE	NTS	SIZE	A2	DRAWING NO	SHEET	REV
				C- 6278897	3 of 3	B

8

7

6

5

4

3

2

1