




RECOMMENDED P. C. B. PATTERN LAYOUT

NOTE:

1 MATERIAL:

CONTACTS: BRASS

INSULATOR: PBT+G.F UL 94V-0 BK

SHELL : BRASS

BACK CUP: PBT+G.F UL 94V-0 BK

2.MECHANICAL:

35N MAX.

WITHDRAWAL FORCE:10N MIN.

DURABILITY:1500 CYCLES MIN.

3.ELECTRICAL:

CURRENT-MAX[AMPS] 1.5A

VOLTAGE-MAX[VOLTS] 30V

WITHSTANDING VOLTAGE 500V AC

CONTACT RESISTANCE [OHMS] 30 MILLIOHMS MAX

INSULATION RESISTANCE [OHMS] 1000 MEGOHMS MIN

4.PLATING:

SEE TABLE NICKEL OVER ALL PLATING

5.ENVIRONMENTAL

TEMPERATURE RANGE -55°C~+85°C

-TOLERANCES- UNLESS OTHERWISE SPECIFIED				CnC Tech . LLC					
X.X ±0.38		X.X° ±3.00°				TITLE: USB 4P A/F DIP 180 30U"			
X.XX ±0.25		X.XX° ±1.00°		APPD:		PRODUCT NO: 1002-021-01000			
X.XXX ±0.13		X.XXX° ±0.500°		CHECK:		DATE	SCALE	UNIT	PAGE
				DRAW:		2010.06.17	1:1	mm	1 / 1