





- 1 0.38µm [.000015] MIN GOLD ON MATING AREA,
1.27µm [.000050] MIN BRIGHT TIN-LEAD ON CRIMP AREA, BOTH OVER
1.27µm [.000050] MIN NICKEL.
- 2 2.54µm [.000100] MIN BRIGHT TIN-LEAD, OVER
1.27µm [.000050] MIN NICKEL.
- 3 GOLD FLASH ON CRIMP AREA,
2.54µm [.000100] MIN TIN ON MATING AREA, BOTH OVER
1.27µm [.000050] MIN NICKEL.
- 4 0.38µm [.000015] MIN GOLD ON MATING AREA,
GOLD FLASH ON CRIMP AREA, BOTH OVER
1.27µm [.000050] MIN NICKEL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 6 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL

5 OBSOLETE	4	487923-5
3	6	487923-4
5 OBSOLETE	1	487923-3
	2	487923-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 3-7-90		 TE Connectivity					
		CHK R.STONE 3-8-90							
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONTACT, SOLDER TAB, .050 C/L —					
	0 PLC ± —		APVD —						
	1 PLC ± —		PRODUCT SPEC —						
	2 PLC ± 0.13[.005]		—						
	3 PLC ± —		APPLICATION SPEC —						
4 PLC ± —		—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL PHOSPHOR BRONZE		FINISH SEE TABLE		WEIGHT —		A2 00779 C=487923		—	
CUSTOMER DRAWING				SCALE 10:1		SHEET 1 of 1		REV D1	