

Distributed by:



**[www.Jameco.com](http://www.Jameco.com) ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.




SUBMINIATURE

## Basic Switch

SS

## Subminiature Basic Switch

- Economical, subminiature basic switch offers long service life (30 million operations minimum)
- All models are free from overtravel restrictions, permit easy setting
- Wide switching capacity range from microvoltage/current loads (1 mA at 5 VDC to high-capacity loads 10.1 A at 250 VAC)
- Standard operating force, low force or super-low force models available



## Ordering Information



## ■ STANDARD TYPE

Microvoltage/microcurrent load 0.1 A max. (Bifurcated crossbar contacts)

Actuator	Contact OF	Part Number				Soldered Terminal	Tab (#110) Terminal		
		PCB Terminal							
		Straight Vertical	Parallel to Left	Parallel to Right					
Pin plunger	25 g	<b>SS-01-ED</b>	—	—	<b>SS-01-E</b>	<b>SS-01-ET</b>			
	50 g	<b>SS-01-FD</b>	—	—	<b>SS-01-F</b>	<b>SS-01-FT</b>			
	150 g	<b>SS-01D</b>	<b>SS-01D1</b>	<b>SS-01D2</b>	<b>SS-01</b>	<b>SS-01T</b>			
Hinge lever	8 g	<b>SS-01GL-ED</b>	—	—	<b>SS-01GL-E</b>	<b>SS-01GL-ET</b>			
	16 g	<b>SS-01GL-FD</b>	—	—	<b>SS-01GL-F</b>	<b>SS-01GL-FT</b>			
	50 g	<b>SS-01GLD</b>	<b>SS-01GLD1</b>	<b>SS-01GLD2</b>	<b>SS-01GL</b>	<b>SS-01GLT</b>			
Simulated roller hinge lever	8 g	<b>SS-01GL13-ED</b>	—	—	<b>SS-01GL13-E</b>	<b>SS-01GL13-ET</b>			
	16 g	<b>SS-01GL13-FD</b>	—	—	<b>SS-01GL13-F</b>	<b>SS-01GL13-FT</b>			
	50 g	<b>SS-01GL13D</b>	—	—	<b>SS-01GL13</b>	<b>SS-01GL13T</b>			
Formed hinge lever	8 g	—	—	—	<b>SS-01GL14-E</b>	<b>SS-01GL14-ET</b>			
	16 g	<b>SS-01GL14-FD</b>	—	—	<b>SS-01GL14-F</b>	—			
	50 g	<b>SS-01GL14D</b>	—	—	<b>SS-01GL14</b>	<b>SS-01GL14T</b>			
Hinged roller lever	8 g	<b>SS-01GL2-ED</b>	—	—	<b>SS-01GL2-E</b>	<b>SS-01GL2-ET</b>			
	16 g	<b>SS-01GL2-FD</b>	—	—	<b>SS-01GL2-F</b>	<b>SS-01GL2-FT</b>			
	50 g	<b>SS-01GL2D</b>	—	—	<b>SS-01GL2</b>	<b>SS-01GL2T</b>			

## General-purpose 5 A max. (Standard rivet contacts)


Actuator	Contact OF	Part Number				Soldered Terminal	Tab (#110) Terminal		
		PCB Terminal							
		Straight Vertical	Parallel to Left	Parallel to Right					
Pin plunger	50 g	SS-5-FD	SS-5-FD1	SS-5-FD2	SS-5-F	SS-5-FT			
	150 g	SS-5D	SS-5D1	SS-5D2	SS-5	SS-5T			
Hinge lever	16 g	SS-5GL-FD	SS-5GL-FD1	SS-5GL-FD2	SS-5GL-F	SS-5GL-FT			
	50 g	SS-5GLD	SS-5GLD1	SS-5GLD2	SS-5GL	SS-5GLT			
Simulated roller hinge lever	16 g	SS-5GL13-FD	—	SS-5GL13-FD2	SS-5GL13-F	SS-5GL13-FT			
	50 g	SS-5GL13D	SS-5GL13D1	SS-5GL13D2	SS-5GL13	SS-5GL13T			
Formed hinge lever	16 g	SS-5GL14-FD	SS-5GL14-FD1	—	SS-5GL14-F	SS-5GL14-FT			
	50 g	SS-5GL14D	SS-5GL14D1	SS-5GL14D2	SS-5GL14	SS-5GL14T			
Hinged roller lever	16 g	SS-5GL2-FD	SS-5GL2-FD1	SS-5GL2-FD2	SS-5GL2-F	SS-5GL2-FT			
	50 g	SS-5GL2D	SS-5GL2D1	SS-5GL2D2	SS-5GL2	SS-5GL2T			

## General-purpose 10.1 A max. (Standard rivet contacts)


Actuator	Contact OF	Part Number				Soldered Terminal	Tab (#110) Terminal		
		PCB Terminal							
		Straight Vertical	Parallel to Left	Parallel to Right					
Pin plunger	150 g	SS-10D	—	—	SS-10	SS-10T			
Hinge lever	50 g	SS-10GLD	—	—	SS-10GL	SS-10GLT			
Simulated roller hinge lever	50 g	SS-10GL13D	—	—	SS-10GL13	SS-10GL13T			
Formed hinge lever	50 g	SS-10GL14D	—	—	SS-10GL14	SS-10GL14T			
Hinged roller lever	50 g	SS-10GL2D	—	—	SS-10GL2	SS-10GL2T			

## ■ CONTACT FORM


**SPDT**  
(common throughout the series)



**SPST-NO\***  
(standard models rated at 0.1 to 0.5 A)



**SPST-NC\***  
(standard models rated at 0.1 to 5 A)



Sealed lead wire terminal models have color-coded leads.

\* The normally open (SPST-NO) and normally closed (SPST-NC) types are not listed in the Ordering Information tables. Directly consult OMRON.

## Specifications

## Microvoltage/microcurrent load type

Contact form	General purpose/resistive load	
	Bifurcated crossbar contacts	
	NC	NO
125 VAC	0.1 A	0.1 A
30 VDC	0.1 A	0.1 A
Inrush current	1 A max.	1 A max.

**Standard type general purpose**

Switch series:	Rivet contacts									
	Resistive load				Lamp load		Inductive load		Motor load	
	SS-5		SS-10		SS-5 and SS-10		SS-5 and SS-10		SS-5 and SS-10	
Contact form	NC	NO	NC	NO	NC	NO	NC	NO	NC	NO
125 VAC	5 A	5 A	10.1 A	10.1 A	1.5 A	0.7 A	3 A	3 A	2.5 A	1.3 A
250 VAC	3 A	3 A	10.1 A	10.1 A	1 A	0.5 A	2 A	2 A	1.5 A	0.8 A
8 VDC	5 A	5 A	10.1 A	10.1 A	2 A	2 A	5 A	4 A	3 A	3 A
14 VDC	5 A	5 A	10.1 A	10.1 A	2 A	2 A	4 A	4 A	3 A	3 A
30 VDC	4 A	4 A	4 A	4 A	2 A	2 A	3 A	3 A	3 A	3 A
125 VDC	0.4 A	0.4 A	0.4 A	0.4 A	0.05 A	0.05 A	0.4 A	0.4 A	0.05 A	0.05 A
250 VDC	0.2 A	0.2 A	0.2 A	0.2 A	0.03 A	0.03 A	0.2 A	0.2 A	0.03 A	0.03 A
Inrush current	20 A max. 10 A max. 20 A max. 15 A max. (both non-inductive and inductive loads)									

Note: 1. The above current ratings are the values of the steady-state current.  
 2. Inductive load has a power factor of 0.4 min. (AC) and a time constant of 7 milliseconds max. (DC). The inductive load applicable to the SS-10 series must have a power factor of 0.75 min.  
 3. Lamp load has an inrush current of 10 times the steady-state current.  
 4. Motor load has an inrush current of 6 times the steady-state current.  
 5. If the switch is used in a DC circuit and is subjected to inrush current or surge, connect a surge suppressor across the switch.

**■ CONTACT RESISTANCE (mΩ max., initial)**

Contact rating:	SS-01□	SS-5□	SS-10□
	0.1 A	3 A or 5 A	10.1 A
Normal operating force models (SS-□)	50 mΩ	30 mΩ	30 mΩ
Low operating force models (SS-□-F)	100 mΩ	50 mΩ	—
Super-low operating force models (SS-□-E)	150 mΩ	—	—
Lead wire models (all OF types)	100 mΩ	50 mΩ	—


**Characteristics** \_\_\_\_\_

Switch type	General-purpose		
Operating speed (see note 3)	0.1 mm to 1 m/second (0.004 to 39.4 in/second)		
Operating frequency	Mechanical	400 operations per minute (pin plunger actuator type)	
	Electrical	60 operations per minute (pin plunger actuator type)	
Insulation resistance	100 MΩ at 500 VDC		
Dielectric strength	Crossbar contact type	600 VAC, 50/60 Hz for 1 minute (see note 1)	
	Others	1,000 VAC, 50/60 Hz for 1 minute between terminals of same polarity 1,500 VAC, 50/60 Hz for 1 minute between current-carrying parts and ground and between each terminal and noncurrent-carrying metal parts	
Vibration	10 to 55 Hz, 1.5 mm double amplitude		
Shock	Mechanical durability	Low-OF type	500 m/s <sup>2</sup> min. (approx. 50 g)
		Others	1,000 m/s <sup>2</sup> min. (approx. 100 g)
	Malfunction durability	Standard type	300 m/s <sup>2</sup> min. (approx. 30 g)
		Low-OF type	200 m/s <sup>2</sup> min. (approx. 20 g)
		Lever type at TTP	Contact gap, 1 ms max.
Ambient temperature	Operating	-25° to 85°C with no icing	
Humidity	85% RH max.		
Service life	Mechanical	30 million operations minimum (OT: rated value) (see note 4)	
	Electrical	200,000 operations minimum (rated load) (see note 2)	
Weight	Approx. 1.6 g pin plunger type		


Note: 1. SS-10 series only.  
 2. 50,000 operations minimum for the SS-10 series.  
 3. Applies to the pin plunger type (at the pin plunger or the lever type).  
 4. 10 million operations for the SS-10 series.  
 5. Data shown are of initial value.

## ■ CHARACTERISTIC DATA

**Mechanical service life**  
Standard type (SS-5, SS-10 series)



**Electrical service life**  
Standard type (SS-5 series)




## Dimensions

Unit: mm (inch)

### ■ STANDARD TYPE


**Pin plunger**  
**SS-01 (-E, -F)**  
**SS-5 (-F)**  
**SS-10**



Operating characteristics	Super-low force model SS-01-E	Low-force models SS-01-F SS-5-F	Standard models SS-01 SS-5	Standard model SS-10
OF max.	25 g	50 g	150 g	150 g
RF min.	2 g	4 g	25 g	25 g
PT max.	0.5 mm (0.020 in)	0.5 mm (0.020 in)	0.5 mm (0.020 in)	0.6 mm (0.024 in)
OT min.	0.5 mm (0.020 in)	0.5 mm (0.020 in)	0.5 mm (0.020 in)	0.4 mm (0.016 in)
MD max.	0.1 mm (0.004 in)	0.1 mm (0.004 in)	0.1 mm (0.004 in)	0.12 mm (0.005 in)
OP	$8.4 \pm 0.5$ mm (0.331 ± 0.020 in)			


Note: 1. Unless otherwise specified, a tolerance of  $\pm 0.4$  mm applies to all dimensions.  
2. Straight vertical PCB terminal models are shown above. Soldered terminal, Tab (#10) terminal, lead wire terminal, PCB terminal parallel to left and PCB terminal parallel to right are shown in the Terminals section.

**Hinge lever**  
**SS-01GL (-E, -F)**  
**SS-5GL (-F)**  
**SS-10GL**



Operating characteristics	Super-low force model SS-01GL-E	Low-force models SS-01GL-F SS-5GL-F	Standard models SS-01GL SS-5GL	Standard model SS-10GL
OF max.	8 g	16 g	50 g	50 g
RF min.	1 g	2 g	6 g	6 g
OT min.	1.2 mm (0.472 in)	1.2 mm (0.472 in)	1.2 mm (0.472 in)	1.0 mm (0.039 in)
MD max.	0.8 mm (0.032 in)	0.8 mm (0.032 in)	0.8 mm (0.032 in)	1.0 mm (0.039 in)
FP max.	13.6 mm (0.535 in)			
OP	$8.8 \pm 0.8$ mm ( $0.346 \pm 0.032$ in)	$8.8 \pm 0.8$ mm ( $0.346 \pm 0.032$ in)	$8.8 \pm 0.8$ mm ( $0.346 \pm 0.032$ in)	$8.8 \pm 0.8$ mm ( $0.346 \pm 0.032$ in)

**Simulated roller hinge lever**  
**SS-01GL13 (-E, -F)**  
**SS-5GL13 (-F)**  
**SS-10GL13**




Operating characteristics	Super-low force model SS-01GL13-E	Low-force models SS-01GL13-F SS-5GL13-F	Standard models SS-01GL13 SS-5GL13	Standard model SS-10GL13
OF max.	8 g	16 g	50 g	50 g
RF min.	1 g	2 g	6 g	6 g
OT min.	1.2 mm (0.472 in)	1.2 mm (0.472 in)	1.2 mm (0.472 in)	1.0 mm (0.039 in)
MD max.	0.8 mm (0.032 in)	0.8 mm (0.032 in)	0.8 mm (0.032 in)	1.0 mm (0.039 in)
FP max.	15.5 mm (0.610 in)			
OP	$10.7 \pm 0.8$ mm ( $0.421 \pm 0.032$ in)	$10.7 \pm 0.8$ mm ( $0.421 \pm 0.032$ in)	$10.7 \pm 0.8$ mm ( $0.421 \pm 0.032$ in)	$10.7 \pm 0.8$ mm ( $0.421 \pm 0.032$ in)

Note: 1. Unless otherwise specified, a tolerance of  $\pm 0.4$  mm applies to all dimensions.  
 2. Straight vertical PCB terminal models are shown above. Soldered terminal, Tab (#10) terminal, lead wire terminal, PCB terminal parallel to left and PCB terminal parallel to right are shown in the Terminals section.


Unit: mm (inch)

**Formed hinge lever**  
**SS-01GL14 (-E, -F)**  
**SS-5GL14 (-F)**  
**SS-10GL14**



Operating characteristics	Super-low force model SS-01GL14-E	Low-force models SS-01GL14-F SS-5GL14-F	Standard models SS-01GL14	Standard model SS-10GL14
OF max.	8 g	16 g	50 g	50 g
RF min.	1 g	2 g	6 g	6 g
OT min.	1.2 mm (0.472 in)	1.2 mm (0.472 in)	1.2 mm (0.472 in)	1.0 mm (0.039 in)
MD max.	0.8 mm (0.032 in)	0.8 mm (0.032 in)	0.8 mm (0.032 in)	1.0 mm (0.039 in)
FP max.	14.9 mm (0.587 in)	14.9 mm (0.587 in)	14.9 mm (0.587 in)	14.9 mm (0.587 in)
OP	10.1 ± 0.8 mm (0.398 ± 0.032 in)	10.1 ± 0.8 mm (0.398 ± 0.032 in)	10.1 ± 0.8 mm (0.398 ± 0.032 in)	10.1 ± 0.8 mm (0.398 ± 0.032 in)

**Hinged roller lever**  
**SS-01GL2 (-E, -F)**  
**SS-5GL2 (-F)**  
**SS-10GL2**






Operating characteristics	Super-low force model SS-01GL2-E	Low-force models SS-01GL2-F SS-5GL2-F	Standard models SS-01GL2	Standard model SS-10GL2
OF max.	8 g	16 g	50 g	50 g
RF min.	1 g	2 g	6 g	6 g
OT min.	1.2 mm (0.472 in)	1.2 mm (0.472 in)	1.2 mm (0.472 in)	1.0 mm (0.039 in)
MD max.	0.8 mm (0.032 in)	0.8 mm (0.032 in)	0.8 mm (0.032 in)	1.0 mm (0.039 in)
FP max.	19.3 mm (0.760 in)	19.3 mm (0.760 in)	19.3 mm (0.760 in)	19.3 mm (0.760 in)
OP	14.5 ± 0.8 mm (0.571 ± 0.032 in)	14.5 ± 0.8 mm (0.571 ± 0.032 in)	14.5 ± 0.8 mm (0.571 ± 0.032 in)	14.5 ± 0.8 mm (0.571 ± 0.032 in)

Note: Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.

## ■ MOUNTING HOLES

### Standard types

Mounting holes below are for reference only.




Note: Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.


## ■ TERMINALS

### General-purpose type


PCB terminal, straight vertical (D)



PCB terminal, parallel to left (D1)




PCB terminal, parallel to right (D2)




Note: Thickness of all the terminals is 0.5 mm.

Soldered terminal (blank)



Quick-connect tab (#110) terminal (T)



## ■ APPROVALS

### UL (File No. E41515)/CSA (File No. LR21642)

Type	Rating
SS-10 series	10.1 A, 250 VAC
SS-5 series	5 A, 125 V, 3 A 250 VAC
SS-01 series	0.1 A, 125 VAC, 30 VDC

### VDE (File No. 5861-3221)

Type	Rating
SS-5 series	5 A, 250 VAC

### SEMKO (File Nos. 43-8614026/43-891609)

Type	Rating
SS-10 series	10 A, 250 VAC
SS-5 series	5 A, 250 VAC

Note: The rated values approved by each of the safety standards (e.g. UL, CSA) may be different from the performance characteristics individually defined in this catalog.

**OMRON**

**OMRON ELECTRONICS, INC.**

One East Commerce Drive  
Schaumburg, IL 60173  
**1-800-55-OMRON**

**OMRON CANADA, INC.**

885 Milner Avenue  
Scarborough, Ontario M1B 5V8  
**416-286-6465**