

CYPRESS  
SEMICONDUCTOR

# CY7C291A CY7C292A/CY7C293A

## Reprogrammable 2K x 8 PROM

### Features

- Windowed for reprogrammability
- CMOS for optimum speed/power
- High speed
  - 20 ns (commercial)
  - 25 ns (military)
- Low power
  - 660 mW (commercial and military)
- Low standby power
  - 220 mW (commercial and military)
- EPROM technology 100% programmable
- Slim 300-mil or standard 600-mil packaging available
- 5V  $\pm 10\%$  V<sub>CC</sub>, commercial and military
- TTL-compatible I/O

- Direct replacement for bipolar PROMs
- Capable of withstanding >2001V static discharge


### Functional Description

The CY7C291A, CY7C292A, and CY7C293A are high-performance 2K-word by 8-bit CMOS PROMs. They are functionally identical, but are packaged in 300-mil (7C291A, 7C293A) and 600-mil wide plastic and hermetic DIP packages (7C292A). The CY7C293A has an automatic power down feature which reduces the power consumption by over 70% when deselected. The ceramic package may be equipped with an erasure window; when exposed to UV light the PROM is erased and can then be reprogrammed. The memory cells utilize proven EPROM floating-gate technology and byte-wide intelligent programming algorithms.

The CY7C291A, CY7C292A, and CY7C293A are plug-in replacements for bipolar devices and offer the advantages of lower power, reprogrammability, superior performance, and programming yield. The EPROM cell requires only 12.5V for the supervoltage and low current requirements allow for gang programming. The EPROM cells allow for each memory location to be tested 100%, as each location is written into, erased, and repeatedly exercised prior to encapsulation. Each PROM is also tested for AC performance to guarantee that after customer programming the product will meet DC and AC specification limits.


A read is accomplished by placing an active LOW signal on CS<sub>1</sub>, and active HIGH signals on CS<sub>2</sub> and CS<sub>3</sub>. The contents of the memory location addressed by the address line (A<sub>0</sub> – A<sub>10</sub>) will become available on the output lines (O<sub>0</sub> – O<sub>7</sub>).

### Logic Block Diagram



C291A-1

### Pin Configurations



C291A-2

C291A-3

Window available on 7C291A and 7C293A only.

### Selection Guide

|                                     |          |            | 7C291A-20<br>7C292A-20<br>7C293A-20 | 7C291A-25<br>7C292A-25<br>7C293A-25 | 7C291A-30<br>7C292A-30<br>7C293A-30 | 7C291AL-35<br>7C292AL-35<br>7C293AL-35<br>7C291A-35<br>7C292A-35<br>7C293A-35 | 7C291AL-50<br>7C292AL-50<br>7C293AL-50<br>7C291A-50<br>7C292A-50<br>7C293A-50 |
|-------------------------------------|----------|------------|-------------------------------------|-------------------------------------|-------------------------------------|-------------------------------------------------------------------------------|-------------------------------------------------------------------------------|
| Maximum Access Time (ns)            |          |            | 20                                  | 25                                  | 30                                  | 35                                                                            | 50                                                                            |
| Maximum Operating Current (mA)      | Standard | Commercial | 120                                 | 90                                  |                                     | 90                                                                            | 90                                                                            |
|                                     |          | Military   |                                     | 120                                 | 120                                 | 90                                                                            | 90                                                                            |
|                                     | L        | Commercial |                                     |                                     |                                     | 60                                                                            | 60                                                                            |
|                                     |          | Military   |                                     |                                     |                                     |                                                                               |                                                                               |
| Standby Current (mA)<br>7C293A Only |          |            | 40                                  | 30                                  | 40                                  | 30                                                                            | 30                                                                            |
|                                     |          |            |                                     | 40                                  |                                     | 40                                                                            | 40                                                                            |



T-46-13-29

CY7C291A  
CY7C292A/CY7C293A**Maximum Ratings**

(Above which the useful life may be impaired. For user guidelines, not tested.)

Storage Temperature ..... - 65°C to +150°C

Ambient Temperature with Power Applied ..... - 55°C to +125°C

Supply Voltage to Ground Potential ..... - 0.5V to +7.0V

DC Voltage Applied to Outputs in High Z State ..... - 0.5V to +7.0V

DC Input Voltage ..... - 3.0V to +7.0V

DC Program Voltage ..... 13.0V

UV Exposure ..... 7258 Wsec/cm<sup>2</sup>Static Discharge Voltage ..... >2001V  
(per MIL-STD-883, Method 3015)

Latch-Up Current ..... &gt;200 mA

**Operating Range**

| Range                     | Ambient Temperature | V <sub>CC</sub> |
|---------------------------|---------------------|-----------------|
| Commercial                | 0°C to +70°C        | 5V ±10%         |
| Industrial <sup>[1]</sup> | -40°C to +85°C      | 5V ±10%         |
| Military <sup>[2]</sup>   | -55°C to +125°C     | 5V ±10%         |

**Electrical Characteristics Over the Operating Range<sup>[3, 4]</sup>**

| Parameters       | Description                                 | Test Conditions                                               | 7C291A-20<br>7C292A-20<br>7C293A-20 |                 | 7C291A-25<br>7C292A-25<br>7C293A-25 |                 | 7C291A-30<br>7C292A-30<br>7C293A-30 |                 | Units |
|------------------|---------------------------------------------|---------------------------------------------------------------|-------------------------------------|-----------------|-------------------------------------|-----------------|-------------------------------------|-----------------|-------|
|                  |                                             |                                                               | Min.                                | Max.            | Min.                                | Max.            | Min.                                | Max.            |       |
| V <sub>OH</sub>  | Output HIGH Voltage                         | V <sub>CC</sub> = Min., I <sub>OH</sub> = -4.0 mA             | 2.4                                 |                 | 2.4                                 |                 | 2.4                                 |                 | V     |
| V <sub>OL</sub>  | Output LOW Voltage                          | V <sub>CC</sub> = Min.,<br>I <sub>OL</sub> = -16.0 mA         |                                     | 0.4             |                                     | 0.4             |                                     | 0.4             | V     |
| V <sub>IH</sub>  | Input HIGH Voltage                          | Guaranteed Input Logical<br>HIGH Voltage for All Inputs       | 2.0                                 | V <sub>CC</sub> | 2.0                                 | V <sub>CC</sub> | 2.0                                 | V <sub>CC</sub> | V     |
| V <sub>IL</sub>  | Input LOW Voltage                           | Guaranteed Input Logical<br>LOW Voltage for All Inputs        |                                     | 0.8             |                                     | 0.8             |                                     | 0.8             | V     |
| I <sub>IX</sub>  | Input Load Current                          | GND ≤ V <sub>IN</sub> ≤ V <sub>CC</sub>                       | -10                                 | +10             | -10                                 | +10             | -10                                 | +10             | μA    |
| V <sub>CD</sub>  | Input Diode Clamp Voltage                   |                                                               | Note 4                              |                 |                                     |                 |                                     |                 |       |
| I <sub>OZ</sub>  | Output Leakage Current                      | GND ≤ V <sub>OUT</sub> ≤ V <sub>CC</sub> ,<br>Output Disabled | -10                                 | +10             | -10                                 | +10             | -10                                 | +10             | μA    |
| I <sub>OS</sub>  | Output Short Circuit Current <sup>[5]</sup> | V <sub>CC</sub> = Max., V <sub>OUT</sub> = GND                | -20                                 | -90             | -20                                 | -90             | -20                                 | -90             | mA    |
| I <sub>CC</sub>  | V <sub>CC</sub> Operating Supply Current    | V <sub>CC</sub> = Max.,<br>I <sub>OUT</sub> = 0 mA            | Com'l                               | 120             |                                     | 120             |                                     |                 | mA    |
|                  |                                             |                                                               | Mil                                 |                 |                                     | 120             |                                     | 120             |       |
| I <sub>SB</sub>  | Standby Supply Current<br>(7C293A Only)     | V <sub>CC</sub> = Max.,<br>CS <sub>1</sub> ≥ V <sub>IH</sub>  | Com'l                               | 40              |                                     | 40              |                                     |                 | mA    |
|                  |                                             |                                                               | Mil                                 |                 |                                     | 40              |                                     | 40              |       |
| V <sub>PP</sub>  | Programming Supply Voltage                  |                                                               | 12                                  | 13              | 12                                  | 13              | 12                                  | 13              | V     |
| I <sub>PP</sub>  | Programming Supply Current                  |                                                               |                                     | 50              |                                     | 50              |                                     | 50              | mA    |
| V <sub>IHP</sub> | Input HIGH Programming<br>Voltage           |                                                               | 3.0                                 |                 | 3.0                                 |                 | 3.0                                 |                 | V     |
| V <sub>ILP</sub> | Input LOW Programming<br>Voltage            |                                                               |                                     | 0.4             |                                     | 0.4             |                                     | 0.4             | V     |

**Notes:**

1. Contact a Cypress representative for industrial temperature range specifications.
2. T<sub>A</sub> is the "instant on" case temperature.
3. See the last page of this specification for Group A subgroup testing information.

4. See the "Introduction to CMOS PROMs" section of the Cypress Data Book for general information on testing.
5. For test purposes, not more than one output at a time should be shorted. Short circuit test duration should not exceed 30 seconds.



PROMS



T-46-13-29

**Electrical Characteristics** Over the Operating Range<sup>[3, 4]</sup> (continued)





| Parameters       | Description                                 | Test Conditions                                               | 7C291AL-35, 50<br>7C292AL-35, 50<br>7C293AL-35, 50 |      | 7C291A-35, 50<br>7C292A-35, 50<br>7C293A-35, 50 |      | Units |
|------------------|---------------------------------------------|---------------------------------------------------------------|----------------------------------------------------|------|-------------------------------------------------|------|-------|
|                  |                                             |                                                               | Min.                                               | Max. | Min.                                            | Max. |       |
| V <sub>OH</sub>  | Output HIGH Voltage                         | V <sub>CC</sub> = Min., I <sub>OH</sub> = - 4.0 mA            | 2.4                                                |      | 2.4                                             |      | V     |
| V <sub>OL</sub>  | Output LOW Voltage                          | V <sub>CC</sub> = Min., I <sub>OL</sub> = - 16.0 mA           |                                                    | 0.4  |                                                 | 0.4  | V     |
| V <sub>IH</sub>  | Input HIGH Voltage                          | Guaranteed Input Logical HIGH Voltage for All Inputs          | 2.0                                                |      | 2.0                                             |      | V     |
| V <sub>IL</sub>  | Input LOW Voltage                           | Guaranteed Input Logical LOW Voltage for All Inputs           |                                                    | 0.8  |                                                 | 0.8  | V     |
| I <sub>Ix</sub>  | Input Load Current                          | GND ≤ V <sub>IN</sub> ≤ V <sub>CC</sub>                       | - 10                                               | +10  | - 10                                            | +10  | μA    |
| V <sub>CD</sub>  | Input Diode Clamp Voltage                   |                                                               | Note 4                                             |      |                                                 |      |       |
| I <sub>OZ</sub>  | Output Leakage Current                      | GND ≤ V <sub>OUT</sub> ≤ V <sub>CC</sub> ,<br>Output Disabled | - 10                                               | +10  | - 10                                            | +10  | μA    |
| I <sub>OS</sub>  | Output Short Circuit Current <sup>[5]</sup> | V <sub>CC</sub> = Max., V <sub>OUT</sub> = GND                | - 20                                               | - 90 | - 20                                            | - 90 | mA    |
| I <sub>CC</sub>  | V <sub>CC</sub> Operating Supply Current    | V <sub>CC</sub> = Max.,<br>V <sub>IN</sub> = 2.0V             | Commercial                                         | 60   |                                                 | 90   | mA    |
|                  |                                             |                                                               | Military                                           |      |                                                 | 90   |       |
| I <sub>SB</sub>  | Standby Supply Current<br>(7C293A Only)     | V <sub>CC</sub> = Max.,<br>CS <sub>1</sub> ≥ V <sub>IH</sub>  | Commercial                                         | 30   |                                                 | 30   | mA    |
|                  |                                             |                                                               | Military                                           |      |                                                 | 40   |       |
| V <sub>PP</sub>  | Programming Supply Voltage                  |                                                               | 12                                                 | 13   | 12                                              | 13   | V     |
| I <sub>PP</sub>  | Programming Supply Current                  |                                                               |                                                    | 50   |                                                 | 50   | mA    |
| V <sub>IHP</sub> | Input HIGH Programming Voltage              |                                                               | 3.0                                                |      | 3.0                                             |      | V     |
| V <sub>ILP</sub> | Input LOW Programming Voltage               |                                                               |                                                    | 0.4  |                                                 | 0.4  | V     |

**Capacitance<sup>[4]</sup>**

| Parameters       | Description        | Test Conditions                                             | Max. | Units |
|------------------|--------------------|-------------------------------------------------------------|------|-------|
| C <sub>IN</sub>  | Input Capacitance  | T <sub>A</sub> = 25°C, f = 1 MHz,<br>V <sub>CC</sub> = 5.0V | 10   | pF    |
| C <sub>OUT</sub> | Output Capacitance |                                                             | 10   | pF    |



T-46-13-29

**CY7C291A**  
**CY7C292A/CY7C293A**
**AC Test Loads and Waveforms<sup>[4]</sup>****Switching Characteristics Over the Operating Range<sup>[3, 4]</sup>**

| Parameters         | Description                                                                        | 7C291A-20 |      | 7C291A-25 |      | 7C291A-30 |      | 7C291AL-35 |      | 7C291AL-50 |      | Units |
|--------------------|------------------------------------------------------------------------------------|-----------|------|-----------|------|-----------|------|------------|------|------------|------|-------|
|                    |                                                                                    | 7C292A-20 |      | 7C292A-25 |      | 7C292A-30 |      | 7C292AL-35 |      | 7C292AL-50 |      |       |
|                    |                                                                                    | 7C293A-20 |      | 7C293A-25 |      | 7C293A-30 |      | 7C293AL-35 |      | 7C293AL-50 |      |       |
|                    |                                                                                    | Min.      | Max. | Min.      | Max. | Min.      | Max. | Min.       | Max. | Min.       | Max. |       |
| t <sub>AA</sub>    | Address to Output Valid                                                            |           | 20   |           | 25   |           | 30   |            | 35   |            | 50   | ns    |
| t <sub>HZCS1</sub> | Chip Select Inactive to High Z                                                     |           | 15   |           | 20   |           | 20   |            | 25   |            | 25   | ns    |
| t <sub>ACS1</sub>  | Chip Select Active to Output Valid                                                 |           | 15   |           | 20   |           | 20   |            | 25   |            | 25   | ns    |
| t <sub>HZCS2</sub> | Chip Select Inactive to High Z<br>(7C293A CS <sub>1</sub> Only) <sup>[6]</sup>     |           | 22   |           | 27   |           | 32   |            | 35   |            | 45   | ns    |
| t <sub>ACS2</sub>  | Chip Select Active to Output Valid<br>(7C293A CS <sub>1</sub> Only) <sup>[6]</sup> |           | 22   |           | 27   |           | 32   |            | 35   |            | 45   | ns    |
| t <sub>PU</sub>    | Chip Select Active to Power-Up<br>(7C293A CS <sub>1</sub> Only)                    | 0         |      | 0         |      | 0         |      | 0          |      | 0          |      | ns    |
| t <sub>PD</sub>    | Chip Select Inactive to Power-Down<br>(7C293A CS <sub>1</sub> Only)                |           | 22   |           | 27   |           | 32   |            | 35   |            | 45   | ns    |

Notes:

6. tHZCS2 and tACS2 refer to 7C293A CS<sub>1</sub> only.



### Erase Characteristics

Wavelengths of light less than 4000 Angstroms begin to erase these PROMs. For this reason, an opaque label should be placed over the window if the PROM is exposed to sunlight or fluorescent lighting for extended periods of time.

The recommended dose of ultraviolet light for erasure is a wavelength of 2537 Angstroms for a minimum dose (UV intensity x exposure time) or 25 Wsec/cm<sup>2</sup>. For an ultraviolet lamp with a 12 mW/cm<sup>2</sup> power rating, the exposure time would be approximately 30 to 35 minutes.

These PROMs need to be within 1 inch of the lamp during erasure. Permanent damage may result if the PROM is exposed to high-intensity UV light for an extended period of time. 7258 Wsec/cm<sup>2</sup> is the recommended maximum dosage.

### Programming Information

Programming support is available from Cypress as well as from a number of third-party software vendors. For detailed programming information, including a listing of software packages, please see the PROM Programming Information located at the end of this section. Programming algorithms can be obtained from any Cypress representative.

Table 1. Mode Selection

| Mode                          | Pin Function <sup>[7]</sup> |                                  |                  |                  |                 |                                 |
|-------------------------------|-----------------------------|----------------------------------|------------------|------------------|-----------------|---------------------------------|
|                               | Read or Output Disable      | A <sub>10</sub> - A <sub>0</sub> | CS <sub>3</sub>  | CS <sub>2</sub>  | CS <sub>1</sub> | O <sub>7</sub> - O <sub>0</sub> |
|                               | Other                       | A <sub>10</sub> - A <sub>0</sub> | PGM              | VFY              | VFP             | D <sub>7</sub> - D <sub>0</sub> |
| Read                          |                             | A <sub>10</sub> - A <sub>0</sub> | V <sub>IH</sub>  | V <sub>IH</sub>  | V <sub>IL</sub> | O <sub>7</sub> - O <sub>0</sub> |
| Output Disable <sup>[8]</sup> |                             | A <sub>10</sub> - A <sub>0</sub> | X                | X                | V <sub>IH</sub> | High Z                          |
| Output Disable                |                             | A <sub>10</sub> - A <sub>0</sub> | X                | V <sub>IL</sub>  | X               | High Z                          |
| Output Disable                |                             | A <sub>10</sub> - A <sub>0</sub> | V <sub>IL</sub>  | X                | X               | High Z                          |
| Program                       |                             | A <sub>10</sub> - A <sub>0</sub> | V <sub>ILP</sub> | V <sub>IHP</sub> | V <sub>FP</sub> | D <sub>7</sub> - D <sub>0</sub> |
| Program Verify                |                             | A <sub>10</sub> - A <sub>0</sub> | V <sub>IHP</sub> | V <sub>ILP</sub> | V <sub>FP</sub> | O <sub>7</sub> - O <sub>0</sub> |
| Program Inhibit               |                             | A <sub>10</sub> - A <sub>0</sub> | V <sub>IHP</sub> | V <sub>IHP</sub> | V <sub>FP</sub> | High Z                          |
| Intelligent Program           |                             | A <sub>10</sub> - A <sub>0</sub> | V <sub>ILP</sub> | V <sub>IHP</sub> | V <sub>FP</sub> | D <sub>7</sub> - D <sub>0</sub> |
| Blank Check Zeros             |                             | A <sub>10</sub> - A <sub>0</sub> | V <sub>IHP</sub> | V <sub>ILP</sub> | V <sub>FP</sub> | Zeros                           |

Notes:

7. X = "don't care" but not to exceed V<sub>CC</sub> + 5%.

8. The power-down mode for the CY7C293A is activated by deselecting CS<sub>1</sub>.







Figure 1. Programming Pinouts

CYPRESS  
SEMICONDUCTOR

T-46-13-29





CY7C291A  
CY7C292A/CY7C293A

## Typical DC and AC Characteristics



PROMS

C291A-10



C291A-11

CYPRESS  
SEMICONDUCTOR

T-46-13-29

CY7C291A

CY7C292A/CY7C293A

Ordering Information<sup>[9]</sup>

| Speed (ns) | I <sub>CC</sub> (mA) | Ordering Code  | Package Type | Operating Range |
|------------|----------------------|----------------|--------------|-----------------|
| 20         | 120                  | CY7C291A-20JC  | J64          | Commercial      |
|            |                      | CY7C291A-20PC  | P13          |                 |
|            |                      | CY7C291A-20SC  | S13          |                 |
|            |                      | CY7C291A-20WC  | W14          |                 |
| 25         | 120                  | CY7C291A-25JC  | J64          | Commercial      |
|            |                      | CY7C291A-25PC  | P13          |                 |
|            |                      | CY7C291A-25SC  | S13          |                 |
|            |                      | CY7C291A-25WC  | W14          |                 |
|            |                      | CY7C291A-25DMB | D14          | Military        |
|            |                      | CY7C291A-25LMB | L64          |                 |
|            |                      | CY7C291A-25QMB | Q64          |                 |
|            |                      | CY7C291A-25TMB | T73          |                 |
|            |                      | CY7C291A-25WMB | W14          |                 |
|            |                      |                |              |                 |
| 30         | 120                  | CY7C291A-30DMB | D14          | Military        |
|            |                      | CY7C291A-30LMB | L64          |                 |
|            |                      | CY7C291A-30QMB | Q64          |                 |
|            |                      | CY7C291A-30TMB | T73          |                 |
|            |                      | CY7C291A-30WMB | W14          |                 |
|            |                      |                |              | Commercial      |
|            |                      | CY7C291AL-35JC | J64          |                 |
|            |                      | CY7C291AL-35PC | P13          |                 |
|            |                      | CY7C291AL-35WC | W14          |                 |
|            |                      |                |              |                 |
| 35         | 60                   | CY7C291AL-35JC | J64          | Commercial      |
|            |                      | CY7C291AL-35PC | P13          |                 |
|            |                      | CY7C291AL-35WC | W14          |                 |
|            | 90                   | CY7C291A-35DC  | D14          | Commercial      |
|            |                      | CY7C291A-35LC  | L64          |                 |
|            |                      | CY7C291A-35SC  | S13          |                 |
|            |                      | CY7C291A-35PC  | P13          |                 |
|            |                      | CY7C291A-35WC  | W14          |                 |
|            | 120                  | CY7C291A-35DMB | D14          | Military        |
|            |                      | CY7C291A-35LMB | L64          |                 |
|            |                      | CY7C291A-35QMB | Q64          |                 |
|            |                      | CY7C291A-35TMB | T73          |                 |
|            |                      | CY7C291A-35WMB | W14          |                 |
| 50         | 60                   | CY7C291AL-50JC | J64          | Commercial      |
|            |                      | CY7C291AL-50PC | P13          |                 |
|            |                      | CY7C291AL-50WC | W14          |                 |
|            | 90                   | CY7C291A-50DC  | D14          | Commercial      |
|            |                      | CY7C291A-50LC  | L64          |                 |
|            |                      | CY7C291A-50SC  | S13          |                 |
|            |                      | CY7C291A-50PC  | P13          |                 |
|            |                      | CY7C291A-50WC  | W14          |                 |
|            | 90                   | CY7C291A-50DMB | D14          | Military        |
|            |                      | CY7C291A-50LMB | L64          |                 |
|            |                      | CY7C291A-50QMB | Q64          |                 |
|            |                      | CY7C291A-50TMB | T73          |                 |
|            |                      | CY7C291A-50WMB | W14          |                 |

| Speed (ns) | I <sub>CC</sub> (mA) | Ordering Code  | Package Type | Operating Range |
|------------|----------------------|----------------|--------------|-----------------|
| 20         | 120                  | CY7C292A-20DC  | D12          | Commercial      |
|            |                      | CY7C292A-20PC  | P11          |                 |
| 25         | 120                  | CY7C292A-25DC  | D12          | Commercial      |
|            |                      | CY7C292A-25PC  | P11          |                 |
|            |                      | CY7C292A-25DMB | D12          |                 |
| 30         | 120                  | CY7C292A-30DMB | D12          | Military        |
| 35         | 60                   | CY7C292AL-35PC | P11          | Commercial      |
|            | 90                   | CY7C292A-35DC  | D12          | Commercial      |
|            |                      | CY7C292A-35PC  | P11          |                 |
|            | 120                  | CY7C292A-35DMB | D12          | Military        |
| 50         | 60                   | CY7C292AL-50PC | P11          | Commercial      |
|            | 90                   | CY7C292A-50DC  | D12          | Commercial      |
|            |                      | CY7C292A-50PC  | P11          |                 |
|            | 120                  | CY7C292A-50DMB | D12          | Military        |

## Notes:

9. Most of these products are available in industrial temperature range. Contact a Cypress representative for specifications and product availability.

CYPRESS  
SEMICONDUCTOR

T-46-13-29

CY7C291A  
CY7C292A/CY7C293AOrdering Information (continued)<sup>9)</sup>

| Speed (ns) | I <sub>CC</sub> (mA) | Ordering Code  | Package Type | Operating Range |
|------------|----------------------|----------------|--------------|-----------------|
| 20         | 120                  | CY7C293A-20JC  | J64          | Commercial      |
|            |                      | CY7C293A-20PC  | P13          |                 |
|            |                      | CY7C293A-20WC  | W14          |                 |
| 25         | 120                  | CY7C293A-25JC  | J64          | Commercial      |
|            |                      | CY7C293A-25PC  | P13          |                 |
|            |                      | CY7C293A-25WC  | W14          |                 |
|            |                      | CY7C293A-25DMB | D14          | Military        |
|            | 60                   | CY7C293A-25LMB | L64          |                 |
|            |                      | CY7C293A-25QMB | Q64          |                 |
|            |                      | CY7C293A-25WMB | W14          |                 |
|            | 30                   | CY7C293A-30DMB | D14          | Military        |
|            |                      | CY7C293A-30LMB | L64          |                 |
|            |                      | CY7C293A-30QMB | Q64          |                 |
|            |                      | CY7C293A-30WMB | W14          |                 |
| 35         | 60                   | CY7C293AL-35JC | J64          | Commercial      |
|            |                      | CY7C293AL-35PC | P13          |                 |
|            |                      | CY7C293AL-35WC | W14          |                 |
|            | 90                   | CY7C293A-35DC  | D14          | Commercial      |
|            |                      | CY7C293A-35LC  | L64          |                 |
|            |                      | CY7C293A-35PC  | P13          |                 |
|            |                      | CY7C293A-35WC  | W14          |                 |
|            | 90                   | CY7C293A-35DMB | D14          | Military        |
|            |                      | CY7C293A-35LMB | L64          |                 |
|            |                      | CY7C293A-35QMB | Q64          |                 |
|            |                      | CY7C293A-35WMB | W14          |                 |
|            |                      | CY7C293A-35WMB | W14          |                 |
| 50         | 60                   | CY7C293AL-50JC | J64          | Commercial      |
|            |                      | CY7C293AL-50PC | P13          |                 |
|            |                      | CY7C293AL-50WC | W14          |                 |
|            | 90                   | CY7C293A-50DC  | D14          | Commercial      |
|            |                      | CY7C293A-50LC  | L64          |                 |
|            |                      | CY7C293A-50PC  | P13          |                 |
|            |                      | CY7C293A-50WC  | W14          |                 |
|            | 90                   | CY7C293A-50DMB | D14          | Military        |
|            |                      | CY7C293A-50LMB | L64          |                 |
|            |                      | CY7C293A-50QMB | Q64          |                 |
|            |                      | CY7C293A-50WMB | W14          |                 |
|            |                      | CY7C293A-50WMB | W14          |                 |

MILITARY SPECIFICATIONS  
Group A Subgroup Testing

## DC Characteristics

| Parameters                      | Subgroups |
|---------------------------------|-----------|
| V <sub>OH</sub>                 | 1, 2, 3   |
| V <sub>OL</sub>                 | 1, 2, 3   |
| V <sub>IH</sub>                 | 1, 2, 3   |
| V <sub>IL</sub>                 | 1, 2, 3   |
| I <sub>Ix</sub>                 | 1, 2, 3   |
| I <sub>OZ</sub>                 | 1, 2, 3   |
| I <sub>CC</sub>                 | 1, 2, 3   |
| I <sub>SB</sub> <sup>[10]</sup> | 1, 2, 3   |

## Switching Characteristics

| Parameters                        | Subgroups       |
|-----------------------------------|-----------------|
| t <sub>AA</sub>                   | 7, 8, 9, 10, 11 |
| t <sub>ACS1</sub> <sup>[11]</sup> | 7, 8, 9, 10, 11 |
| t <sub>ACS2</sub> <sup>[10]</sup> | 7, 8, 9, 10, 11 |

## SMD Cross Reference

| SMD Number | Suffix | Cypress Number |
|------------|--------|----------------|
| 5962-87650 | 01KX   | CY7C291-50TMB  |
| 5962-87650 | 01LX   | CY7C291-50WMB  |
| 5962-87650 | 013X   | CY7C291-50QMB  |
| 5962-87650 | 03KX   | CY7C291-35TMB  |
| 5962-87650 | 03LX   | CY7C291-35WMB  |
| 5962-87650 | 033X   | CY7C291-35QMB  |
| 5962-88734 | 02JX   | CY7C292A-45DMB |
| 5962-88734 | 02KX   | CY7C291A-45KMB |
| 5962-88734 | 02LX   | CY7C291A-45DMB |
| 5962-88734 | 023X   | CY7C291A-45LMB |
| 5962-88734 | 03JX   | CY7C292A-35DMB |
| 5962-88734 | 03KX   | CY7C291A-35KMB |
| 5962-88734 | 03LX   | CY7C291A-35DMB |
| 5962-88734 | 033X   | CY7C291A-35LMB |
| 5962-88734 | 04JX   | CY7C292A-25DMB |
| 5962-88734 | 04KX   | CY7C291A-25KMB |
| 5962-88734 | 04LX   | CY7C291A-25DMB |
| 5962-88734 | 043X   | CY7C291A-25LMB |

## Notes:

10. 7C293A only.

11. 7C291A and 7C292A only.

Document #: 38-00075-E



PROMS