

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2008

© COPYRIGHT 2008

BY -

ALL RIGHTS RESERVED.

LOC

E

DIST

B

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

BA1



REVISED PER ECO-11-005150

29MAR2011

RK

HMR


SERIES 36501J, 36501E AS SHOWN




- 1 TERMINAL WRAPAROUND: 0.007"(0.18mm) APPROX. ON BOTH ENDS
- 2 AVAILABLE IN 2 DIFFERENT SERIES
- 3 FOR FURTHER INFORMATION SEE DATA SHEET FOR 3650 SERIES-LOW INDUCTANCE,HIGH FREQUENCY CHIP INDUCTOR

RoHS Compliant


RECOMMENDED LAND PATTERN FOR 36501J, 36501E SERIES



36501E SERIES



36501J SERIES



36501E	1.27	0.76	0.61	0.15	0.23	0.56	0.66	0.50	0.46
36501J	1.80	1.12	1.02	0.38	0.33	0.86	1.02	0.64	0.64
SERIES	A MAX.	B MAX.	C MAX.	D REF.	F	G	H	K	J

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

SUBHASH.M

14-NOV-08

CHK

PRAKASH.S

14-NOV-08

APVD

STEPHEN.P

14-NOV-08

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

STE

TE Connectivity

NAME

LOW INDUCTANCE,
HIGH FREQUENCY CHIP
INDUCTOR SERIES 3650

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

1624112

-

SCALE 20:1

SHEET 1 OF 1

REV BA1