





LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPR
AD	14	✓	✓		B	REDESIGN & REDRAIN PER AD2635	3/13/99	KN
		✓	✓		C	REVISED PER AD4760	10/90	CP




VIEW Y-Y

- △ PART NUMBER AND DATE CODE STAMPED IN THIS AREA ON EITHER SIDE.
- ② CONTACT: COPPER ALLOY
HOSING: GLASS FILLED POLYESTER 94 V0,
COLOR-BLACK
CAM ROLL: STAINLESS STEEL
BOARD LOCK: GLASS FILLED NYLON
COLOR-BLACK
INSERT: BRASS
- ③ CONTACT: .00030 GOLD SELECTIVE PLATED IN
CONTACT AREA. FILLED POLYESTER 94 V0 MINIMUM
THICKNESS ON POST TIPS. OVER NICKEL UNDER
PLATE .00050 MINIMUM THICKNESS ALL OVER
- ④ CAM ROLL AND BOARD LOCK SHIPPED WITH EACH
CONNECTOR. ROTATE IN DIRECTION OF ALLOWING TO
OPEN.
- ⑤ CAM ROLL MAY NOT EXTEND BEYOND HOUSING SURFACE.



SECTION X-X



RECOMMENDED P.C. BOARD LAYOUT

1.60 3.400 2.600 2.800 2.400 24 25/90 G F E D C B A POSITION PART NO		19-1	
SOLDER THICKNESS SPEC IF OTHER DIMENSIONS ARE IN INCHES TOLERANCES UN- 2 PL DEC 3 PL DEC ANGLES		DR K, NOLT 3/13/85 D, GORENC 3/13/85 D, GORENC 3/13/85 NAME ROTARY ZIF ASSEMBLY .100 x .200, SOLDER PCST, OPEN BOTH ENDS	
MATERIAL 2		APPD 108-9048	
FINISH 2		APPLICATION, SPEC WEIGHT D 00779 SCALE 4:1 DRAWING NO 650019 SHEET 1 OF	

CUSTOMER DRAWING