


ROLLER BALL SWITCH

SPECIFICATIONS:

Current Rating:	.2A @ 12VDC				
Mounting Centers:	1.16"				
Mounting Hole:	.12"				
Dimensions:	.85" W x 1.6" L x 1.8"H				
Terminal Type:	10" Leads, 24 AWG				
Part No.	Type	Action			Actuator
30-17070	SPST	OFF	-	(ON)	Roller Ball

Note: () = Momentary




SNAP-IN TAMPER SWITCH

SPECIFICATIONS:

Current Rating:		1A @ 125VAC		
Terminal Type:		.250" Quick Connect		

Part No.	Type	Action			Actuator
30-17074	SPST	OFF	-	(ON)	Plastic (.55" H.)

Note: () = Momentary



Mounting Hole: 0.75"





FRIG SWITCH- SPST

ELECTRICAL RATING; UL Listed SPST Switch.
Current Rating: 5A @125 VAC
Insulation Resistance: @DC 500V 100 Megohms
Withstand Voltage: AC 1500V 1 minute
Contact Resistance: DC 2-4V 1A 100 milliohms-ohms or less.
Life: 100,000 cycles at 5 Amps
Minimum stroke to open contacts is 0.5mm from full open position
Action: (OFF) - ON



Designed for use in a refrigerator as a light switch, turning "on" when the door is opened. Switch is normally on until the activator is depressed; or pushed down by a closing door. For mounting in metal panel. Can be used in "dead mans" switch applications. Applications could include alarm systems, hood up indicator switch etc.






No. 30-17065

Round Hole Mounting Plunger TAMPER SWITCH

ELECTRICAL RATING:
not UL Listed SPST Switch
Current Rating: 2A @125 VAC, 1A @250 VAC
Insulation Resistance: @DC 500V 50 Megohms
Withstand Voltage: AC 1500V 1 minute
Minimum stroke to open contacts is depressing actuator by
.020" or 0.5mm from fully relaxed position.
ACTION: (OFF)- ON



A very economical switch. Mounts in 3/8" round hole (panel thickness up to 1/10"). The switch is normally closed (on) when the actuator is fully extended and open (off) when the actuator is depressed .020" travel distance. Total actuator travel distance is 0.40"



No. 30-17063