










MJS Series

Microminiature Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE










SPECIFICATIONS	FEATURES
Contact rating: 100 mA at 12 VDC Initial contact resistance: 20 milliohms max. Insulation resistance: 100 megohms min. at 500 VDC Dielectric strength: 500 volts RMS at sea level Electrical life: 10,000 cycles min. Operating temperature range: -10°C to +60°C Actuation force: 225g (average) Solder heat resistance: 260°C max. for 5 seconds Washing not recommended	- Molded-in terminals minimize flux or solder entry. - Molded-in high temperature phenolic base. - Low Profile. - Bifurcated wiping contact design.
	MATERIALS
	Contacts & terminals: Silver plated Case & actuator: Thermoplastic Terminal seal: Molded-in

MODEL NO. MJS12	1P2T		 ● = COMMON		
MODEL NO. MJS12R	1P2T		 ● = COMMON		
MODEL NO. MJS13	1P3T		 ● = COMMON		

MJS Series

Microminiature Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

MODEL NO. MJS13R  RIGHT ANGLE ACTUATOR	.079 (2.00) TRAVEL/THROW 1P3T  SCHEMATIC  MECHANICAL OUTLINE  P.C. BOARD LAYOUT
MODEL NO. MJS22  VERTICAL ACTUATOR	.079 (2.00) TRAVEL/THROW 2P2T  SCHEMATIC  MECHANICAL OUTLINE  P.C. BOARD LAYOUT
MODEL NO. MJS22R  RIGHT ANGLE ACTUATOR	.079 (2.00) TRAVEL/THROW 2P2T  SCHEMATIC  MECHANICAL OUTLINE  P.C. BOARD LAYOUT