


# T1/Cept/ISDN-PRI Transformers

Dual Surface Mount, 1500 Vrms, Extended & Standard Temperature Range



- RoHS peak reflow temperature rating: 245°C
- Dual SMT package contains transmit and receive transformers
- Models matched to leading transceiver ICs
- Isolation voltage: 1500 Vrms
- UL recognized

## Electrical Specifications @ 25°C

| RoHS-6 Compliant Part Number                                                                | Turns Ratio <sup>B</sup> (Pri:Sec ±2%) | OCL @ 25°C (mH MIN) | L <sub>L</sub> (μH MAX) | C <sub>w/w</sub> (pF MAX) | DCR Pri (Ω MAX) | DCR Sec (Ω MAX) | Package/ Schematic | Primary Pin |
|---------------------------------------------------------------------------------------------|----------------------------------------|---------------------|-------------------------|---------------------------|-----------------|-----------------|--------------------|-------------|
| <b>Extended Temperature Range Models<sup>1</sup> - Operating Temperature -40°C to +85°C</b> |                                        |                     |                         |                           |                 |                 |                    |             |
| PE-68841NL                                                                                  | 1CT:2CT & 1CT:2CT                      | 1.20 & 1.20         | 0.80 & 0.80             | 50 & 50                   | 1.00 & 1.00     | 1.70 & 1.70     | AN/2               | 12-10, 4-6  |
| PE-68822NL                                                                                  | 1CT:2CT & 1:1.36CT                     | 1.60 & 1.60         | 1.00 & 0.80             | 60 & 55                   | 1.70 & 1.70     | 2.00 & 1.70     | AN/1               | 12-10, 4-6  |
| PE-68826NL <sup>E</sup>                                                                     | 1:1/1.26 & 1:2CT                       | 1.20 & 1.20         | 0.80 & 0.80             | 50 & 60                   | 1.00 & 1.00     | 1.10 & 1.70     | AN/4               | 12-10, 4-6  |
| PE-68828NL                                                                                  | 1CT:1CT & 1CT:1CT                      | 1.20 & 1.20         | 0.80 & 0.80             | 50 & 50                   | 1.00 & 1.00     | 1.00 & 1.00     | AN/2               | 1-3, 4-6    |
| PE-68874NL                                                                                  | 1CT:1.15CT & 1CT:1.15CT                | 1.20 & 1.20         | 0.80 & 0.80             | 50 & 50                   | 1.20 & 1.20     | 1.40 & 1.40     | AN/2               | 1-3, 4-6    |
| PE-68877NL                                                                                  | 1CT:1CT & 1CT:2CT                      | 1.20 & 1.20         | 0.80 & 0.80             | 50 & 50                   | 1.00 & 1.00     | 1.00 & 1.80     | AN/2               | 1-3, 4-6    |
| PE-68884NL                                                                                  | 1CT:1.36CT & 1CT:1.36CT                | 1.20 & 1.20         | 0.80 & 0.80             | 50 & 50                   | 1.20 & 1.20     | 1.40 & 1.40     | AN/2               | 1-3, 4-6    |
| <b>Standard Temperature Range Models - Operating Temperature 0°C to +70°C</b>               |                                        |                     |                         |                           |                 |                 |                    |             |
| PE-68864NL <sup>A</sup>                                                                     | 1CT:2CT & 1:1                          | 1.20 & 1.20         | 0.30-0.55 & 0.80        | 30 & 30                   | 0.70 & 0.70     | 1.20 & 0.70     | AN/3               | 1-3, 5-6    |
| PE-68836NL <sup>E</sup>                                                                     | 1:1/1.26 & 1:1/1.26                    | 1.50 & 1.50         | 0.40 & 0.40             | 45 & 35                   | 0.80 & 0.80     | 1.00 & 1.00     | AN/5               | 12-10, 9-7  |



**Notes:** To order Tape & Reel packaging, add a "T" suffix to the part number (i.e. PE-68864NL becomes PE-68864NLT).

See Page 7 and 8 for Table Notes.

## Mechanical

## Schematics

AN



Weight .....4.0 grams  
Tape & Reel .....250/reel  
Tube .....30/tube

USA 858 674 8100

Germany 49 7032 7806 0

Singapore 65 6287 8998


Shanghai 86 21 62787060

China 86 755 33966678

Taiwan 886 3 4356768

# T1/Cept/ISDN-PRI Transformers

Dual Surface Mount, 1500 Vrms, Small Package



- RoHS peak reflow temperature rating: 245°C
- Dual SMT package contains transmit and receive transformers
- Models matched to leading transceiver ICs
- UL recognized (some parts pending approval)

## Electrical Specifications @ 25°C

| RoHS-6 Compliant Part Number |          | Turns Ratio <sup>B</sup><br>(Pri:Sec ±5%) | OCL<br>(mH MIN) | C <sub>w/w</sub><br>(pF MAX) | L <sub>L</sub><br>(μH MAX) | DCR Pri<br>(Ω MAX) | Package/<br>Schematic | Primary Pins |
|------------------------------|----------|-------------------------------------------|-----------------|------------------------------|----------------------------|--------------------|-----------------------|--------------|
| STD Temp                     | EXT Temp |                                           |                 |                              |                            |                    |                       |              |
| PE-65861NL                   | T1090NL  | 1CT:2CT & 1CT:2CT                         | 1.20 & 1.20     | 30 & 30                      | .60 & .60                  | 0.70 & 0.70        | BH/1                  | 16-14, 6-8   |
| -                            | T1076NL  | 1CT:1.15CT & 1CT:1.15CT                   | 1.20 & 1.20     | 30 & 30                      | .60 & .60                  | 0.70 & 0.70        | BH/2                  | 16-14, 6-8   |
| PE-65870NL                   | -        | 1CT:1.15CT & 1CT:1.15CT                   | 1.20 & 1.20     | 30 & 30                      | .60 & .60                  | 0.70 & 0.70        | BH/1                  | 1-3, 6-8     |
| PE-68678NL                   | T1094NL  | 1CT:1CT & 1CT:2CT                         | 1.20 & 1.20     | 30 & 30                      | .60 & .60                  | 0.70 & 0.70        | BH/1                  | 16-14, 6-8   |
| PE-68786NL                   | -        | 1CT:1.4CT & 1CT:1.41CT                    | 1.00 & 1.00     | 30 & 30                      | .60 & .60                  | 0.70 & 0.70        | BH/1                  | 16-14, 11-9  |
| T1023NL                      | -        | 1CT:1.4CT & 1CT:1.41CT                    | 1.00 & 1.00     | 30 & 30                      | .60 & .60                  | 0.70 & 0.70        | BH/1                  | 1-3, 11-9    |
| T1021NL                      | -        | 2CT:1/1.26CT & 2CT:1/1.26                 | 1.50 & 1.50     | 40 & 40                      | .50 & .50                  | 0.70 & 0.70        | BH/1                  | 1-3, 11-9    |
| T1137NL                      | TX1287NL | 1CT:2.42CT & 1CT:2.42CT                   | 1.20 & 1.20     | 25 & 25                      | .60 & .60                  | 0.70 & 0.70        | BH/1                  | 1-3, 6-8     |
| -                            | T1146NL  | 1:2/2.4 & 1CT:2CT                         | 1.00 & 1.00     | 35 & 35                      | 1.00 & 1.00                | 0.80 & 0.80        | BH/4                  | 1-3, 6-8     |
| -                            | TX1188NL | 1CT:2CT & 1CT:2CT                         | 1.20 & 1.20     | 30 & 30                      | .60 & .60                  | 0.70 & 0.70        | BH/1                  | 1-3, 6-8     |
| -                            | TX1089NL | 1CT:1CT & 1CT:1CT                         | 1.20 & 1.20     | 30 & 30                      | .80 & .80                  | 0.70 & 0.70        | BH/1                  | 1-3, 6-8     |
| -                            | TX1467NL | 1CT:1CT & 1CT:2CT                         | 1.20 & 1.20     | 30 & 30                      | .80 & .80                  | 1.00 & 1.00        | BH/3                  | 16-14, 11-9  |



Notes: Standard (STD) operating temperature range is 0C to 70C. Extended (EXT) operating temperature range is -40C to +85C.

See pages 7 and 8 for table notes.

## Mechanicals


## Schematics

BH



SUGGESTED PAD LAYOUT

Unless otherwise specified, all tolerances are ± .010 / 0,25



Weight .....1.0 grams  
Tape & Reel .....600/reel  
Tube .....40/tube

USA 858 674 8100

Germany 49 7032 7806 0


Singapore 65 6287 8998

Shanghai 86 21 62787060

China 86 755 33966678

Taiwan 886 3 4356768

Single Reinforced Insulation, 3 kVrms



- RoHS peak reflow temperature rating: 245°C
- Dual SMT package contains transmit and receive transformers
- Models matched to leading transceiver ICs
- Isolation voltage: 1500 Vrms
- UL recognized

**Electrical Specifications @ 25°C - Operating Temperature 0°C to 70°C (Unless Otherwise Noted)**


| RoHS-6 Compliant<br>Part Number | Turns Ratio <sup>B</sup><br>(Pri:Sec ±5%) | <sup>B</sup> OC <sup>L</sup> <sup>C</sup><br>(mH MIN) | w/w <sup>L</sup><br>(pF MAX) | L<br>(μH MAX) | DCR Pri<br>(Ω MAX) | DCR Sec<br>(Ω MAX) | Package/<br>Schematic | Primary<br>Pins |
|---------------------------------|-------------------------------------------|-------------------------------------------------------|------------------------------|---------------|--------------------|--------------------|-----------------------|-----------------|
| PE-65830NL                      | 1.27CS:1                                  | .800                                                  | 15                           | 0.70          | 0.50               | 0.35               | IS/3                  | 1-5             |
| PE-65832NL                      | 1:1.36CT                                  | 1.20                                                  | 35                           | 0.60          | 0.70               | 0.90               | IS/4                  | 10-6            |
| PE-65833NL <sup>A</sup>         | 1CT:2CT                                   | 1.20                                                  | 20                           | 0.30-0.55     | 0.50               | 0.90               | IS/1                  | 1-5             |
| PE-65834NL                      | 1:1                                       | 1.20                                                  | 20                           | 0.50          | 0.50               | 0.50               | IS/2                  | 1-5             |
| PE-65835NL                      | 1CT:2CT                                   | 1.20                                                  | 15                           | 0.80          | 0.70               | 1.10               | IS/1                  | 1-5             |
| PE-65838NL                      | 1:1.14CT                                  | 1.50                                                  | 30                           | 1.00          | 0.70               | 0.90               | IS/4                  | 10-6            |
| PE-65839NL <sup>E</sup>         | 1:1/1.26                                  | 1.50                                                  | 35                           | 0.60          | 0.70               | 1.10               | IS/4                  | 10-6            |
| PE-68646NL <sup>E</sup>         | 1:1.58/2                                  | 1.50                                                  | 20                           | 0.70          | 0.70               | 1.20               | IS/4                  | 10-6            |

See pages 7 and 8 for table notes.


## Mechanical

## Schematics

## IS



**Notes:**  
Leads are 22 AWG solderable.  
Unused pins not provided.



**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$  Unless otherwise specified, all tolerances are  $\pm \frac{.010}{0.25}$

**Weight** .....4 grams  
**Tube** .....35/tube

USA 858 674 8100

Germany 49 7032 7806 0

Singapore 65 6287 8998


Shanghai 86 21 62787060

China 86 755 33966678

Taiwan 886 3 4356768

# T1/Cept/ISDN-PRI Transformers

Single Through Hole, 1500Vrms



- RoHS peak reflow temperature rating: 245°C
- Extended and standard temperature range
- Dual and single through hole models available
- Models matched to leading transceiver ICs
- UL recognized
- Isolation Voltage: 1500 Vrms MIN

## Electrical Specifications @ 25°C


| RoHS-6 Compliant Part Number                                                                | Turns Ratio <sup>B</sup><br>(Pri:Sec ±2%) | OCL @ 25°C<br>(mH MIN) | C <sub>w/w</sub><br>(pF MAX) | L <sub>L</sub><br>(μH MAX) | DCR Pri<br>(Ω MAX) | DCR Sec<br>(Ω MAX) | Package/<br>Schematic | Primary Pins |
|---------------------------------------------------------------------------------------------|-------------------------------------------|------------------------|------------------------------|----------------------------|--------------------|--------------------|-----------------------|--------------|
| <b>Standard Temperature Range Single Transformers - Operating Temperature 0°C to +70°C</b>  |                                           |                        |                              |                            |                    |                    |                       |              |
| PE-64931NL                                                                                  | 1:1:1 (1:2CS)                             | 1.20                   | 25                           | 0.50                       | 0.70               | 0.70 & 0.70        | HC/2                  | 1-2          |
| PE-64934NL                                                                                  | 1:1w                                      | 1.20                   | 25                           | 0.50                       | 0.70               | 0.70               | HC/1                  | 1-2          |
| PE-64936NL <sup>E</sup>                                                                     | 1CT:1                                     | 1.20                   | 25                           | 0.80                       | 0.70               | 0.70               | HC/3                  | 1-5          |
| PE-64937NL                                                                                  | 1:1.36                                    | 1.20                   | 35                           | 0.80                       | 0.70               | 0.80               | HC/1                  | 5-6          |
| PE-65351NL                                                                                  | 1:2CT                                     | 1.20                   |                              | 0.50                       | 0.70               | 1.30               | HC/3                  | 2-6          |
| PE-65363NL                                                                                  | 1:4CT                                     | 0.50                   | 40                           | 1.00                       | 0.70               | 1.50               | HC/5                  | 1-5          |
| PE-65388NL                                                                                  | 1:1.15CT                                  | 1.50                   | 35                           | 0.60                       | 0.70               | 0.90               | HC/3                  | 2-6          |
| PE-65389NL <sup>E</sup>                                                                     | 1:1/1.26                                  | 1.50                   | 40                           | 0.40                       | 0.70               | 0.90               | HC/3                  | 2-6          |
| PE-65415NL                                                                                  | 1CT:2CT                                   | 1.20                   | 30                           | 0.50                       | 0.70               | 1.20               | HC/4                  | 1-5          |
| PE-68644NL                                                                                  | 1CT:1                                     | 0.70                   | 20                           | 0.70                       | 0.20               | 0.80               | HC/3                  | 1-5          |
| <b>Extended Temperature Range Single Transformer - Operating Temperature -40°C to +85°C</b> |                                           |                        |                              |                            |                    |                    |                       |              |
| PE-65770NL                                                                                  | 1:1.15CT                                  | 1.50                   | 40                           | 0.80                       | 0.90               | 1.00               | HC/3                  | 2-6          |
| PE-65771NL                                                                                  | 1CT:2CT                                   | 1.20                   | 50                           | 0.60                       | 1.00               | 2.00               | HC/4                  | 2-6          |
| PE-65778NL                                                                                  | 1CT:1CT                                   | 1.20                   | 40                           | 1.00                       | 1.00               | 1.00               | HC/4                  | 1-5          |
| TX1252NL                                                                                    | 1CT:1                                     | 1.20                   | 40                           | 1.00                       | 1.00               | 1.00               | HC/3                  | 1-5          |

See Pages 7 and 8 for Table Notes.


## Mechanical

## Schematic


HC



Notes: Leads are 24 AWG solderable.  
Unused pins not provided.



Dimensions: Inches mm Unless otherwise specified, all tolerances are ± .010 0,25



Weight .....2 grams

Tube .....60/tube

USA 858 674 8100

Germany 49 7032 7806 0

Singapore 65 6287 8998

Shanghai 86 21 62787060

China 86 755 33966678

Taiwan 886 3 4756768

# T1/Cept/ISDN-PRI Transformers

Dual Through Hole, 1500 Vrms




| Electrical Specifications @ 25°C                                                    |                                           |                        |                              |                            |                    |                    |                       |              |
|-------------------------------------------------------------------------------------|-------------------------------------------|------------------------|------------------------------|----------------------------|--------------------|--------------------|-----------------------|--------------|
| RoHS-6 Compliant Part Number                                                        | Turns Ratio <sup>B</sup><br>(Pri:Sec ±5%) | OCL @ 25°C<br>(mH MIN) | C <sub>w/w</sub><br>(pF MAX) | L <sub>L</sub><br>(μH MAX) | DCR Pri<br>(Ω MAX) | DCR Sec<br>(Ω MAX) | Package/<br>Schematic | Primary Pins |
| Standard Temperature Range Single Transformers - Operating Temperature 0°C to +70°C |                                           |                        |                              |                            |                    |                    |                       |              |
| PE-64921NL                                                                          | 1:2CT & 1:1.36                            | 1.20 & 1.20            | 35 & 35                      | 0.50 & 0.80                | 0.80 & 0.80        | 1.20 & 1.00        | HD/2                  | 14-12, 5-7   |
| PE-65565NL                                                                          | 1:1.15CT & 1:2CT                          | 1.50 & 1.20            | 35 & 40                      | 0.60 & 0.50                | 0.70 & 0.70        | 1.10 & 1.30        | TD/1                  | 14-12, 5-7   |


See Pages 7 and 8 for Table Notes.

## Mechanicals


### TD DUAL




### HD DUAL



## Schematics



## Transformer Selection Guide



## Application Notes


**1. Extended Temperature Range Models** - For extended temperature range transformers (-40°C to +85°C operating temperature range), OCL (Open Circuit Inductance for the primary winding) is specified at both -40°C and +25°C. At -40°C, OCL is 600  $\mu$ H minimum for all low temperature models. All other parameters are specified at +25°C only. Standard temperature range is 0°C to +70°C.

**2. ET Product** - All coils have an ET product of 10 V- $\mu$ sec minimum.


**3. Flammability** - Materials used in the products are recognized as UL94-VO approved. Products meet the requirements of IEC 695-2-2 (Needle Flame Test).

**4. Balance Characteristics** - The transformers meet the requirements for longitudinal balance of FCC part 68.

**5. Common Mode Rejection Ratio** - The CMRR for all transformers is better than 50 dB at 1 MHz. A typical test circuit is shown below.



**6. Crosstalk Attenuation** - In the dual packages, which contain transmit and receive transformers side by side, sufficient crosstalk attenuation is achieved by the inherent characteristics of the toroid cores as well as by their proper positioning. The crosstalk attenuation is typically 50 dB or better from 100 kHz to 10 MHz. This result was established with the test circuit shown below.



**7. Return Loss** - ITU-T G.703 and European national regulatory documents specify minimum return loss levels. The transformers will allow these limits to be complied within situations where they are applicable.

| Frequency   | 50-100 kHz | 100 kHz-2 MHz | 2-3 MHz |
|-------------|------------|---------------|---------|
| Return Loss |            |               |         |
| TX          | 9 dB       | 15 dB         | 11 dB   |
| RX          | 12 dB      | 18 dB         | 14 dB   |

**8. Surge Voltage Capability** - All transformers and chokes meet surge voltage tests according to the most stringent regulatory documents when system designs include the proper voltage and current suppression devices:

Metallic Voltage: 800 V peak, 10/560  $\mu$ sec  
Longitudinal Voltage: 2,400 V peak, 10/700  $\mu$ sec

**9. Isolation Voltage** - 100% of transformers are tested during production to the specified isolation voltage level.

**10. Safety Agency Recognition** - Parts listed as "Recognized" or "Certified" meet Underwriter Laboratories, UL 1459 and UL 1950 per file E133523 (S).


**Transformers with Reinforced Insulation according to IEC950, such as PE-68646NL (pg. 3) is certified by the following organizations:**

| Code | Certificate Information                                       |
|------|---------------------------------------------------------------|
| T    | TUV, EN60 950/EN 41003, Cert. R9371358, reinforced insulation |
| U    | UL 1459/UL1950, File E133523 (S), reinforced insulation       |

**11. General Information** - The transformers are specifically designed for use in 1.544 Mbps (T1), 2.048 Mbps (CEPT) and ISDN Primary rate (PRI) interface applications. They are matched to the majority of the line interface transceiver ICs currently available. Use of the proper transformer allows the interface circuit to comply with ITU-T G.703 and other standards regarding pulse waveform, return loss, and balance.

**12. Common Mode Chokes** - The "high-frequency" 4-lines common mode chokes shown in this data sheet provide an effective means of compliance with national and international regulations on EMI. They are designed to be used in conjunction with Pulse's T1/CEPT transformers as shown in the typical application below. Crosstalk is typically -70 dB at 1 MHz and -55 dB at 10 MHz.

### Typical Application



T608.U (05/12)

## Notes From Tables (pages 1-6):

**A.** Tolerance leakage inductance:  
.30  $\mu$ H min to .55  $\mu$ H MAX.

**B.** OCL (primary inductance) and  $L_L$  (leakage inductance) are measured at the primary winding. Turns ratio is specified primary: secondary. (CT = Center Tap; CS = Split Center Tap).

**C.** To make a 1CT:1 ratio from a 1CT: 2CT ratio, use only one half of the secondary (2CT) winding.

**D.** For Reinforced 3 kVrms Dual SMT Transformers, refer to data sheet T617. For Octal SMT Transformers, refer to data sheet T622.

**E.** Dual Ratio Transformers: These transformers have tapped secondary windings to provide two turns ratios (T/R). Use the entire primary winding and connect

| Part Number | Turns Ratio 1 | Secondary Pins | Turns Ratio 2 | Secondary Pins |
|-------------|---------------|----------------|---------------|----------------|
| PE-65839NL  | 1:1           | 3-5            | 1:1.26        | 1-5            |
| PE-68646NL  | 1:1.58        | 3-5            | 1:2           | 1-5            |
| PE-65389NL  | 1:1           | 3-5            | 1:1.26        | 1-5            |
| PE-68826NL  | 1:1           | 2-3            | 1:1.26        | 1-3            |
| PE-68836NL  | 1:1           | 2-3/5-6        | 1:1.26        | 1 3/4 - 6      |

**F.** Standard packaging for surface mount "AN" and "LA" packages is ant-static tubes. Optional Tape & Reel packaging can be ordered by adding "T" suffix to the part number (i.e. PE-68864NLT).


**G.** Safety Agency approvals pending.

**H.** The turns ratio of these devices have been designed, in conjunction with semiconductor vendor recommendations, to allow connections to various terminations (e.g 75  $\Omega$  or 120  $\Omega$  with the same transformer). For 75  $\Omega$  termination, the PEB 2235 requires the following turns ratio: 1:1.57 (TX) and 1:1.26 (RX) which can be achieved using pins (1-2):(15-16) for TX and (10-11):(5-8) for RX. For 120  $\Omega$ , the following turns ratio are required: 1:2 (TX) and 1:1 (RX), which are pins (1-2):(16-14) for TX and (9-11):(5-8) for RX.


### Electrical Specifications @ 25°C - Operating Temperature 0°C to 70°C

| Pulse Part Number                                 | Turns Ratio ( $\pm 5\%$ ) | OCL ( $\mu$ H MIN) | Package/Schematic    |
|---------------------------------------------------|---------------------------|--------------------|----------------------|
| <b>HIGH FREQUENCY COMMON MODE CHOKES, 4-LINES</b> |                           |                    |                      |
| PE-65554NL                                        | 1:1:1:1                   | 24.0               | IN/1 (Through Hole)  |
| PE-65555NL                                        | 1:1:1:1                   | 8.0                | IN/1 (Through Hole)  |
| PE-65854NL                                        | 1:1:1:1                   | 47.0               | SH/1 (Surface Mount) |
| PE-65857NL                                        | 1:1:1:1                   | 24.0               | LA/2 (Surface Mount) |

**Notes:** For additional Common Mode Chokes, refer to data sheet G002



### Schematics







# Common Mode Chokes For Telecom Applications

For EMI Reduction



## Mechanicals

SH

LA



IN



|                                                                   | SH             | LA            | IN             |
|-------------------------------------------------------------------|----------------|---------------|----------------|
| Weight                                                            | .....0.3 grams | .....2 grams  | .....2.5 grams |
| Tape & Reel                                                       | .....1500/reel | .....250/reel | .....(N/A)     |
| Tube                                                              | .....25/tube   | .....30/tube  | .....35/tube   |
| Dimensions:                                                       | Inches         |               |                |
|                                                                   | mm             |               |                |
| Unless otherwise specified, all tolerances are $\pm .010$<br>0,25 |                |               |                |

## For More Information

**Pulse Worldwide Headquarters**  
12220 World Trade Drive  
San Diego, CA  
92128  
U.S.A.

Tel: 858 674 8100  
Fax: 858 674 8262

**Pulse Europe**  
Einsteinstrasse 1  
D-71083 Herrenberg  
Germany

Tel: 49 7032 78060  
Fax: 49 7032 7806 135

**Pulse China Headquarters**  
B402, Shenzhen Academy of  
Aerospace Technol-  
ogy Bldg.  
10th Kejian Road  
High-Tech Zone  
Nanshan District  
Shenzhen, PR China  
518057  
Tel: 86 755 33966678  
Fax: 86 755 33966700

**Pulse North China**  
Room 2704/2705  
Super Ocean Finance  
Ctr.  
2067 Yan An Road  
West  
Shanghai 200336  
China  
Tel: 86 21 62787060  
Fax: 86 2162786973

**Pulse South Asia**  
135 Joo Seng Road  
#03-02  
PM Industrial Bldg.  
Singapore 368363  
Tel: 65 6287 8998  
Fax: 65 6287 8998

**Pulse North Asia**  
3F, No. 198  
Zhongyuan Road  
Zhongli City  
Taoyuan County 320  
Taiwan R. O. C.  
Tel: 886 3 4356768  
Fax: 886 3 4356823 (Pulse)  
Fax: 886 3 4356820 (FRE)

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2012. Pulse Electronics, Inc. All rights reserved.