





LEGEND

8818-**-*(*)*

MATERIAL
(.27)/.0106 THK.
BLANK= BRASS
A= PHOS BRONZE

OPTION CODE
BLANK=AS SHOWN

WINDING SPEC
BLANK=CHAIN, PER WINDING DETAIL "B"
L=L00SE

PLATING
SEE NOTE 2

- NOTES:
1. MATERIAL: SEE LEGEND
 2. FINISH:
(P909) OVERALL HOT TIN DIP: (0.00254)/.000100 MIN.
(550) SELECT GOLD: (0.000381)/.000015 MIN.
OVERALL GOLD FLASH: (0.000051)/.000002 MIN.
OVERALL NICKEL UNDERPLATE: (0.000761)/.000030 MIN.
(555) SELECT GOLD: (0.000381)/.000015 MIN.
OVERALL NICKEL UNDERPLATE: (0.000761)/.000030 MIN.
 3. PRODUCT SPECIFICATION: PS-08-50
 4. PACKAGING SPECIFICATION:
LOOSE TERMINALS: PER PK-2759-001
CHAIN FORM TERMINALS: NONE
 5. CRIMP ACCEPTS 18-22 GA. WIRE WITH (2.791)/.110 MAX. INSULATION DIA.
 6. DIMENSIONS GIVEN ACROSS CENTERLINES ARE SYMMETRICAL ABOUT THOSE CENTERLINES WITHIN HALF THE TOTAL TOLERANCE.
 7. TERMINAL FOR USE IN 41695 SERIES HOUSINGS.
 8. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

EDP NO.	ENGINEERING NO.
	8818-(555)
	8818-(555)L
08-50-0008	8818-(P909)
08-50-0023	8818-(P909)L
40-01-1181	8818-(999)
40-01-1182	8818-A(999)
08-65-0128	8818-A(555)
08-65-0129	8818-A(555)L
08-52-0131	8818-A(P909)
08-52-0132	8818-A(P909)L
08-58-0135	8818-A(550)
08-58-0136	8818-A(550)L

WINDING DETAIL "B"

ADD WINDING DETAIL IEC NO: UCP2014-4151 DRAWN BY: CHYONGKUN 2014/04/07 APPROV: FSM TH 2014/04/21	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
				MM/IN		---	INCH	
	▽=0	mm INCH		DRAWN BY	DATE	TITLE		
	▽=0	4 PLACES ±						