

### THE WIDEST RANGE IN MINIATURE SWITCHES



- ☐ 17 actuators including toggles, paddle levers and locking levers in different lengths.
- ☐ Various contact materials for low and high currents.
- ☐ 8 functions including maintained and momentary versions.
- ☐ 1 to 4 pole configurations.



- ☐ 12 terminal types including 9 for PC board mounting. Other types include quick-connect and wire-wrap.
- ☐ 6 bushing styles from 6 (.236) plain to 11,9 (15/32) threaded.
- ☐ 3 types of finish including military black.



- ☐ 3 approvals (UL - CSA - CECC).
- ☐ 4 types of sealing for terminal or front panel requirements.
- ☐ Numerous accessories available for actuator and bushing options.

# 5000 series

## Toggle switches

### Overview

MODEL  
STRUCTURE

A



### ABOUT THIS SERIES

On the following pages, you will find successively :

- model structure of switches with threaded bushing
- model structure of switches with plain bushing
- options in the same order as in above chart

**Dimensions** : first dimensions are in mm while inches are shown as bracketed numbers.




**NOTICE** : please note that not all combinations of above numbers are available. Refer to the following pages for further information.



# 5000 series

## Toggle switches

### Overview



**Sealing boots** are available. They are presented in section H.



**Mounting accessories** : standard hardware supplied with all models with Ø 6,35 (1/4) or Ø 6 (.236) threaded bushing : 2 hex nuts 8 mm (.314) across flats, 1 locking ring and 1 lockwasher.  
Standard and special hardware available are presented in section I.



**Packaging unit** : 25 pieces or 50 pieces depending on models.

# 5000 series

## Toggle switches

### Specifications

#### ELECTRICAL SPECIFICATIONS

- Current/voltage rating with resistive load :

| Contact                     | Maximum                                               | Minimum              | Level*     |
|-----------------------------|-------------------------------------------------------|----------------------|------------|
| Silver (A)                  | 4A 30VDC                                              | 50mA 10VDC           | III and IV |
| Silver,<br>gold plated (AD) | 4A 30VDC<br>Gold plating withstands up to 100mA 30VDC | 10mA 50mV<br>10µA 5V | I to IV    |
| Brass,<br>gold plated (CD)  | 0,4 VA at 20VAC or DC                                 | 10mA 50mV<br>10µA 5V | I and II   |

- For inductive, lamp or capacitive load, consult factory.
- Initial contact resistance : 10 mΩ max.
- Insulation resistance : 1.000 MΩ min. at 500VDC
- Dielectric strength :
  - 1.000 Vrms 50 Hz min. between terminals
  - 1.500 Vrms 50 Hz min. between poles
  - 1.500 Vrms 50 Hz min. between terminals and frame
- Contact bounce : 2 ms max.
- Electrical life at full load :
  - 50.000 cycles for single and double pole
  - 40.000 cycles for 3 pole
  - 30.000 cycles for 4 pole
- Low level or mechanical life : 100.000 cycles

\* For details, see Technical Information, end of catalogue.

#### MATERIALS

- Case : diallylphthalate (DAP) or high temperature plastic material (UL94-V0)
- Actuator : brass, nickel plated
- Paddles : UL94HB polyamide
- Lever caps : vinyl
- Bushing : brass, nickel plated
- Housing : stainless steel or steel tin plated
- Contacts
  - A : silver
  - AD : silver, gold plated
  - CD : brass, gold plated
  - X814 : for peak currents, see "Special options".
- Terminal seal : epoxy

#### GENERAL SPECIFICATIONS

- Torque : 1,25 Nm (.922 Ft.lb) max. applied to nut
- Panel thickness : 2,5 mm (.098) with 2 nuts - 4 mm (.157) with 1 nut
- Operating temperature : -40°C to +85°C

#### AGENCY APPROVALS/PREFERENTIAL LIST



CECC 96201-007

3A 250VAC, 6A 125VAC


For **VDE**, refer to 55000 series.

#### NATO


**Availability** : consult factory for details of approved models.

**Marking** : to order switches marked UL, CSA or CECC, complete appropriate box of ordering format. The preferential list does not appear on the switches.


→ Keyway



• 1, 2, 3 and 4 pole configurations



MODEL  
STRUCTURE



Shown with standard lever


### Single pole



5636  
5639  
5637  
5638  
5632

| III | II  | I   |
|-----|-----|-----|
| 2-3 |     | 1-2 |
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |

→ Keyway




### Double pole



5646  
5649  
5647  
5648  
5642  
5644\*  
5644 1R\*  
5644 2R\*

| III | II  | I   |
|-----|-----|-----|
| 2-3 |     | 1-2 |
| 5-6 |     | 4-5 |
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |
| ON  | ON  | ON  |
| ON  | ON  | MOM |
| MOM | ON  | MOM |

→ Keyway



\* Function 4 : SP in DP case - specify CT or TH connections, see end of catalogue.


### Three pole



5656  
5659  
5657  
5658  
5652

| III | II  | I   |
|-----|-----|-----|
| 2-3 |     | 1-2 |
| 5-6 |     | 4-5 |
| 8-9 |     | 7-8 |
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |

→ Keyway



# 5000 series

## Toggle switches - solder lug terminals

Threaded bushing  $\varnothing 6,35$  (1/4) : 5600

MODEL  
STRUCTURE


### Four pole



5666  
5669  
5667  
5668  
5662  
5664\*  
5664 1R\*  
5664 2R\*

| III   | II  | I     |
|-------|-----|-------|
| 2-3   |     | 1-2   |
| 5-6   |     | 4-5   |
| 8-9   |     | 7-8   |
| 11-12 |     | 10-11 |
| ON    | -   | ON    |
| ON    | OFF | ON    |
| MOM   | OFF | MOM   |
| ON    | OFF | MOM   |
| ON    | -   | MOM   |
| ON    | ON  | ON    |
| ON    | ON  | MOM   |
| MOM   | ON  | MOM   |

→ Keyway




\*Function 4 : DP in 4P case - specify CT or TH connections, see end of catalogue.

### PANEL CUT-OUT



Standard



With K  
sealing option




With X408  
sealing option



### 5700 models

- Flatted bushing Ø 6,35 mm (1/4)
- 1, 2, 3 and 4 pole configurations

#### MODEL STRUCTURE




For model structure numbers, refer to 5600 models and replace 6 with 7.



### 5500 models

- Threaded bushing Ø 6 mm x 0.75 SI (.236 x 0.75 IS)
- 1, 2, 3 and 4 pole configurations

#### MODEL STRUCTURE



For model structure numbers, refer to 5600 models and replace 6 with 5.




# 5000 series

## Toggle switches - solder lug terminals

Threaded bushing Ø 11,9 (15/32) : 5600M

MODEL  
STRUCTURE

→ Keyway



- 1, 2, 3 and 4 pole configurations
- Supplied with 2 hex nuts and 1 locking ring
- Panel thickness up to 6 mm (.236)



MODEL  
STRUCTURE



Shown with standard lever




### Single pole



5636M  
5639M  
5637M  
5638M  
5632M

| III | II  | I   |
|-----|-----|-----|
| 2-3 |     | 1-2 |
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |

→ Keyway





### Double pole



5646M  
5649M  
5647M  
5648M  
5642M  
5644M\*  
5644M 1R\*  
5644M 2R\*

| III | II  | I   |
|-----|-----|-----|
| 2-3 |     | 1-2 |
| 5-6 |     | 4-5 |
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |
| ON  | ON  | ON  |
| ON  | ON  | MOM |
| MOM | ON  | MOM |

→ Keyway



\* Function 4 : SP in DP case - specify CT or TH connections, see end of catalogue.




### Three pole



5656M  
5659M  
5657M  
5658M  
5652M

| III | II  | I   |
|-----|-----|-----|
| 2-3 |     | 1-2 |
| 5-6 |     | 4-5 |
| 8-9 |     | 7-8 |
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |

→ Keyway




### Four pole



5666M  
5669M  
5667M  
5668M  
5662M  
5664M\*  
5664M 1R\*  
5664M 2R\*

| III   | II  | I     |
|-------|-----|-------|
| 2-3   |     | 1-2   |
| 5-6   |     | 4-5   |
| 8-9   |     | 7-8   |
| 11-12 |     | 10-11 |
| ON    | -   | ON    |
| ON    | OFF | ON    |
| MOM   | OFF | MOM   |
| ON    | OFF | MOM   |
| ON    | -   | MOM   |
| ON    | ON  | ON    |
| ON    | ON  | MOM   |
| MOM   | ON  | MOM   |

→ Keyway



\*Function 4 : DP in 4P case - specify CT or TH connections, see end of catalogue.

### PANEL CUT-OUT




OTHER : M bushing can be combined with other types such as : 5200, Z, MIWR... Consult factory.

Threaded bushing Ø 6,35 (1/4) : 5200

114




- Also available with plain bushing, see "Special options" X371




\_\_\_\_\_

Shown with standard lever

ON - ON  
ON OFF ON  
MOM OFF MOM  
ON OFF MOM  
ON - MOM




ON - ON  
ON OFF ON  
MOM OFF MOM  
ON OFF MOM  
ON - MOM  
ON ON ON  
ON ON MOM  
MOM ON MOM



\*Function 4 : SP in DP case - specify CT or TH connections, see end of catalogue.

|     |     |     |
|-----|-----|-----|
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |



### Four pole



5266 B  
5269 B  
5267 B  
5268 B  
5262 B  
5264 B\*  
5264 1R B\*  
5264 2R B\*

| III   | II  | I     |
|-------|-----|-------|
| 2-3   |     | 1-2   |
| 5-6   |     | 4-5   |
| 8-9   |     | 7-8   |
| 11-12 |     | 10-11 |
| ON    | -   | ON    |
| ON    | OFF | ON    |
| MOM   | OFF | MOM   |
| ON    | OFF | MOM   |
| ON    | -   | MOM   |
| ON    | ON  | ON    |
| ON    | ON  | MOM   |
| MOM   | ON  | MOM   |

→ Keyway



\*Function 4 : DP in 4P case - specify CT or TH connections, see end of catalogue.

### PANEL CUT-OUT

5200 - 5000 - 5400



Standard




With K sealing option

### 5000 models

- Terminal spacing 5,08 mm (.200)
- Epoxy sealed terminals standard
- 1 and 2 pole configurations

Diagram as per 5200 model



### MODEL STRUCTURE



Shown with standard lever

### Terminal spacing 5,08 (.200) - single and double pole

→ Keyway



Single pole Double pole  
5036 5046  
5039 5049  
5037 5047  
5038 5048  
5032 5042  
5044\*  
5044 1R\*  
5044 2R\*

| III | II  | I   |
|-----|-----|-----|
| 2-3 |     | 1-2 |
| 5-6 |     | 4-5 |
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |
| ON  | ON  | ON  |
| ON  | ON  | MOM |
| MOM | ON  | MOM |



\*Function 4 : SP in DP case - specify CT or TH connections, see end of catalogue.

# 5000 series

Toggle switches - straight PC terminals

MODEL  
STRUCTURE


A

Diagram, as per 5200 model

## 5400 models


- Threaded bushing Ø 6,35 mm (1/4)
- Terminal spacing 4 mm (.157)
- 1, 2, 3 and 4 pole configurations

MODEL  
STRUCTURE



For model structure numbers, refer to  
**5200** models and replace 2 with 4.


Panel cut-out, see 5200.




## 5900 models


- Flatted bushing Ø 6,35 mm (1/4)
- Terminal spacing 4,7 mm (.185)
- 1, 2, 3 and 4 pole configurations

MODEL  
STRUCTURE



For model structure numbers, refer to  
**5200** models and replace 2 with 9.





### 5100 models


- Threaded bushing Ø 6 mm x 0.75 SI (.236 x 0.75 IS)
- Terminal spacing 4,7 mm (.185)
- 1, 2, 3 and 4 pole configurations

#### MODEL STRUCTURE



For model structure numbers, refer to 5200 models and replace 2 with 1.


Panel cut-out, see below.



### 5300 models

- Threaded bushing Ø 6 mm x 0.75 SI (.236 x 0.75 IS)
- Terminal spacing 4 mm (.157)
- 1, 2, 3 and 4 pole configurations


#### MODEL STRUCTURE




For model structure numbers, refer to 5200 models and replace 2 with 3.

#### PANEL CUT-OUT

##### 5100 - 5300



Standard



With X408 sealing option

# 5000 series

## Toggle switches - quick-connect terminals

Threaded bushing Ø 6,35 (1/4) : 5200Z

MODEL  
STRUCTURE

→ Keyway



- Terminal spacing 4,7 mm (.185)
- Epoxy sealed terminals standard
- 1 and 2 pole configurations



MODEL  
STRUCTURE



Shown with standard lever

### Single pole




5236Z  
5239Z  
5237Z  
5238Z  
5232Z

III II I  
2-3 1-2

ON - ON  
ON OFF ON  
MOM OFF MOM  
ON OFF MOM  
ON - MOM

→ Keyway



### Double pole




5246Z  
5249Z  
5247Z  
5248Z  
5242Z  
5244Z\*  
5244Z 1R\*  
5244Z 2R\*

III II I  
2-3 1-2  
5-6 4-5


ON - ON  
ON OFF ON  
MOM OFF MOM  
ON OFF MOM  
ON - MOM  
ON ON ON  
ON ON MOM  
MOM ON MOM

→ Keyway



\*Function 4 : SP in DP case - specify CT or TH connections, see end of catalogue.

### PANEL CUT-OUT




Standard



With K  
sealing option




With X408  
sealing option





## 5900Z models

- Flatted bushing Ø 6,35 mm (1/4)
- Terminal spacing 4,7 mm (.185)
- Epoxy sealed terminals standard
- 1 and 2 pole configurations

### MODEL STRUCTURE




For model structure numbers, refer to 5200Z models and replace 2 with 9.




## 5100Z models

- Threaded bushing Ø 6 mm x 0.75 SI (.236 x 0.75 IS)
- Terminal spacing 4,7 mm (.185)
- Epoxy sealed terminals standard
- 1 and 2 pole configurations


### MODEL STRUCTURE



For model structure numbers, refer to 5200Z models and replace 2 with 1.



Threaded bushing Ø 6,35 (1/4) : 5200MIWR



- 

```



graph LR
    Start[ ] --- Node1[1 | ]
    Node1 --- Node2[2 | ]
    Node2 --- Node3[3 | ]
    Node3 --- Node4[4 | ]
    Node4 --- Node5[5 | ]
    Node5 --- Node6[6 | ]
    Node6 --- Node7[7 | ]
    Node7 --- Node8[8 | ]
    Node8 --- Null[ ]
    style Start fill:none,stroke:none
    style Null fill:none,stroke:none
  
```

→ Keyway



III                  II                  I  
2-3                                  1-2

|     |     |     |
|-----|-----|-----|
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |





→ Keyway




5246MIWR  
5249MIWR  
5247MIWR  
5248MIWR  
5242MIWR  
5244 MIWR\*  
5244 1R MIWR\*  
5244 2R MIWR\*

|     |    |     |
|-----|----|-----|
| III | II | I   |
| 2-3 |    | 1-2 |
| 5-6 |    | 4-5 |

ON - ON  
ON OFF ON  
MOM OFF MOM  
ON OFF MOM  
ON - MOM  
ON ON ON  
ON ON MOM  
MOM ON MOM



**APEM**



- Terminal spacing 4,7 mm (.185)
- 1, 2 and 3 pole configurations

Special switch **5200WX404** with reduced overall dimensions is presented under "Special options".

### MODEL STRUCTURE




Shown with standard lever

### Single pole



**5236W**  
**5239W**  
**5237W**  
**5238W**  
**5232W**

| III | II  | I   |
|-----|-----|-----|
| 2-3 |     | 1-2 |
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |




### Double pole



**5246W**  
**5249W**  
**5247W**  
**5248W**  
**5242W**  
**5244W\***  
**5244W 1R\***  
**5244W 2R\***

| III | II  | I   |
|-----|-----|-----|
| 2-3 |     | 1-2 |
| 5-6 |     | 4-5 |
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |
| ON  | ON  | ON  |
| ON  | ON  | MOM |
| MOM | ON  | MOM |




\*Function 4 : SP in DP case - specify CT or TH connections, see end of catalogue.

### Three pole



**5256W**  
**5259W**  
**5257W**  
**5258W**  
**5252W**

| III | II  | I   |
|-----|-----|-----|
| 2-3 |     | 1-2 |
| 5-6 |     | 4-5 |
| 8-9 |     | 7-8 |
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |




# 5000 series

## Toggle switches - plain bushing

Right angle terminals - horizontal : 5400W

MODEL  
STRUCTURE

### PCB MOUNTING FOR 5200W



### 5400W models

- Terminal spacing 4 mm (.157)
- 1 and 2 pole configurations


Diagram, as per 5200W model

### MODEL STRUCTURE




For model structure numbers, refer to **5200W** single and double pole and replace 2 with 4.


### PC LAYOUT



SP




DP



- Pin spacing 3,81 mm (.150)
- 1, 2, 3 and 4 pole configurations

### MODEL STRUCTURE




Shown with standard lever

### Single pole



5236WW  
5239WW  
5237WW  
5238WW\*\*  
5232WW\*\*

| III | II  | I   |
|-----|-----|-----|
| 2-3 |     | 1-2 |
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |




### Double pole



5246WW  
5249WW  
5247WW  
5248WW\*\*  
5242WW\*\*  
5244WW\*  
5244WW 1R\*  
5244WW 2R\*

| III | II  | I   |
|-----|-----|-----|
| 2-3 |     | 1-2 |
| 5-6 |     | 4-5 |
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |
| ON  | ON  | ON  |
| ON  | ON  | MOM |
| MOM | ON  | MOM |




### Three pole



5256WW  
5259WW  
5257WW  
5258WW\*\*  
5252WW\*\*

| III | II  | I   |
|-----|-----|-----|
| 2-3 |     | 1-2 |
| 5-6 |     | 4-5 |
| 8-9 |     | 7-8 |
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |



\* and \*\* : see notes next page.

# 5000 series

## Toggle switches - plain bushing

Right angle terminals - vertical : 5200WW - 5400WW

MODEL  
STRUCTURE

### Four pole



5266WW  
5269WW  
5267WW  
5268WW\*\*  
5262WW\*\*  
5264WW\*  
5264WW 1R\*  
5264WW 2R\*

| III   | II | I     |
|-------|----|-------|
| 2-3   |    | 1-2   |
| 5-6   |    | 4-5   |
| 8-9   |    | 7-8   |
| 11-12 |    | 10-11 |

|     |     |     |
|-----|-----|-----|
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |
| ON  | ON  | ON  |
| ON  | ON  | MOM |
| MOM | ON  | MOM |



\* Function 4 : SP in DP case, DP in 4P case - specify CT or TH connections, see end of catalogue.

\*\* Functions 2 and 8 : reversed connection available, consult factory.

### PCB MOUNTING




### 5400WW models

- Pin spacing 2,54 mm (.100)
- 1, 2, 3 and 4 pole configurations


Diagram as per 5200WW model

### MODEL STRUCTURE



For model structure numbers, refer to **5200WW** models and replace 2 with 4.


### PC LAYOUT





Brackets reduce mechanical stress on solder joints and increase resistance to vibrations.  
Bracket material : tin plated steel.

- Epoxy sealed terminals standard
- 1 and 2 pole configurations



MODEL  
STRUCTURE



Shown with standard lever


### Short bracket - width 15,75 (.620) - single pole : 5230Y



5236Y B  
5239Y B  
5237Y B  
5238Y B  
5232Y B

| III | II | I   |
|-----|----|-----|
| 2-3 |    | 1-2 |

|     |     |     |
|-----|-----|-----|
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |




### Short bracket - width 15,75 (.620) - double pole : 5240Y



5246Y B  
5249Y B  
5247Y B  
5248Y B  
5242Y B  
5244Y B\*  
5244Y 1R B\*  
5244Y 2R B\*

| III | II | I   |
|-----|----|-----|
| 2-3 |    | 1-2 |
| 5-6 |    | 4-5 |

|     |     |     |
|-----|-----|-----|
| ON  | -   | ON  |
| ON  | OFF | ON  |
| MOM | OFF | MOM |
| ON  | OFF | MOM |
| ON  | -   | MOM |
| ON  | ON  | ON  |
| ON  | ON  | MOM |
| MOM | ON  | MOM |



\* Function 4 : SP in DP case - specify CT or TH connections, see end of catalogue.

# 5000 series

## Toggle switches - plain bushing

Straight PC terminals - bracket mounting : 5200Y4 - Y6 - Y7

MODEL  
STRUCTURE

### Tall bracket - width 15,75 (.620) : 5200Y4



| Single pole | Double pole  | III | II      | I   |
|-------------|--------------|-----|---------|-----|
| 5236Y4 B    | 5246Y4 B     | 2-3 |         | 1-2 |
| 5239Y4 B    | 5249Y4 B     | 5-6 |         | 4-5 |
| 5237Y4 B    | 5247Y4 B     |     | ON      | ON  |
| 5238Y4 B    | 5248Y4 B     |     | ON OFF  | ON  |
| 5232Y4 B    | 5242Y4 B     |     | MOM OFF | MOM |
|             | 5244Y4 B*    |     | ON      | MOM |
|             | 5244Y4 1R B* |     | ON ON   | MOM |
|             | 5244Y4 2R B* |     | MOM ON  | MOM |



### Short bracket - width 19,05 (.750) : 5200Y6




| Single pole | Double pole  | III | II      | I   |
|-------------|--------------|-----|---------|-----|
| 5236Y6 B    | 5246Y6 B     | 2-3 |         | 1-2 |
| 5239Y6 B    | 5249Y6 B     | 5-6 |         | 4-5 |
| 5237Y6 B    | 5247Y6 B     |     | ON      | ON  |
| 5238Y6 B    | 5248Y6 B     |     | ON OFF  | ON  |
| 5232Y6 B    | 5242Y6 B     |     | MOM OFF | MOM |
|             | 5244Y6 B*    |     | ON      | MOM |
|             | 5244Y6 1R B* |     | ON ON   | MOM |
|             | 5244Y6 2R B* |     | MOM ON  | MOM |



### Tall bracket - width 19,05 (.750) : 5200Y7



| Single pole | Double pole  | III | II      | I   |
|-------------|--------------|-----|---------|-----|
| 5236Y7 B    | 5246Y7 B     | 2-3 |         | 1-2 |
| 5239Y7 B    | 5249Y7 B     | 5-6 |         | 4-5 |
| 5237Y7 B    | 5247Y7 B     |     | ON      | ON  |
| 5238Y7 B    | 5248Y7 B     |     | ON OFF  | ON  |
| 5232Y7 B    | 5242Y7 B     |     | MOM OFF | MOM |
|             | 5244Y7 B*    |     | ON      | MOM |
|             | 5244Y7 1R B* |     | ON ON   | MOM |
|             | 5244Y7 2R B* |     | MOM ON  | MOM |



\* Function 4 : SP in DP case - specify CT or TH connections, see end of catalogue.




# 5000 series

## Toggle switches

### CONTACT MATERIALS


UG1410A



- A Silver
- AD Silver, gold plated
- CD Brass, gold plated


Special contacts for peak currents : see X814, under "Special Options".

### FINISH



- Blank Nickel plated
- G Black finish on bushing, actuator and hardware

### SEALING



- Blank
  - For 5000 - 5200Z and 5200MIWR models : epoxy sealed terminals standard
  - Other models : no sealing required

- B Epoxy sealed terminals

- K Front panel sealing by one O-ring and sealing washer. Protects the switch against water and dust. Panel seal withstands 1 bar pressure and remains sealed even when switch is operated.




Available on models with  $\varnothing 6,35$  (1/4) or 11,9 (15/32) **threaded bushing only.**  
Not available with levers 8, 9, 12, 22, 23.



- KB Combined sealings

- ① O-ring
- ② Sealing washer




Sealing by two O-rings, see X408 under "Special options".

# 5000 series

## Toggle switches

OPTIONS  
● ● ●

### FLUORESCENT TIP



Blank

None

Standard lever

Locking lever


-038

White fluorescent tip.  
Becomes luminous when submitted to ultraviolet rays.




Available with matt black finish (option G) only.

Consult factory for levers available with this option.



-19




Same dimensions as standard actuator below.

### ACTUATORS




Levers for threaded bushing models Ø 6,35 (1/4) or Ø 6 (.236)

Dash compulsory before lever code.




Blank

Standard




-2




-4N

For use with paddles only




-8

Not available with sealing options K or X408




-9

Not available with sealing options K or X408




-12


Not available with sealing options K or X408



-16



-17




-21 (+U640)

U640 to be placed in last box of ordering format. Replace 0 by colour code.



### ACTUATORS (continued)



**-22**

Not available with sealing options K or X408



**-23**


Not available with sealing options K or X408



**-25**

Not available with sealing options K or X408

### Levers for threaded bushing models Ø 11,9 (15/32) : 5600M




**Blank**

Standard




**-27**

### Locking levers




**-1V**

1 locked position (function 6)



**-2V**

2 locked positions (function 6)



**-3V**

3 locked positions (functions 9 and 4)

Consult factory for other locking lever options.




Available with Ø 6,35 mm (1/4) threaded bushing models only.  
For plain bushing models, see X386 or X916 under "Special options" on the following pages.

### ACTUATORS (continued)


For plain bushing models : W - WW and Y

A




Blank

Standard




-2




-4N


For use with paddles only




-7



-16



-17



-21 (+U640)

U640 to be placed in last box of ordering format. Replace 0 by colour code.

#### Actuator colours

Replace "0" by number

|     |           |
|-----|-----------|
| 1   | blue      |
| 1/4 | dark blue |
| 2   | black     |
| 3   | green     |
| 4   | grey      |
| 5   | yellow    |
| 6   | red       |
| 7   | ivory     |
| 7/1 | white     |
| 9   | orange    |



#### LEVER LENGTH

With bracket or mounting plate lever length will be reduced by 0,4 mm (.015) as a rule. Please refer to switch technical drawings in "Model Structure" pages for details.



# 5000 series

## Toggle switches


### SPECIAL OPTIONS

**Blank** No special requirement



**X408** Front panel sealing by two O-rings. Flatted bushing for precise orientation. Protects the switch against water and dust. Panel seal withstands 1 bar pressure and remains sealed even when switch is operated. Includes sealed terminals (option B).




Available only on models with threaded bushing except 5600M. Not available with levers 8, 9, 12, 22, 23.



**X404** Horizontal right angle with reduced overall dimensions (shown with lever -16)









|               | III | II  | I   |
|---------------|-----|-----|-----|
|               | 2-3 |     | 1-2 |
|               | 5-6 |     | 4-5 |
| Single pole   |     |     |     |
| 5236W X404    | ON  | -   | ON  |
| 5239W X404    | ON  | OFF | ON  |
| 5237W X404    | MOM | OFF | MOM |
| 5238W X404    | ON  | OFF | MOM |
| 5232W X404    | ON  | -   | MOM |
| 5244W X404*   | ON  | ON  | ON  |
| 5244W1R X404* | ON  | ON  | MOM |
| 5244W2R X404* | MOM | ON  | MOM |








\* Function 4 : SP in DP case - specify CT or TH connections, see end of catalogue.

Levers lengths for WX404 (also available with X445 option)



Note : levers -8, -9 and -12 not available with function 2 (ON-MOM)



\* U640 to be placed in last box of ordering format. Replace 0 by colour code.

Insulating caps and paddles for X404 :

Insulating cap U1710 available with lever style 16.

Paddles U240N, U290N and U390N available with lever style 4N. See details on next pages.

### SPECIAL OPTIONS (continued)

- X371** Plain bushing Ø 6,25 mm (.246) (instead of standard threaded bushing).
- X372** Threaded bushing Ø 6,35 (1/4). **Height 7 mm (.274).**
- X386** Threaded bushing Ø 6,35 mm (1/4) to replace plain bushing on models W - WW and Y.
- X442** Threaded bushing Ø 6,35 mm (1/4) - **Height 9,9 mm (.389).**
- X445** Plain bushing. **Height 7,2 mm (.283)** - for W, WW and Y models. Available with the same levers, insulating cap and paddles as X404.
- X601** **Silver plated brass contacts.**  
Current/voltage rating for an electrical life of 20.000 cycles : 0,5A 30VDC.  
Minimum quantity : 5.000 pieces per model and shipment.

**X681** **Satin chrome** actuator

### X814 Switches for peak currents

Peak current up to 120A (1 ms) 60VDC - single/double pole



Single pole  
**5636A X814** ON - ON

Double pole  
**5646A X814** ON - ON







- Contacts : silver/nickel alloy (AgNi)
- Max. current/voltage rating : 2/120A (1 ms) 60VDC - 10.000 cycles
- Further specifications and dimensions : see 5600 series.
- General information on peak currents : see end of catalogue.

**X902** Plain bushing Ø 6,25 mm (.246) - **Height 9 mm (.354)** (not available with K sealing option).

**X916** Locking lever on model with plain bushing.



With options X372, X386, X442 and X445, the lever lengths indicated on previous pages will be modified.






# 5000 series

## Toggle switches

### AGENCY APPROVALS



**UL** All standard models, except 5200MIWR

**CSA**

**CECC** Standard models 5600 - 5200

**Availability** : consult factory for details of approved combinations or options.


**Marking** : to order switches marked UL, CSA or CECC, complete above box with desired approvals, in this order & without space (ex. : ULCSACECC). Blank : no agency approval required.

**VDE (with UL & CSA)**


Refer to 55000 series on the following pages.

Preferential lists : see specifications.

### INSULATING CAPS AND PADDLES




#### Insulating caps




**U270**

For standard lever & threaded bushing only



**U1040**

For standard lever & plain bushing only



**U1710**

For lever 17 and threaded bushing  
For lever 7 and plain bushing

#### Cap colours

Replace last "0" by number

|     |           |
|-----|-----------|
| 1   | blue      |
| 1/4 | dark blue |
| 2   | black     |
| 3   | green     |
| 4   | grey      |
| 5   | yellow    |
| 6   | red       |
| 7/1 | white     |
| 9   | orange    |



Insulating caps are not available in ivory colour.

# 5000 series

## Toggle switches

OPTIONS  
● ● ●

### INSULATED CAPS AND PADDLES (continued)

#### Paddles

For use with lever 4N only. Shown with standard threaded bushing. Order separately.



#### Paddle colours

Replace last  
"0" by number

|     |           |
|-----|-----------|
| 1   | blue      |
| 1/4 | dark blue |
| 2   | black     |
| 3   | green     |
| 4   | grey      |
| 5   | yellow    |
| 6   | red       |
| 7   | ivory     |
| 7/1 | white     |
| 9   | orange    |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Apem:

[5646A](#) [5638AKB](#) [5637AG](#) [5257WCDB16](#) [5636ADKB16](#) [5646AB](#) [5636AB](#) [5644TH1RAGB8](#) [5236WCDB16X404](#)  
[5636AGK-2V](#) [5666MA16](#) [5242MIWRCD](#) [5666A16](#) [5236CDB](#) [5636AG](#) [5636AG-2V](#) [5242WWCDB16X445](#)  
[5248WCDB16X404](#) [5642MAB](#) [5644TH1RAB9](#) [5644TH2RAKB](#) [5647AKB](#) [5648AKB](#) [5648MAB](#) [5652AKB](#) [5652MAB](#)  
[5657AKB](#) [5658AKB](#) [5658MAB](#) [5662MAB](#) [5664MTH1RAB](#) [5664TH1RAB9](#) [5664TH1RAKB](#) [5664THAKB](#)  
[5666AB1V](#) [5667AKB](#) [5668AKB](#) [5668MAB](#) [5669AB3V](#) [5669MAB](#) [5232AB](#) [5232ABULCSA](#) [5232CDB](#)  
[5232WCDB16X404](#) [5232WWCDB16X445](#) [5232ZA](#) [5236AB](#) [5236ABULCSA](#) [5236CDBF](#) [5236CDGKB2V](#)  
[5236MIWRCD](#) [5236MIWRCDK2V](#) [5236WAB16X404](#) [5236WWAB16X386](#) [5236WWAB16X445](#) [5236WWCD](#)  
[5236WWCDB16X445](#) [5236WWCDBX386](#) [5236YAB16X386](#) [5236YCDB16X445](#) [5236ZA](#) [5236ZAULCSA](#) [5237AB](#)  
[5237CDB](#) [5237WCDB16X404](#) [5237WWCD](#) [5237WWCDB16X445](#) [5237ZA](#) [5238AB](#) [5238CDB](#) [5238WCDB16X404](#)  
[5238WWCDB16X445](#) [5239AB](#) [5239CDB](#) [5239WAB16X404](#) [5239WCDB16X404](#) [5239WWCDB16X445](#)  
[5239YAB16X386](#) [5239YCDB16X445](#) [5239ZA](#) [5242CDB](#) [5242WAB](#) [5242WCDB16X404](#) [5244THCDB](#) [5246AB](#)  
[5246AB16X371](#) [5246CDB](#) [5246CDGKB2V](#) [5246MIWRA](#) [5246MIWRADX449](#) [5246WAB16X404](#) [5246WCDB16X404](#)  
[5246WWAB16X386](#) [5246WWCDB16X445](#) [5246YCDB16X445](#) [5246ZA](#) [5247AB](#) [5247CDB](#) [5247WCDB16X404](#)  
[5247WWCDB16X445](#)