



Micro Commercial Components
20736 Marilla Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

1SS136

Features

- High reliability.
- High speed. (t_{rr} =2.0ns Max.)
- Silicon epitaxial planar

Absolute maximum Ratings


Symbol	Rating	Rating	Unit
V_{RM}	Peak Reverse Voltage	75	V
V_R	DC Reverse Voltage	65	V
I_{FM}	Peak Forward Current	600	mA
I_O	Mean Rectifying Current	200	mA
I_{surge}	Surge Current (1us)	4.0	A
T_J	Operating Junction Temperature	-55 to +150	$^{\circ}C$
T_{STG}	Storage Temperature	-55 to +150	$^{\circ}C$

Electrical Characteristics @ 25 $^{\circ}C$ Unless Otherwise Specified

Symbol	Parameter	Min	Max	Units
OFF CHARACTERISTICS				
V_F	Forward Voltage ($I_F=100mA$)	---	1.0	Vdc
I_R	Reverse Current ($V_R=65V$)	---	0.5	μA
C_T	Capacitance Between Terminals ($V_R=0$, $f=1.0MHz$)	---	3.0	pF
t_{rr}	Reverse Recovery Time ($V_R=6.0V$, $I_F=10mA$)	---	2.0	ns

High Speed Switching Diode

DO-34



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.094	.118	2.40	3.00	
B	.063	.079	1.60	2.00	
C	.012	.020	0.30	0.50	
D	1.102	1.181	28.00	30.00	