

3.2×2.5mm for Consumer Products/ Mobile Communications/ Automotive



RoHS Compliant

Features

- Crystal unit for Consumer Products
- Miniature and low profile (3.2×2.5×0.55mm)
- Ceramic package
- Reflow compatible
- AEC-Q200 qualified
(Please contact us for Automotive use)

Applications

- Digital Electronics
- Consumer Products
- Car Electronics
- Mobile Communications, Bluetooth®, Wireless LAN

* Bluetooth® Trademarks are owned by Bluetooth SIG Inc.

How to Order

CX3225SB 12000 □ □ □ □ □ □ □

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series ② Frequency
③ Load Capacitance ④ Frequency Tolerance

D0 8 pF **G** ±15×10⁻⁶

⑤ Operating Temp. Range ⑥ Frequency Temp. Stability

EJ -10 to +70°C ±15×10⁻⁶

LJ -30 to +85°C ±15×10⁻⁶

PS -40 to +125°C ±50×10⁻⁶

⑦ Individual Specification

Packaging (Tape & Reel 1000/ 3000 pcs./ reel)

Specifications

Item	Symbol	Specification			Units	Remarks
Frequency Range	f _{nom}	12000 to 54000			kHz	
Overtone Order	OT	Fundamental			—	
Load Capacitance	CL	8			pF	Please contact us for other Load Capacitance.
Frequency Tolerance	f _{tol}	±15			×10 ⁻⁶	25°C±3°C
Motional Series Resistance	R1	Table 1			ohm	
Drive Level	DL	Table 2			μW	
Operating Temp. Range	T _{use}	-10 to +70	-30 to +85	-40 to +125	°C	
Storage Temp. Range	T _{stg}	-40 to +85		-40 to +125	°C	
Frequency Temp. Characteristics	f _{tem}	±15		±50	×10 ⁻⁶	Freq. deviation from the value at 25°C

Please contact us for other specifications.

Table1 Motional Series Resistance


Frequency Range	Motional Series Resistance
12000≤f _{nom} <13000kHz	150Ω max.
13000≤f _{nom} <20000kHz	80Ω max.
20000≤f _{nom} ≤54000kHz	50Ω max.

Table2 Level of Drive

Frequency Range	Level of Drive
12000≤f _{nom} ≤54000kHz	10μW (100μW max.)


Dimensions

(Unit: mm)



Recommended Land Pattern

(Unit: mm)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AVX:

[CX3225SB24576D0FEQZZ](#) [CX3225SB27000D0FEJZZ](#) [CX3225SB16000E0FPZ25](#) [CX101F-040.000-H0445](#)
[CX3225SB-16.00-H2950](#) [CX3225SB-26.00-H2827](#) [CX3225SB26000H0FLJZZ](#) [CX3225SB24000D0HERZ1](#)
[CX3225SB12000D0FLJZZ](#) [CX3225SB12288D0FLJZ1](#) [CX3225SB13560D0FLJ14](#) [CX3225SB27000H0FZF33](#)
[CX3225SB24576H0KESZZ](#) [CX3225SB26000D0FLJZZ](#) [CX3225SB16000D0FLJZZ](#) [CX3225SB2000D0FPLCC](#)
[CX3225SB25000D0FPLCC](#) [CX3225SB40000D0FPLCC](#) [CX3225SB38400D0FPLCC](#) [CX3225SB40000D0FFFCC](#)
[CX3225SB16000D0FPLCC](#) [CX3225SB12000D0FFJCC](#) [CX3225SB13560D0FPLCC](#) [CX3225SB16000D0FFJCC](#)
[CX3225SB19200D0FPLCC](#) [CX3225SB48000D0FFFCC](#) [CX3225SB32000D0FPLCC](#) [CX3225SB30000D0FPLCC](#)
[CX3225SB12000D0FPNCC](#) [CX3225SB24000D0FFJCC](#) [CX3225SB48000D0FPLCC](#) [CX3225SB24000D0FPLCC](#)
[CX3225SB27000D0FFFCC](#) [CX3225SB38400D0FFFCC](#) [CX3225SB32000D0FFFCC](#) [CX3225SB27000D0FPLCC](#)
[CX3225SB26000D0FFFCC](#) [CX3225SB25000D0FFFCC](#) [CX3225SB20000D0FPLCC](#) [CX3225SB48000D0FPJC1](#)
[CX3225SB54000D0WPSC1](#) [CX3225SB48000D0WPSC1](#) [CX3225SB54000D0WPSC2](#) [CX3225SB48000D0FPJC2](#)
[CX3225SB54000D0FPJC2](#) [CX3225SB54000D0FPJC1](#) [CX3225SB48000D0WPSC2](#)