ADAM-6050
ADAM-6051
ADAM-6052

18-ch Isolated Digital I/O Module
14-ch Isolated Digital I/O Module with 2-ch Counter
16-ch Source-type Isolated Digital I/O Module

ADAM-6050

ADAM-6051

ADAM-6052

Specifications

Digital Input

- **Channels** 12
- **Dry Contact** Logic level 0: close to GND
  Logic level 1: open
- **Wet Contact** Logic level 0: 0 ~ 3 V_{DC}
  Logic level 1: 10 ~ 30 V_{DC}
- **Supports 3 kHz Counter Input (32-bit + 1-bit overflow)**
- **Keep/Discard Counter Value when Power-off**
- **Supports 3 kHz Frequency Input**
- **Supports Inverted DI Status**

Digital Output

- **Channels** 6 (Sink Type)
- **Open Collector to 30 V, 100 mA maximum load**
- **Supports 5 kHz Pulse Output**
- **Supports High-to-Low and Low-to-High Delay Output**

Ordering Information

- **ADAM-6050** 18-ch Isolated DI/O Module

Specifications

Digital Input

- **Channels** 12
- **Dry Contact** Logic level 0: close to GND
  Logic level 1: open
- **Wet Contact** Logic level 0: 0 ~ 3 V_{DC}
  Logic level 1: 10 ~ 30 V_{DC}
- **Supports 3 kHz Counter Input (32-bit + 1-bit overflow)**
- **Keep/Discard Counter Value when Power-off**
- **Supports 3 kHz Frequency Input**
- **Supports Inverted DI Status**

Counter Input

- **Channels** 2
- **Mode** Counter, Frequency
- **Keep/Discard Counter Value when Power-off**
- **Maximum Count** 4,294,967,295
  (32-bit + 1-bit overflow)
- **Input Frequency** Frequency Mode:
  0.2 ~ 4500 Hz
  Counter Mode: 0 ~ 4.5 kHz

Digital Output

- **Channels** 2 (Sink Type)
- **Open Collector to 30 V, 100 mA maximum load**
- **Supports 5 kHz Pulse Output**
- **Supports High-to-Low and Low-to-High Delay Output**

Ordering Information

- **ADAM-6051** 16-ch Isolated DI/O with Counter Module

Specifications

Digital Input

- **Channels** 8
- **Dry Contact** Logic level 0: close to GND
  Logic level 1: open
- **Wet Contact** Logic level 0 : 0 ~ 3 V_{DC}
  Logic level 1 : 10 ~ 30 V_{DC}
- **Supports 3 kHz Counter Input (32-bit + 1-bit overflow)**
- **Keep/Discard Counter Value when Power-off**
- **Supports 3 kHz Frequency Input**
- **Supports Inverted DI Status**

Digital Output

- **Channels** 8 (Source Type)
- **Digital Output** 10 ~ 35 V_{DC}
- **Current** 1 A (per channel)
- **Supports 5 kHz Pulse Output**
- **Supports High-to-Low and Low-to-High Delay Output**
- **Supports Over Current Protection**

Ordering Information

- **ADAM-6052** 16-ch Source-type Isolated DI/O Module

Common Specifications

General

- **LAN** 10/100Base-T(X)
- **Power Consumption** 2 W @ 24 V_{DC}
- **Connectors** 1 x RJ-45 (LAN), Plug-in screw terminal block (I/O and power)
- **Watchdog** System (1.6 second) and Communication (programmable)
- **Power Input** 10 ~ 30 V_{DC}
- **Supports Peer-to-Peer**
- **Supports GCL**
- **Supports Modbus/TCP, TCP/IP, UDP and HTTP Protocol**

Protection

- **Power Reversal Protection**
- **Isolation Protection** 2,000 V_{DC}

Environment

- **Operating Temperature** -10 ~ 70° C
- **Storage Temperature** -20 ~ 80° C
- **Humidity (Operating)** 20 ~ 95% RH (non-condensing)
- **Humidity (Storage)** 0 ~ 95% RH (non-condensing)