

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0009502242

Status:


Active

Overview:

kk

Description:

3.96mm (.156") Pitch KK® Crimp Terminal Housing, Friction Ramp, 24 Circuits



Series

image - Reference only

Documents:

- 3D Model

Product Specification PS-08-50 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Crimp Housings

Series

2139

Application

Power, Wire-to-Board

Overview

kk

Product Name

KK®

Physical

Circuits (maximum)

24

Color - Resin

Natural

Flammability

94V-2

Gender

Plug

Glow-Wire Compliant

No

Keying to Mating Part

Yes

Lock to Mating Part

Yes

Material - Resin

Nylon

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

3.96mm (.156")

Pitch - Termination Interface

3.96mm (.156")

Polarized to Mating Part

No

Stackable

No

Temperature Range - Operating

0°C to +75°C

Material Info

Old Part Number

2139-24P

Reference - Drawing Numbers

Product Specification

PS-08-50

Sales Drawing

SD-2139

EU RoHS

China RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

2139Series

Use With

2478 Crimp Terminals for 18-24 AWG, 2578 Crimp Terminals for 22-26 AWG

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[09-50-2242](#)